

		Material Composition Declaration © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.			This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.					
1752-21.1		IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x		Form Type * Distribute		Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information				
Supplier Information										
Company name* onsemi			Company unique ID		Unique ID Authority			Response Date* 2024-04-25		
Contact Name Product-Env-Stewards			Title - Contact Product Enviro Compliance		Phone - Contact* NA			Email - Contact* Product-Env-Stewards@onsemi.com		
Authorized Representative* Product-Env-Stewards			Title - Representative Product Enviro Compliance		Phone - Representative* NA			Email - Representative* Product-Env-Stewards@onsemi.com		
	Requester Item Number	Mfr Item Number	Mfr Item Name		Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
		FNA40560	IPM SPM45 600V 5A		2024-04-25		CPA	11113.298	mg	Each
Manufacturing Process Information										
	Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating		Peak Process Body Temperature		Max Time at Peak Temperature		Number of Reflow Cycles	
	Matte Tin (Sn) - annealed	CU Alloy	NA		0	C	30	seconds	3	
Comments										
For more information regarding material composition please refer to page 3										

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a "RoHS restricted substance") in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
RoHS Declaration *	4 - Item(s) does not contain RoHS restricted substances per the definition above except for selected exemptions		Supplier Acceptance * Accepted
Exemption: 7a: Lead in high melting temperature type solders (i.e. lead based solder alloys containing 85% by weight or more lead).			
Exemption List Version	EL-2011/534/EU		
Declaration Signature			
Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.			
Supplier Digital Signature	Rastislav Drska		

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Die	37.4431	mg	Supplier	Silicon (Si)	7440-21-3		37.4431	mg
Die Attach	2.3868	mg	Supplier	Silver (Ag)	7440-22-4		1.7901	mg
			Supplier	Phenolic Resin-2	54208-63-8		0.5967	mg
Die Attach Solder	43.092	mg	Supplier	Silver (Ag)	7440-22-4		1.0773	mg
			A	Lead (Pb)	7439-92-1	7a	39.8601	mg
			Supplier	Tin (Sn)	7440-31-5		2.1546	mg
Heat Sink Attach	23.1894	mg	Supplier	Dicyandiamine	461-58-5		1.6233	mg
			Supplier	Ortho Cresol Novolac Resin	29690-82-2		1.8552	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		19.711	mg
Lead Frame	3510.64	mg	Supplier	Silver (Ag)	7440-22-4		884.6813	mg
			Supplier	Copper (Cu)	7440-50-8		2625.9585	mg
Mold Compound-Black	6269.7	mg	Supplier	Ortho Cresol Novolac Resin	29690-82-2		423.2048	mg
			Supplier	Carbon Black (C)	1333-86-4		31.3485	mg
			Supplier	Fused Silica (SiO2)	60676-86-0		5391.9424	mg
			Supplier	Phenolic Resin (Novolac)	9003-35-4		423.2048	mg
Plating	60.7986	mg	Supplier	Tin (Sn)	7440-31-5		60.7986	mg
Substrate	1138.32	mg	Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		1104.1704	mg
			Supplier	Silicon Dioxide (SiO2)	99493-55-7		11.3832	mg
			Supplier	Cobalt Oxide (CoO)	1307-96-6		11.3832	mg
			Supplier	Manganese Tetraoxide (Mn3O4)	1317-35-7		11.3832	mg
Thermistor	4.4737	mg	Supplier	Silver (Ag)	7440-22-4		0.3579	mg
			Supplier	Tin (Sn)	7440-31-5		0.076	mg
			Supplier	Nickel Oxide (NiO)	1313-99-1		1.1631	mg
			Supplier	Palladium (Pd)	7440-05-3		0.1521	mg
			Supplier	Iron Trioxide (Fe2O3)	1309-37-1		0.0002	mg
			B	Nickel (Ni)	7440-02-0		0.0313	mg
			Supplier	Cobalt Oxide (Co3O4)	1308-06-1		0.7694	mg
			Supplier	Manganese Tetraoxide (Mn3O4)	1317-35-7		1.9236	mg
Wire Bond - Al	22.005	mg	Supplier	Aluminum (Al)	7429-90-5		22.005	mg
Wire Bond - Cu	1.2488	mg	Supplier	Palladium (Pd)	7440-05-3		0.025	mg
			Supplier	Copper (Cu)	7440-50-8		1.2238	mg