

 <b>Material Composition Declaration</b> © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.		This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.								
1752-21.1		IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>			Form Type * Distribute		Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information			
<b>Supplier Information</b>										
Company name* <b>onsemi</b>			Company unique ID			Unique ID Authority		Response Date* <b>2024-04-24</b>		
Contact Name <b>Product-Env-Stewards</b>			Title - Contact Product Enviro Compliance			Phone - Contact* <b>NA</b>		Email - Contact* <b>Product-Env-Stewards@onsemi.com</b>		
Authorized Representative* <b>Product-Env-Stewards</b>			Title - Representative Product Enviro Compliance			Phone - Representative* <b>NA</b>		Email - Representative* <b>Product-Env-Stewards@onsemi.com</b>		
	Requester Item Number	Mfr Item Number	Mfr Item Name		Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
		FUSB302BMPX	USB-C Port Control w/ PD		2024-04-24		TH2	17.833	mg	Each
<b>Manufacturing Process Information</b>										
	Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating		Peak Process Body Temperature		Max Time at Peak Temperature		Number of Reflow Cycles	
	Precious metal (e.g. Ag,Au, NiPdAu) (no Sn)	CU Alloy	1		260	C	30	seconds	3	
Comments <b>level 1 - maximum time at peak temperature during soldering is 10-30 seconds</b> <b>For more information regarding material composition please refer to page 3</b>										

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a “RoHS restricted substance”) in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier’s liability and the Company’s remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
RoHS Declaration *	1 - Item(s) does not contain RoHS restricted substances per the definition above		Supplier Acceptance * Accepted
<b>Exemption: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.</b>			
Exemption List Version	EL-2011/534/EU		
Declaration Signature			
<b>Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.</b>			
Supplier Digital Signature	Rastislav Drska		

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Die	0.438	mg	Supplier	Silicon (Si)	7440-21-3		0.438	mg
Die Attach	0.06	mg	Supplier	Isobornyl Methacrylate	7534-94-3		0.0036	mg
			Supplier	Silver (Ag)	7440-22-4		0.0489	mg
			Supplier	Isobornyl Acrylate	5888-33-5		0.0036	mg
			Supplier	Misc.	Proprietary Data		0.0003	mg
			Supplier	Tricyclo[5.2.1.02,6]decanedimethanol Diacrylate (C18H24O4)	42594-17-2		0.0036	mg
Lead Frame	14.092	mg	Supplier	Zinc (Zn)	7440-66-6		0.017	mg
			Supplier	Iron (Fe)	7439-89-6		0.331	mg
			Supplier	Copper (Cu)	7440-50-8		13.74	mg
			Supplier	Phosphorus (P)	7723-14-0		0.004	mg
Mold Compound-Black	2.743	mg	Supplier	Carbon Black (C)	1333-86-4		0.0137	mg
			Supplier	Fused Silica (SiO2)	60676-86-0		2.4138	mg
			Supplier	Ortho-Cresol Novolac Resin	29690-82-2		0.1783	mg
			Supplier	Phenolic Resin (Novolac)	9003-35-4		0.1372	mg
Plating	0.103	mg	Supplier	Palladium (Pd)	7440-05-3		0.009	mg
			B	Nickel (Ni)	7440-02-0		0.092	mg
			Supplier	Gold (Au)	7440-57-5		0.002	mg
Wire Bond - Au	0.397	mg	Supplier	Gold (Au)	7440-57-5		0.397	mg