

**Material Composition Declaration**

© Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

1752-21.1

IPC Web Site for Information on IPC-1752 Standard
<http://www.ipc.org/IPC-175x>

Form Type *
Distribute

Declaration Class *
Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information

Supplier Information**Company name***

onsemi

Company unique ID

Unique ID Authority

Response Date*

2026-09-12

Contact Name

Title - Contact

Phone - Contact***Email - Contact*****Product-Env-Stewards**

Product Enviro Compliance

NA

Product-Env-Stewards@onsemi.com**Authorized Representative***

Title - Representative

Phone - Representative***Email - Representative*****Product-Env-Stewards**

Product Enviro Compliance

NA

Product-Env-Stewards@onsemi.com

	Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
		GBPC15005W	BR GBPCW GPPN 15A 50V	2026-09-12		TSCBE	16949.998	mg	Each

Manufacturing Process Information

	Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating	Peak Process Body Temperature	Max Time at Peak Temperature	Number of Reflow Cycles
	Precious metal (e.g. Ag,Au, NiPdAu) (no Sn)	CU Alloy	NA	0C	30seconds	3

Comments

For more information regarding material composition please refer to page 3

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a “RoHS restricted substance”) in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier’s liability and the Company’s remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.			
RoHS Declaration *	4 - Item(s) does not contain RoHS restricted substances per the definition above except for selected exemptions		Supplier Acceptance * Accepted
Exemption: 7a: Lead in high melting temperature type solders (i.e. lead based solder alloys containing 85% by weight or more lead). Exemption: 7c-I Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound.			
Exemption List Version	EL-2011/534/EU		
Declaration Signature			
Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.			
Supplier Digital Signature	Rastislav Drska		

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Case	2949.3	mg	Supplier	Ortho Cresol Novolac Resin	29690-82-2		589.8748	mg
			Supplier	Silica (SiO2)	14464-46-1		2064.5603	mg
			Supplier	Phosphorus (P)	7723-14-0		58.9152	mg
			Supplier	Phenolic Resin (Novolac)	9003-35-4		235.9497	mg
Die	33.561	mg	Supplier	Silicon (Si)	7440-21-3		30.2049	mg
			B	Nickel (Ni)	7440-02-0		0.2181	mg
			Supplier	Gold (Au)	7440-57-5		0.0503	mg
			Supplier	Lead Bisilicate	65997-18-4	7c	3.0876	mg
Die Attach Solder	18.1365	mg	Supplier	Silver (Ag)	7440-22-4		0.4534	mg
			A	Lead (Pb)	7439-92-1	7a	16.7763	mg
			Supplier	Tin (Sn)	7440-31-5		0.9068	mg
Die Attach Solder - Solder Wafer	82.8855	mg	Supplier	Silver (Ag)	7440-22-4		2.0721	mg
			A	Lead (Pb)	7439-92-1		76.6691	mg
			Supplier	Tin (Sn)	7440-31-5		4.1443	mg
Heat Sink	3803.24	mg	Supplier	Aluminum (Al)	7429-90-5		3803.24	mg
Lead Frame	1220.4	mg	Supplier	Iron (Fe)	7439-89-6		0.9763	mg
			Supplier	Copper (Cu)	7440-50-8		1219.1797	mg
			Supplier	Phosphorus (P)	7723-14-0		0.244	mg
Marking Ink	0.5085	mg	Supplier	Silicon Dioxide (SiO2)	112945-52-5		0.0254	mg
			Supplier	1-Hydroxycyclohexyl phenyl ketone	947-19-3		0.0254	mg
			Supplier	Padimate (C14H21NO2)	21245-01-2		0.0509	mg
			Supplier	2-Propenoic acid polymer	53192-18-0		0.3305	mg
			Supplier	Aluminum (Al)	7429-90-5		0.0763	mg
Mold Compound-White	6552.36	mg		Polymer Resin	proprietary data		1092.2784	mg
			Supplier	1,2-Bis(pentabromophenyl) ethane	84852-53-9		382.0026	mg
			Supplier	Brominated epoxy resin	Proprietary Data		1419.8964	mg
			B	Antimony Trioxide (Sb2O3)	1309-64-4		218.1936	mg
			Supplier	Carbon Black (C)	1333-86-4		54.3846	mg
			Supplier	Aluminum Hydroxide (Al(OH)3)	21645-51-2		655.236	mg
			Supplier	Fused Silica (SiO2)	60676-86-0		2730.3682	mg
Plating-2	14.916	mg	B	Nickel (Ni)	7440-02-0		14.916	mg
Terminal	2274.69	mg	Supplier	Iron (Fe)	7439-89-6		2.7296	mg

			Supplier	Copper (Cu)	7440-50-8		2270.9822	mg
			Supplier	Phosphorus (P)	7723-14-0		0.9781	mg