



Material Composition Declaration
 © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

1752-21.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information
-----------	--	---------------------------	---

Supplier Information

Company name* On Semiconductor	Company unique ID	Unique ID Authority	Response Date* 2021-06-17
Contact Name Product-Env-Stewards	Title - Contact Product Enviro Compliance	Phone - Contact* NA	Email - Contact* Product-Env-Stewards@onsemi.com
Authorized Representative* Product-Env-Stewards	Title - Representative Product Enviro Compliance	Phone - Representative* NA	Email - Representative* Product-Env-Stewards@onsemi.com

Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
	MT9V128IA3XTC-DR-E	VGA 1/4 SOC	2021-06-17		TWU	186.0	mg	Each

Manufacturing Process Information

Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating	Peak Process Body Temperature	Max Time at Peak Temperature	Number of Reflow Cycles
SnAgCu	CU Alloy	3	260 C	30 seconds	3

Comments
ATTENTION: MSL 3 Rated item requires Bake and Dry Pack (after electrical test)
For more information regarding material composition please refer to page 3

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a "RoHS restricted substance") in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
RoHS Declaration *	5 - Item(s) is obsolete, no information is available		Supplier Acceptance * Accepted
<p>Exemption: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.</p>			
Exemption List Version	EL-2011/534/EU		
Declaration Signature			
<p>Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.</p>			
Supplier Digital Signature	Rastislav Drska		

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Die	26.39	mg		Misc.	proprietary data		0.1003	mg
			Supplier	Silicon (Si)	7440-21-3		26.0285	mg
			Supplier	Aluminum (Al)	7429-90-5		0.2613	mg
Die Attach	2.2	mg	Supplier	Bisphenol A_Epichlorohydrin Polymer	25068-38-6		0.825	mg
			Supplier	Ethylene Glycol	107-21-1		0.022	mg
			Supplier	Sulfonium (Thiodi-4,1-phenylene)	89452-37-9		0.066	mg
			Supplier	Modified Silicon Dioxide (SiO2)	67762-90-7		0.462	mg
			Supplier	Formaldehyde Polymer	9003-36-5		0.825	mg
Imaging Lens	25.2	mg	Supplier	Titanium Dioxide (TiO2)	13463-67-7		1.26	mg
			Supplier	Sodium Monoxide (Na2O)	1313-59-3		1.26	mg
			Supplier	Boron Trioxide (B2O3)	1303-86-2		1.26	mg
			Supplier	Zinc Monoxide (ZnO)	1314-13-2		1.26	mg
			B	Antimony Trioxide (Sb2O3)	1309-64-4		0.126	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		1.26	mg
			Supplier	Potassium Monoxide (K2O)	12136-45-7		1.26	mg
			Supplier	Silica Crystalline (SiO2)	14808-60-7		17.514	mg
Lid Attach	1.45	mg	Supplier	Bisphenol A_Epichlorohydrin Polymer	25068-38-6		0.145	mg
			Supplier	Filler (SiO2)	68909-20-6		0.145	mg
			Supplier	Other Additive Agents	Proprietary Data		0.145	mg
			Supplier	Epoxy Prepolymer	Proprietary Data		0.435	mg
			Supplier	Formaldehyde Polymer	9003-36-5		0.58	mg
Mold Compound-Black	65.64	mg		Phenolic Resin	proprietary data		9.846	mg
			Supplier	Oxirane	39817-09-9		9.846	mg
			Supplier	1,4-Bis(2,3-epoxypropoxy)butane	2425-79-8		1.9692	mg
			Supplier	Carbon Black (C)	1333-86-4		0.6564	mg
			Supplier	Fused Silica (SiO2)	60676-86-0		42.0096	mg
			Supplier	Silica Crystalline (SiO2)	14808-60-7		1.3128	mg
Solder Ball	26.34	mg	Supplier	Silver (Ag)	7440-22-4		0.7902	mg
			Supplier	Tin (Sn)	7440-31-5		25.4181	mg
			Supplier	Copper (Cu)	7440-50-8		0.1317	mg
Substrate and Solder Mask	38.5	mg	Supplier	Fiber Glass (SiO2)	65997-17-3		8.1582	mg

			Supplier	Inorganic Filler of Solder Mask_Talc (Mg ₃ Si ₄ O ₁₀ (OH) ₂)	14807-96-6		0.5043	mg
			Supplier	Silica Amorphous (SiO ₂)	7631-86-9		0.1271	mg
			Supplier	Acetophenone Derivative	Proprietary Data		0.7546	mg
			Supplier	Carbon Black (C)	1333-86-4		0.1271	mg
			Supplier	2,4-Diethyl-9H-thioxanthen-9-one (DETX)	82799-44-8		0.1271	mg
			Supplier	Aluminum Hydroxide (Al(OH) ₃)	21645-51-2		3.7422	mg
			Supplier	Solvent Naphtha (Solvent oil)	64742-94-5		1.5092	mg
			Supplier	Bismaleimide Triazine resin	Proprietary Data		1.2936	mg
			Supplier	Copper (Cu)	7440-50-8		18.2528	mg
			Supplier	Barium Sulfate (BaSO ₄)	7727-43-7		3.9039	mg
Wire Bond - Au	0.28	mg	Supplier	Gold (Au)	7440-57-5		0.28	mg