



Material Composition Declaration
 © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

1752-21.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information
-----------	--	---------------------------	---

Supplier Information

Company name* On Semiconductor	Company unique ID	Unique ID Authority	Response Date* 2020-10-24
Contact Name Product-Env-Stewards	Title - Contact Product Enviro Compliance	Phone - Contact* NA	Email - Contact* Product-Env-Stewards@onsemi.com
Authorized Representative* Product-Env-Stewards	Title - Representative Product Enviro Compliance	Phone - Representative* NA	Email - Representative* Product-Env-Stewards@onsemi.com

Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
	MT9D131C12STC-DR	2.0 MP 1/3 SOC	2020-10-24		PHT	1140.11	mg	Each

Manufacturing Process Information

Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating	Peak Process Body Temperature	Max Time at Peak Temperature	Number of Reflow Cycles
Precious metal (e.g. Ag,Au, NiPdAu) (no Sn)	CU Alloy	3	260 C	30 seconds	3

Comments
ATTENTION: MSL 3 Rated item requires Bake and Dry Pack (after electrical test)
For more information regarding material composition please refer to page 3

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a "RoHS restricted substance") in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
RoHS Declaration *	1 - Item(s) does not contain RoHS restricted substances per the definition above		Supplier Acceptance * Accepted
Exemption: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.			
Exemption List Version	EL-2011/534/EU		
Declaration Signature			
Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.			
Supplier Digital Signature	Rastislav Drska		

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Ceramic Substrate	796.65	mg	Supplier	Cobalt (Co)	7440-48-4		1.0356	mg
			Supplier	Titanium Dioxide (TiO2)	13463-67-7		7.9665	mg
			Supplier	Tungsten (W)	7440-33-7		33.539	mg
			Supplier	Magnesium Monoxide (MgO)	1309-48-4		4.7799	mg
			Supplier	Calcium Oxide (CaO)	60873-85-0		4.0629	mg
			Supplier	Silica Amorphous (SiO2)	7631-86-9		22.3062	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		687.1107	mg
			B	Nickel (Ni)	7440-02-0		3.2663	mg
			Supplier	Gold (Au)	7440-57-5		1.9916	mg
			Supplier	Chromium Trioxide (Cr2O3)	1308-38-9		30.5914	mg
Die	72.31	mg	Supplier	Misc.	n/a		0.2748	mg
			Supplier	Silicon (Si)	7440-21-3		71.3194	mg
			Supplier	Aluminum (Al)	7429-90-5		0.7159	mg
Die Attach	36.94	mg	Supplier	Epoxy resins	129915-35-1		11.4034	mg
			Supplier	Polybutadiene polymer	n/a		1.5921	mg
			Supplier	Fused Silica (SiO2)	60676-86-0		13.4499	mg
			Supplier	Acrylic resins	n/a		10.4947	mg
Imaging Lens	222.79	mg	Supplier	Titanium Dioxide (TiO2)	13463-67-7		11.6965	mg
			Supplier	Sodium Monoxide (Na2O)	1313-59-3		11.3623	mg
			Supplier	Boron Trioxide (B2O3)	1303-86-2		11.6965	mg
			Supplier	Zinc Monoxide (ZnO)	1314-13-2		11.4291	mg
			B	Antimony Trioxide (Sb2O3)	1309-64-4		1.1139	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		11.2509	mg
			Supplier	Potassium Monoxide (K2O)	12136-45-7		11.2732	mg
			Supplier	Silica Crystalline (SiO2)	14808-60-7		152.9676	mg
Lid Attach	8.5	mg	Supplier	Other Additive Agents	n/a		1.4807	mg
			Supplier	Photoinitiator	n/a		0.3468	mg
			Supplier	Epoxy Prepolymer	n/a		6.6725	mg
Marking Ink	0.08	mg	Supplier	Bisphenol A_Epichlorohydrin polymer	25068-38-6		0.0711	mg
			Supplier	1-Methoxy-2-propyl acetate (MPA)	108-65-6		0.0038	mg
			Supplier	Cyclohexanone	108-94-1		0.004	mg
			Supplier	Xylene	1330-20-7		0.0011	mg

Wire Bond - Au	2.84	mg	Supplier	Gold (Au)	7440-57-5		2.84	mg
----------------	------	----	----------	-----------	-----------	--	------	----