



**Material Composition Declaration**  
 © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

1752-21.1	IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information
-----------	--	---------------------------	---

**Supplier Information**

<b>Company name*</b> On Semiconductor	Company unique ID	Unique ID Authority	<b>Response Date*</b> 2019-12-14
<b>Contact Name</b> Product-Env-Stewards	Title - Contact Product Enviro Compliance	<b>Phone - Contact*</b> NA	<b>Email - Contact*</b> Product-Env-Stewards@onsemi.com
<b>Authorized Representative*</b> Product-Env-Stewards	Title - Representative Product Enviro Compliance	<b>Phone - Representative*</b> NA	<b>Email - Representative*</b> Product-Env-Stewards@onsemi.com

Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
	NOIV1SN5000A-QDC	VITA5000 MONO ML LLC68	2019-12-14		THA	4310.68	mg	Each

**Manufacturing Process Information**

Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating	Peak Process Body Temperature	Max Time at Peak Temperature	Number of Reflow Cycles
Precious metal (e.g. Ag,Au, NiPdAu) (no Sn)	CU Alloy	3	260 C	30 seconds	3

Comments  
**ATTENTION: MSL 3 Rated item requires Bake and Dry Pack (after electrical test)**  
**For more information regarding material composition please refer to page 3**

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a "RoHS restricted substance") in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
<b>RoHS Declaration *</b>	1 - Item(s) does not contain RoHS restricted substances per the definition above		<b>Supplier Acceptance *</b> Accepted
<b>Exemption: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.</b>			
Exemption List Version	EL-2006/690/EC		
<b>Declaration Signature</b>			
<b>Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.</b>			
Supplier Digital Signature	Jozef Vavro		

**Homogeneous Material Composition Declaration for Electronic Products**

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Ceramic Substrate	3182.9	mg	Supplier	Cobalt (Co)	7440-48-4		0.9549	mg
			Supplier	Tungsten (W)	7440-33-7		49.6532	mg
			Supplier	Magnesium Monoxide (MgO)	1309-48-4		35.0119	mg
			Supplier	Silica Amorphous (SiO2)	7631-86-9		111.4015	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		2858.8806	mg
			B	Nickel (Ni)	7440-02-0		0.9549	mg
			Supplier	Gold (Au)	7440-57-5		1.9097	mg
			Supplier	Chromium Trioxide (Cr2O3)	1308-38-9		124.1331	mg
Die	350.69	mg	Supplier	Silicon (Si)	7440-21-3		350.69	mg
Die Attach	1.85	mg	Supplier	Epoxized Condensate Of Para-Hydrobenzaldehyde And Alkyl Phenol	129915-35-1		0.2775	mg
			Supplier	Silver (Ag)	7440-22-4		1.5725	mg
Glass Attach Epoxy	10.8	mg	Supplier	Bisphenol A_Epichlorohydrin polymer	25068-38-6		4.4852	mg
			Supplier	4,4'-Diaminodiphenyl Sulfone (DDS-4,4')	80-08-0		1.7064	mg
			Supplier	Filler (SiO2?C2H6Cl2Si)	68611-44-9		4.2595	mg
			Supplier	Carbon Black (C)	1333-86-4		0.2905	mg
			Supplier	Additive	1760-24-3, 2530-83-8		0.0583	mg
Glass Lid /Cap	762.4	mg	Supplier	Boron Trioxide (B2O3)	1303-86-2		64.0416	mg
			Supplier	Silica Amorphous (SiO2)	7631-86-9		456.8301	mg
			Supplier	Barium Monoxide (BaO)	1304-28-5		60.3821	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		60.3821	mg
			Supplier	Calcium Monoxide (CaO)	1305-78-8		120.7642	mg
Wire Bond - Al	2.04	mg	Supplier	Aluminum (Al)	7429-90-5		2.04	mg