



Product Overview

AR0230CS: 2 MP 1/3" CMOS Image Sensor

For complete documentation, see the [data sheet](#)

Product Description

The AR0230CS is a 1/2.7-inch CMOS digital image sensor with an active-pixel array of 1928Hx1088V. It captures images in either linear or high dynamic range modes, with rolling-shutter readout. It includes sophisticated camera functions such as in-pixel binning, windowing and both video and single frame modes. It is designed for both low light and high dynamic range scene performance. It is programmable through a simple two wire serial interface. The AR0230CS produces extraordinarily clear, sharp digital pictures, and its ability to capture both continuous video and single frames makes it the perfect choice for a wide range of applications, including surveillance and HD video.

Features

- High Dynamic Range

Applications

- Security

Part Electrical Specifications

Product	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Color	Package Type
AR0230CSSC00SUEA 0-DRBR	Pb-free Halide free	NEW	CMOS	2.1	60	1/2.7 inch	Electronic Rolling and Global Reset Release	3.0 x 3.0	RGB	IBGA-80
AR0230CSSC00SUEA 0-DRBR-E	Pb-free Halide free	NEW	CMOS	2.1	60	1/2.7 inch	Electronic Rolling and Global Reset Release	3.0 x 3.0	RGB	IBGA-80

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015