



Product Overview

AR0141CS: 1.0 MP 1/4" CMOS Image Sensor

For complete documentation, see the [data sheet](#)

Product Description

ON Semiconductor's AR0141CS is a 1/4-inch CMOS digital imagesensor with an active-pixel array of 1280Hx800V. It includes sophisticated camera functions such as in-pixel binning, windowing and both video and single frame modes. It is programmable through a simple two-wire serial interface. The AR0141CS produces extraordinarily clear, sharp digital pictures, and its ability to capture both continuous video and single frames makes it the perfect choice for a wide range of applications, including surveillance and HD video.

Applications

- Security
- Scanning

Part Electrical Specifications

Product	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Color	Package Type
AR0141CS2C00SUEA 0-DP	Pb-free Halide free	NEW	CMOS	1	60	1/4 inch	Electronic Rolling	3.0 x 3.0	RGB	IBGA-63
AR0141CS2C00SUEA 0-DR	Pb-free Halide free	NEW	CMOS	1	60	1/4 inch	Electronic Rolling	3.0 x 3.0	RGB	IBGA-63
AR0141CS2M00SUEA 0-DR-E	Pb-free Halide free	NEW	CMOS	1	60	1/4 inch	Electronic Rolling	3.0 x 3.0	Mono	IBGA-63

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015