

Product Overview

BD138: 1.5 A, 60 V PNP Bipolar Power Transistor

For complete documentation, see the data sheet.

This series of plastic, medium-power PNP transistors are designed for use as audio amplifiers and drivers utilizing complementary or quasi complementary circuits.

Features

- DC Current Gain - $h_{FE} = 40$ (Min) @ $I_C = 0.15$ Adc
- BD 136, 138, 140 are complementary with BD 135, 137, 139
- Pb-Free Package is Available*

Part Electrical Specifications

Product	Compliance	Status	Polarity	Type	$V_{CE(sat)}$ Max (V)	I_C Cont. (A)	V_{CEO} Min (V)	V_{CBO} (V)	V_{EBO} (V)	$V_{BE(sat)}$ (V)	$V_{BE(on)}$ (V)	h_{FE} Min	h_{FE} Max	f_T Min (MHz)	P_{TM} Max (W)	Package Type
BD13810STU	Pb-free	Active	PNP	General Purpose	0.5	1.5	60	60	5	-	1	40	250	-	12.5	TO-126-3
BD13816STU	Pb-free	Active	PNP	General Purpose	0.5	1.5	60	60	5	-	1	40	250	-	12.5	TO-126-3
BD138G	Pb-free Halide free	Active	PNP	General Purpose	0.5	1.5	60	60	5	-	1	40	250	-	12.5	TO-225-3

For more information please contact your local sales support at www.onsemi.com.

Created on: 2/17/2019