

Product Overview

CAV24C64: EEPROM Serial 64-Kb I²C - Automotive Grade

For complete documentation, see the data sheet.

The CAV24C64 is a EEPROM Serial 64-Kb I²C devices, internally organized as 8192 words of 8 bits each.

It features a 32-byte page write buffer and supports the Standard (100 kHz) and Fast (400 kHz) I²C protocol.

External address pins make it possible to address up to eight CAV24C64 devices on the same bus.

Features

- Automotive Temperature Grade 1 (-40°C to +125°C)
 - 2.5 V to 5.5 V Supply Voltage Range
 - This Device is Pb-Free, Halogen Free/BFR Free, and RoHS Compliant
 - Supports Standard and Fast I²C Protocol
 - 32-Byte Page Write Buffer
 - Hardware Write Protection for Entire Memory
 - CAV Prefix for Automotive and Other Applications Requiring Site and Change Control
 - Schmitt Triggers and Noise Suppression Filters on I²C Bus Inputs(SCL and SDA)
 - Low Power CMOS Technology
 - 1,000,000 Program/Erase Cycles
- For more features, see the data sheet

Benefits

- Allows the use in safety critical application.
- Single power supply from 2.5V to 5.5V. Functional over the entire temperature range.
- Space-Efficient Packaging

Applications

- Immobilizer unit
- Seat control unit
- Wiper module
- Fan control unit
- Park assist unit

Part Electrical Specifications

Product	Compliance	Status	Type	Density	Organization	Data Transmission Standard	f _{cycle} Max (kHz)	t _{acc} Max ns	V _{cc} Min (V)	V _{cc} Max (V)	I _{standby} Max (μA)	I _{act} Max (mA)	T Min (°C)	T Max (°C)	Package Type
CAV24C64C4CTR	AEC Qualified PPAP Capable Pb-free Halide free	Active	Serial	64 kb	8k x 8	I2C	400	900	2.5	5.5	5	2	-40	125	WLCS P-4
CAV24C64WE-GT3	AEC Qualified PPAP Capable Pb-free Halide free	Active	Serial	64 kb	8k x 8	I2C	400	900	2.5	5.5	5	2	-40	125	SOIC-8
CAV24C64YE-GT3	AEC Qualified PPAP Capable Pb-free Halide free	Active	Serial	64 kb	8k x 8	I2C	400	900	2.5	5.5	5	2	-40	125	TSSOP-8

For more information please contact your local sales support at www.onsemi.com.

Created on: 2/17/2019