



Product Overview

KAF-3200: Full Frame CCD, Image Sensor, 3.3 MP

For complete documentation, see the [data sheet](#)

Product Description

The KAF-3200 Image Sensor is a high performance CCD (charge-coupled device) with 2184H x 1472V photoactive pixels designed for a wide range of image sensing applications.

The sensor incorporates true two-phase CCD technology, simplifying the support circuits required to drive the sensor as well as reducing dark current without compromising charge capacity. The sensor also utilizes the TRUESENSE Transparent Gate Electrode to improve sensitivity compared to the use of a standard front side illuminated polysilicon electrode.

Features

- True Two Phase Full Frame Architecture
- TRUESENSE Transparent Gate Electrode for high sensitivity
- 100% Fill Factor
- Low Dark Current
- Microlens option
- High Output Sensitivity

Applications

- Medical
- Scientific

Part Electrical Specifications

Product	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (μm)	Color	Package Type
KAF-3200-ABA-CD-AE	Pb-free Halide free	Active	Full Frame CCD	3.3	2.5	4/3 inch		6.8 x 6.8	Mono	CDIP-24
KAF-3200-ABA-CD-B2	Pb-free Halide free	Active	Full Frame CCD	3.3	2.5	4/3 inch		6.8 x 6.8	Mono	CDIP-24
KAF-3200-ABA-CP-AE	Pb-free Halide free	Active	Full Frame CCD	3.3	2.5	4/3 inch		6.8 x 6.8	Mono	CDIP-24
KAF-3200-ABA-CP-B2	Pb-free Halide free	Active	Full Frame CCD	3.3	2.5	4/3 inch		6.8 x 6.8	Mono	CDIP-24

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015