

## Product Overview

### LM2904\_XFCS: LM2904\_XFCS

For complete documentation, see the data sheet.

LM2904\_XFCS

#### Part Electrical Specifications

Product	Compliance	Status	Rail to Rail	Channels	V <sub>S</sub> Min (V)	V <sub>S</sub> Max (V)	I <sub>Q</sub> Typ (mA)	V <sub>OS</sub> Max (mV)	GBW Typ (MHz)	SR Typ (V/μs)	I <sub>O</sub> Typ (mA)	ΔV <sub>OS</sub> /ΔT (μV/C)	e <sub>N</sub> (nV/√Hz)	I <sub>bias</sub> Typ (pA)	CMRR Typ (dB)	Architecture	Temperature Range (°C)	Package Type
LM2904MX	Pb-free	Active	No	2	3	32	0.75	7	1	0.6	40	7	-	-45000	70	Bipolar	-40 to 105	SOIC-8
LM2904N	Pb-free	Active	No	2	3	32	0.75	7	1	0.6	40	7	-	-45000	70	Bipolar	-40 to 105	PDIP-8

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 12/17/2018