

Product Overview

LV88561JA: Motor Driver, Single-Phase, PWM, Full-Wave, BLDC for 24V/48V fan

For complete documentation, see the data sheet.

The LV88561JA/R is the pre-driver for a single-phase 24 V/48 V BLDC motor, which has the closed loop controller for motor rotation speed. This is available to control a motor with low vibration and the low noise. In addition, lead-angle adjustment is possible by external pins. Lead-angle value and lead-angle slant can be adjusted independently. Thus, the device can be driven by high efficiency and low noise with various motors. Motor speed setting curve is adjustable for many variety using external resistor only. As a method of the rotary speed control of the motor, direct-PWM pulse input is adopted.

Features

- Single-phase full wave drive pre-driver include closed loop speed control
- Speed control function by PWM duty input (25 Hz to 100 kHz)
- Soft start-up function and PWM soft switching phase transition
- Soft PWM duty cycle transitions
- Built-in current limit circuit and thermal protection circuit
- Built-in locked rotor protection and auto recovery circuit
- FG signal output
- Dynamic lead angle adjustment with respect to rotational

Benefits

- high accuracy for motor speed control
- wide operation range
- low noise and silent drive
- low noise and silent drive
- safety
- safety
- easy to motor control
- high efficiency

Applications

- Motor Drive Unit

End Products

- Server cooling fan
- Telecom cooling fan

For more information please contact your local sales support at www.onsemi.com.

Created on: 1/21/2019