

Product Overview

MC10H124: Quad TTL to ECL Translator

For complete documentation, see the data sheet.

The MC10H124 is a quad translator for interfacing data and control signals between a saturated logic section and the MECL section of digital systems. The 10H part is a functional/pinout duplication of the standard MECL 10K family part, with 100% improvement in propagation delay, and no increase in power-supply current.

Features

- Propagation Delay, 1.5 ns Typical
- Improved Noise Margin 150 mV (Over Operating Voltage and Temperature Range)
- Voltage Compensated
- MECL 10K Compatible
- Pb-Free Packages are Available

Part Electrical Specifications

Product	Compliance	Status	Channels	Input Level	Output Level	V _{CC} Typ (V)	f _{Max} Typ (MHz)	t _{pd} Typ (ns)	t _r & t _f Max (ps)	Package Type
MC10H124FNG	Pb-free Halide free	Active	4	TTL	ECL	5	50	1.6	1500	PLLC-20
MC10H124FNR2G	Pb-free Halide free	Active	4	TTL	ECL	5	50	1.6	1500	PLLC-20
MC10H124PG	Pb-free Halide free	Active	4	TTL	ECL	5	50	1.6	1500	PDIP-16

For more information please contact your local sales support at www.onsemi.com.

Created on: 12/14/2018