



Product Overview

MT9M024: 1.2 MP 1/3" CMOS Image Sensor

For complete documentation, see the [data sheet](#)

Product Description

ON Semiconductor's focus on excellent pixel performance provides the foundation for this sensor's exceptional image quality with superior color accuracy, low light sensitivity and low noise level. This cost-effective imaging solution enables high speed image capture capabilities and includes variable functions, including gain, frame rate, and exposure while maintaining low power consumption.

Applications

- Security

Part Electrical Specifications

Product	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Color	Package Type
MT9M024IA3XTC-DPBR	AEC Qualified PPAP Capable Pb-free Halide free	NEW	CMOS	1.2	60	1/3 inch	Electronic Rolling	3.75 x 3.75	RGB	IBGA-63
MT9M024IA3XTC-DRBR	AEC Qualified PPAP Capable Pb-free Halide free	NEW	CMOS	1.2	60	1/3 inch	Electronic Rolling	3.75 x 3.75	RGB	IBGA-63
MT9M024IA3XTM-DPBR	AEC Qualified PPAP Capable Pb-free Halide free	NEW	CMOS	1.2	60	1/3 inch	Electronic Rolling	3.75 x 3.75	Mono	IBGA-63
MT9M024IA3XTM-DRBR	AEC Qualified PPAP Capable Pb-free Halide free	NEW	CMOS	1.2	60	1/3 inch	Electronic Rolling	3.75 x 3.75	Mono	IBGA-63

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015