



Product Overview

MMBT2907AW: PNP Bipolar Transistor

For complete documentation, see the data sheet

Product Description

The PNP Bipolar Transistor is designed for general purpose amplifier applications. It is housed in the SOT-323/SC-70 package which is designed for low power surface mount applications.

Features

- Miniature SC-70/SOT-323 Surface Mount Package Saves Board Space
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant
- NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AECQ101 Qualified and PPAP Capable

Part Electrical Specifications

Product	Compliance	Status	Polarity	I _C Continuous (A)	V _{(BR)CEO} Min (V)	h _{FE} Min	h _{FE} Max	f _T Min (MHz)	P _{TM} Max (W)	Package Type
MMBT2907AWT1G	AEC Qualified Pb-free Halide free	Active	PNP	0.6	60	100	-	200	0.15	SC-70-3 / SOT-323-3
NSVMMBT2907AWT1G	AEC Qualified PPAP Capable Pb-free Halide free	Active	PNP	0.6	60	100	-	200	0.15	SC-70-3 / SOT-323-3

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015