

## Product Overview

### MUR1620CT: Power Rectifier, Ultra-Fast Recovery, Common Cathode, 16 A, 200 V

For complete documentation, see the data sheet.

The Ultrafast Rectifier is designed for use in switching power supplies, inverters and as free wheeling diodes.

#### Features

- Ultrafast 35 and 60 Nanosecond Recovery Times
- 175 C Operating Junction Temperature
- Popular TO-220 Package
- Epoxy Meets UL94, V<sub>0</sub> @ 1/8"
- High Temperature Glass Passivated Junction
- High Voltage Capability to 600 Volts
- Low Leakage Specified @ 150 C Case Temperature
- Current Derating @ Both Case and Ambient Temperatures

Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 1.9 grams (approximately)

For more features, see the data sheet

#### Part Electrical Specifications

Product	Compliance	Status	Type	I <sub>O(rec)</sub> Max (A)	t <sub>rr</sub> Max (ns)	V <sub>RRM</sub> Max (V)	V <sub>FM</sub> Max (V)	I <sub>FSM</sub> Max (A)	I <sub>R</sub> Max (mA)	Package Type
MUR1620CTG	Pb-free	Active	Ultrafast	16	35	200	0.975	100	0.005	TO-220-3

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 2/21/2019