



Product Overview

MT9P031: 5 MP 1/3" CMOS Image Sensor

For complete documentation, see the [data sheet](#)

Product Description

ON Semiconductor's focus on pixel performance excellence provides the foundation for this sensor's exceptional image quality with superior color accuracy, low-light sensitivity, and low noise level. This cost-effective CMOS imaging solution enables high speed image capture capabilities, and includes variable functions, including gain, frame rate, and exposure while maintaining low power consumption.

Applications

- Security

Part Electrical Specifications

Product	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Color	Package Type
MT9P031I12STC-DP	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48
MT9P031I12STC-DR	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48
MT9P031I12STC-DR1	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48
MT9P031I12STC-TP	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48
MT9P031I12STM-DP	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48
MT9P031I12STM-DP1	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48
MT9P031I12STM-DR	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48
MT9P031I12STM-DR1	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48
MT9P031I12STM-TP	Pb-free Halide free	NEW	CMOS	5	15	1/2.5 inch	Electronic Rolling	2.2 x 2.2	RGB	ILCC-48

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015