



Product Overview

MT9V034: VGA 1/3" GS CMOS Image Sensor

For complete documentation, see the [data sheet](#)

Product Description

ON Semiconductor's focus on pixel performance excellence provides the foundation for this sensor's exceptional image quality with superior color accuracy, low-light sensitivity, and low noise level. This cost-effective CMOS imaging solution enables high speed image capture capabilities, and includes variable functions, including gain, frame rate, and exposure while maintaining low power consumption.

Part Electrical Specifications

Product	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Color	Package Type
MT9V034C12STC-DP	Pb-free Halide free	NEW	CMOS	WVGA	60	1/3 inch	Global Shutter	6.0 x 6.0	RGB	CLCC-48
MT9V034C12STC-DR	Pb-free Halide free	NEW	CMOS	WVGA	60	1/3 inch	Global Shutter	6.0 x 6.0	RGB	CLCC-48
MT9V034C12STM-DP	Pb-free Halide free	NEW	CMOS	WVGA	60	1/3 inch	Global Shutter	6.0 x 6.0	Mono	CLCC-48
MT9V034C12STM-DR	Pb-free Halide free	NEW	CMOS	WVGA	60	1/3 inch	Global Shutter	6.0 x 6.0	Mono	CLCC-48
MT9V034C12STM-DR1	Pb-free Halide free	NEW	CMOS	WVGA	60	1/3 inch	Global Shutter	6.0 x 6.0	Mono	CLCC-48
MT9V034C12STM-TP	Pb-free Halide free	NEW	CMOS	WVGA	60	1/3 inch	Global Shutter	6.0 x 6.0	Mono	CLCC-48
MT9V034C12STM-TR	Pb-free Halide free	NEW	CMOS	WVGA	60	1/3 inch	Global Shutter	6.0 x 6.0	Mono	CLCC-48

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015