

Product Overview

NCL30086: AC-DC Power Factor Corrected Quasi-Resonant Primary Side Current Mode Controller for LED Lighting with Smart Analog/Dimming Capability

For complete documentation, see the data sheet.

The NCL30086 is an AC-DC power factor corrected flyback controller targeting isolated and non-isolated “Smart-dimmable” constant current LED drivers. The controller operates in a quasi-resonant mode to provide optimal efficiency. The current control algorithm supports flyback, buck-boost, and SEPIC topologies. Thanks to a novel control method, the device is able to tightly regulate a constant LED current from the primary side. This removes the need for secondary side feedback circuitry, biasing and an optocoupler.

The device is highly integrated with a minimum number of external components. A robust suite of safety protection is built in to simplify the design. This device is specifically intended for very compact space efficient designs and supports analog and PWM dimming with a dedicated dimming input intended to control the average LED current. To ensure reliable operation at elevated temperatures, a user configurable current foldback circuit is also provided. The NCL30086 is housed in the SOIC10 which has the same body size as a standard SOIC8.

Features

- Constant Current Control with Primary Side Feedback
- Power factor correction with low harmonic distortion
- Precise Current Regulation Accuracy
- Line feedforward for enhanced regulation accuracy
- Wide Vcc operating range
- User Programmable Thermal Foldback
- Open and Shorted LED/Output Diode Protection
- Wide temperature range of -40 to 125 °C
- Dedicated Analog/Digital Dimming control
- VCC Undervoltage and overvoltage protection

For more features, see the data sheet

Benefits

- No Optocoupler or secondary control circuitry required
- Exceeds industry needs for lighting
- No need for binning of LEDs or production trimming
- Improve regulation across line variation
- Supports wide range of LED forward voltages
- Protects LED driver from overheating under severe conditions
- Enhanced fault handling
- Supports outdoor and high temperature environments
- Enables smart lighting applications

Applications

- Integrated LED Drive Electronics
- LED Driver
- Open Frame LED Driver

End Products

- LED Bulbs and Tubes
- LED Light Engines
- Electronic Control Gear for LED Systems
- LED Driver Power Supplies and Adapters

Part Electrical Specifications

Product	Compliance	Status	Topology	V _I Min (V)	V _I Max (V)	V _O Max (V)	I _O Max (mA)	f _{sw} Typ (kHz)	Package Type
NCL30086BDR2G	Pb-free Halide free	Active	Step-Up/Step-Down Flyback	9.4	26	200	3000	Up to 150	SOIC-10 NB

For more information please contact your local sales support at www.onsemi.com.

Created on: 7/22/2019