

Product Overview

NGTB40N120IHR: IGBT, 1200V 40A FS2-RC Induction Heating

For complete documentation, see the data sheet.

This Insulated Gate Bipolar Transistor (IGBT) features a robust and cost effective Field Stop (FS) Trench construction, and provides superior performance in demanding switching applications, offering both low on-state voltage and minimal switching loss. The IGBT is well suited for resonant or soft switching applications.

Features

- Optimized for Low Case Temperature in IH Cooker Applications
- Extremely Efficient Trench with Fieldstop Technology
- Reliable and Cost Effective Single Die Solution
- Consumer Appliances
- Soft Switching

Benefits

- Low Switching Loss Reduces System Power Dissipation

Applications

- Inductive Heating

Part Electrical Specifications

Product	Compliance	Status	$V_{ES}^{(BR)C}$ Typ (V)	I_C Max (A)	$V_{CE(sat)}$ Typ (V)	V_F Typ (V)	E_{off} Typ (mJ)	E_{on} Typ (mJ)	T_{rr} Typ (ns)	I_{rr} Typ (A)	Gate Charge Typ (nC)	Short Circuit Withstand (μ s)	E_{AS} Typ (mJ)	P_D Max (W)	Co- Pack aged Diode	Pack age Type
NGTB40N120IHRWG	Pb-free Halide free	Active	1200	40	2.3	2.1	0.95	-	-	-	225	-	-	384	Yes	TO-247-3

For more information please contact your local sales support at www.onsemi.com.

Created on: 2/21/2019