

Product Overview

NCP1090: Controller, PoE-PD Interface, Integrated

For complete documentation, see the data sheet.



The NCP1090, NCP1091 and NCP1092 are members of ON Semiconductor's high power HIPO™ Power over Ethernet Powered Device (PoE-PD) product family and integrate an IEEE 802.3af PoE-PD interface controller.

Features

- Fully supports IEEE 802.3af specifications
- 500 mA operational current limit
- Industrial temperature range -40°C to 85°C with full operation up to 125°C junction temperature
- Vertical N-Channel DMOS pass switch offers the robustness of discrete MOSFETs

Benefits

- Broad compatibility with power sourcing equipment
- Headroom above the IEEE 802.3af power limitation
- Extended operational range
- More durable than most integrated products

Applications

- Wireless access points
- Voice over IP products
- IP camera

End Products

- WiMax
- WiFi
- Motor control

Part Electrical Specifications

Product	Compliance	Status	Topology	Phases	Control Mode	V _{CC} Min (V)	V _{CC} Max (V)	f _{sw} Typ (kHz)	Package Type
NCP1090DBRG	Pb-free	Active				36	57		TSSOP-8
	Halide free								
NCP1090DG	Pb-free	Active				36	57		SOIC-8
	Halide free								
NCP1090DRG	Pb-free	Active				36	57		SOIC-8
	Halide free								

For more information please contact your local sales support at www.onsemi.com.

Created on: 2/23/2019