

Product Overview

NL7SZ97: Flexible Choice Logic (9 Configurable Functions)

For complete documentation, see the data sheet.

The NL7SZ97 is an advanced high-speed CMOS multifunction gate. The device allows the user to choose logic functions MUX, AND, OR, NAND, NOR, INVERT and BUFFER. The device has Schmitt-trigger inputs, thereby enhancing noise immunity. The NL7SZ97 input and output structures provide protection when voltages up to 7.0 V are applied, irregardless of the supply voltage.

Features

- High Speed: $t_{PD} = 3.3 \text{ ns (Typ) @ } V_{CC} = 5.0 \text{ V}$
- Low Power Dissipation: $I_{CC} = 1 \text{ A (Maximum) at } T_A = 25\text{C}$
- Power Down Protection Provided on inputs
- Balanced Propagation Delays
- Overvoltage Tolerant (OVT) Input and Output Pins
- Ultra-Small Package
- This is a Pb-Free Device

Applications

- General Purpose Logic

End Products

- Handheld: PDA, Digital Cameras, GPS

Part Electrical Specifications

Product	Compliance	Status	Type	Channels	V_{CC} Min (V)	V_{CC} Max (V)	t_{pd} Max (ns)	I_O Max (mA)	Package Type
NL7SZ97DFT2G	Pb-free	Active	SmartGate	1	1.65	5.5	null	null	SC-88-6 / SC-70-6 / SOT-363-6
	Halide free								
NLV7SZ97DFT2G	AEC Qualified PPAP Capable Pb-free Halide free	Active	SmartGate	1	1.65	5.5	2.5	null	SC-88-6 / SC-70-6 / SOT-363-6

For more information please contact your local sales support at www.onsemi.com.

Created on: 1/16/2019