

Product Overview

NLU1G32: Single 2-Input OR Gate

For complete documentation, see the data sheet.

The NLU1G32 MiniGate™ is an advanced high speed CMOS 2 input OR gate in ultra small footprint. The NLU1G32 input and output structures provide protection when voltages up to 7.0 volts are applied, regardless of the supply voltage.

Features

- High Speed: $t_{PD} = 3.7$ ns (Typ) at $V_{CC} = 5.0$ V
- Low Power Dissipation: $I_{CC} = 1$ μ A (Max) at $T_A = 25^\circ$ C
- Power Down Protection Provided on inputs
- Power Down Protection Provided on outputs
- Overvoltage Tolerant (OVT) Input and Output Pins
- Ultra Small Pb Free Package

Applications

- ASIC Fixes Simplified PCB Routing Glue Logic System Integration Voltage Translation

Part Electrical Specifications

Product	Compliance	Status	Type	Channels	V_{CC} Min (V)	V_{CC} Max (V)	t_{pd} Max (ns)	I_o Max (mA)	Package Type
NLU1G32AMUTCG	Pb-free Halide free	Active	OR	1	1.65	5.5	null	null	UDFN-6
NLU1G32CMUTCG	Pb-free Halide free	Active	OR	1	1.65	5.5	null	null	UDFN-6
NLU1G32MUTCG	Pb-free Halide free	Active	OR	1	1.65	5.5	null	null	UDFN-6

For more information please contact your local sales support at www.onsemi.com.

Created on: 1/23/2019