



Product Overview

NVTFS4823N: Power MOSFET 30V, 30A, 10.5 mOhm, Single N-Channel, u8FL, Logic Level.

For complete documentation, see the data sheet

Product Description

Automotive Power MOSFET in a 3x3mm flat lead package designed for compact and efficient designs and including high thermal performance. Wettable Flank Option available for Enhanced Optical Inspection. AEC-Q101 Qualified MOSFET and PPAP capable suitable for automotive applications.

Features	Benefits
<ul style="list-style-type: none"> Low on resistance Low Qg 100% avalanche tested AEC-Q101 qualified 	<ul style="list-style-type: none"> Minimal conduction losses Minimal switching losses Safeguards against voltage overstress failures Suitable for automotive applications

Applications	End Products
<ul style="list-style-type: none"> Power Supply DC-DC switcher output drivers 	<ul style="list-style-type: none"> Automotive infotainment systems

Part Electrical Specifications

Product	Compliance	Status	Channel Polarity	Configuration	V _{DS} (BR) Min (V)	V _{DS} Max (V)	V _{GS} (th) Max (V)	I _D Max (A)	P _D Max (W)	r _{DS(on)} Max @ V _{GS} = 2.5 V (m)	r _{DS(on)} Max @ V _{GS} = 4.5 V (m)	r _{DS(on)} Max @ V _{GS} = 10 V (m)	Q _g Typ @ V _{GS} = 4.5 V (nC)	Q _g Typ @ V _{GS} = 10 V (nC)	Q _{gd} Typ @ V _{GS} = 4.5 V (nC)	Q _{rr} Typ (nC)	C _{iss} Typ (pF)	C _{oss} Typ (pF)	C _{rss} Typ (pF)	Package Type
NVTFS4823NTAG	AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	30	20	2.5	30	21		17.5	10.5	6	12	2.4	5	750	175	100	u8FL / WD FN-8
NVTFS4823NTWG	AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	30	20	2.5	30	21		17.5	10.5	6	12	2.4	5	750	175	100	u8FL / WD FN-8
NVTFS4823NWFTAG	AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	30	20	2.5	30	21		17.5	10.5	6	12	2.4	5	750	175	100	u8FL / WD FN-8
NVTFS4823NWFTWG	AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	30	20	2.5	30	21		17.5	10.5	6	12	2.4	5	750	175	100	u8FL / WD FN-8

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015