



Product Overview

PYTHON500: CMOS Image Sensor, Global Shutter, 0.5 MP (SVGA)

For complete documentation, see the data sheet

Product Description

The PYTHON 500 is a 1/3 inch SVGA CMOS image sensor with a pixel array of 800 by 600 pixels.

The high sensitivity 4.8 μm x 4.8 μm pixels support low noise “pipelined” and “triggered” global shutter readout modes. Furthermore the correlated double sampling (CDS) support in global shutter mode results in reduced noise and increased dynamic range.

The sensor has on-chip programmable gain amplifiers and 10-bit A/D converters. The integration time and gain parameters can be reconfigured without any visible image artifact. Optionally the on-chip automatic exposure control loop (AEC) controls these parameters dynamically. The image's black level is either calibrated automatically or can be adjusted by adding a user programmable offset.

A high level of programmability using a four wire serial peripheral interface enables the user to read out specific regions of interest. Up to 8 regions can be programmed, achieving even higher frame rates. The sensor has 4 LVDS lanes, facilitating frame rates up to 560 frames per second in Zero ROT mode. Each channel runs at 720 Mbps. A separate synchronization channel containing payload information is provided to facilitate the image reconstruction at the receiving end.

The PYTHON 500 is packaged in a 48-pin LCC package and is available in a monochrome and color version.

Contact your local ON Semiconductor office for more information.

Features

- IP-CDS global shutter technology
- True HW scalable family concept
- High configurability
- Fast adaptability
- Multiple windowing
- High dynamic range
- Higher frame rates

Benefits

- Enables global shutter imaging with single digit noise performance
- Easily adopt multiple resolutions (5 resolutions with single PCB)
- High flexibility to optimize sensor for customer application
- Fast switching between operating modes
- Speed increase from windowing in x- and y- direction
- Capturing high dynamic scenes with no loss to image quality
- Faster image capturing capabilities

Applications

- Machine Vision
- Motion Monitoring
- Security
- Barcode scanning
- Traffic Surveillance (ITS)

End Products

- Industrial cameras and systems
- Medical imaging systems
- Barcode readers
- Inspection systems (food, bottles, recycling labels)

Part Electrical Specifications

Product	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (μm)	Color	Package Type
NOIP1SE0500A-QDI	Pb-free	Active	CMOS	0.5	560	1/3 inch	Global	4.8 x 4.8	Color	LCC-48
	Halide free									
NOIP1SN0500A-QDI	Pb-free	Active	CMOS	0.5	560	1/3 inch	Global	4.8 x 4.8	Mono	LCC-48
	Halide free									

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015