

## Product Overview

### NCV8716: LDO Regulator, 80 mA, Ultra-Low Iq

For complete documentation, see the data sheet.

The NCV8716 is 80 mA LDO Linear Voltage Regulator. It is a very stable and accurate device with ultra-low ground current consumption (4.7  $\mu$ A over the full output load range) and a wide input voltage range (up to 24 V). The regulator incorporates several protection features such as Thermal Shutdown and Current Limiting.

#### Similar Products:

	<a href="#">NCV8715</a>	<a href="#">NCV8716</a>	<a href="#">NCV8718</a>
Output Current (A)	0.05	0.08	0.30
PSRR f=1 kHz (dB)	50	50	60
Dropout Voltage (V)	0.230	0.310	0.285

#### Features

- Wide Input Voltage Range from 2.5 V up to 24 V
- Ultra-Low Quiescent Current: 3.2  $\mu$ A Typical
- Fixed Output Voltage Options: from 1.2 V to 5.0 V
- PSRR 60 dB at 100 kHz
- Available in WDFN8 2 x 2 mm package

#### Benefits

- Compatible with most battery sources and DC output voltage adapters
- Helps to reduce the current consumption
- Very-well suited to power low supply voltage microcontrollers and sensors
- Provides very good input to output isolation
- Offers very small overall solution size

#### Applications

- Safety Systems
- Communication Systems
- Infotainment, Audio

## Part Electrical Specifications

Product	Compliance	Status	Output	Polarity	V <sub>O</sub> (V)	I <sub>O</sub> Typ (A)	V <sub>I</sub> Min (V)	V <sub>I</sub> Max (V)	V <sub>DO</sub> Typ (V)	I <sub>q</sub> Typ (mA)	PSRR (dB)	Noise (μV <sub>rms</sub> )	Enable	Power Good	Package Type
NCV8716MT15TBG	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	Positive	1.5	0.08	2.5	24		0.0034	56	120	No	No	WDFN -6
NCV8716MT18TBG	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	Positive	1.8	0.08	2.5	24		0.0034	60	140	No	No	WDFN -6
NCV8716MT25TBG	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	Positive	2.5	0.08	2.5	24	0.4	0.0034	60	160	No	No	WDFN -6
NCV8716MT28TBG	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	Positive	2.8	0.08	2.5	24	0.38	0.0034	58	180	No	No	WDFN -6
NCV8716MT30TBG	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	Positive	3	0.08	2.5	24	0.37	0.0034	58	190	No	No	WDFN -6
NCV8716MT33TBG	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	Positive	3.3	0.08	2.5	24	0.35	0.0034	60	200	No	No	WDFN -6
NCV8716MT50TBG	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	Positive	5	0.08	2.5	24	0.31	0.0034	54	220	No	No	WDFN -6

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 5/19/2019