

## Product Overview

### NGTD8R65F2: Rectifier 650V 30A FS2 bare die

For complete documentation, see the data sheet.

Rectifier bare die intended for use as IGBT reverse diode

### Features

- Extremely Efficient Trench with Field Stop Technology
- $T_{Jmax} = 175^{\circ}C$
- Optimized for High Speed Switching
- These are Pb-Free Devices

### Applications

- Solar Inverter
- Uninterruptible Power Inverter Supplies (UPS)
- Welding

### Part Electrical Specifications

Product	Compliance	Status	$V_{ES}^{(BR)C}$ Typ (V)	$I_C$ Max (A)	$V_{CE(sa)}$ Typ (V)	$V_F$ Typ (V)	$E_{off}$ Typ (mJ)	$E_{on}$ Typ (mJ)	$T_{rr}$ Typ (ns)	$I_{rr}$ Typ (A)	Gate Charge Typ (nC)	Short Circuit Withstand ( $\mu s$ )	$E_{AS}$ Typ (mJ)	$P_D$ Max (W)	Co- Pack aged Diode	Pack age Type
NGTD8R65F2SWK	Pb-free	Active	650	-	-	2.1	-	-	-	-	-	-	-	-	-	
	Halide free															
NGTD8R65F2WP	Pb-free	Active	650	-	-	2.1	-	-	-	-	-	-	-	-	-	
	Halide free															

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 2/15/2019