

AI Server Fan Drive Applications using NCP81295 and NCP81428 Smart Fuse

AND90444/D

INTRODUCTION AND SYSTEM REQUIREMENTS

Modern servers rely on redundant 12 V BLDC fans for cooling loads that generate large amounts of heat such as GPU's. Fan startup current, locked-rotor conditions, cable inductance, and hot-swap events all place demands on the power-distribution network. The NCP81428 and NCP81295 Smart Fuse (Electronic Fuse or eFuse) provides protection, monitoring, and telemetry for these loads.

NCP81428 SOLUTION OVERVIEW

The NCP81428 integrates a low $R_{DS(on)}$ MOSFET, hot-swap controller, telemetry, fault logging, and PMBus communications. A dedicated Smart Fuse per fan module improves fault isolation and allows system firmware to identify degraded or failed fans, adjust system for fan speed or board heating adding further intelligence to the system implementation.

NCP81295 SOLUTION OVERVIEW

The NCP81295 integrates a low $R_{DS(on)}$ MOSFET and analog hot-swap controller. The NCP81295 features the

same protections as NCP81428 but without PMBus for loads that do not require telemetry.

DESIGN CONSIDERATIONS FOR SERVER FAN LOADS

Server fans commonly draw several times their rated operating current during startup. Soft-start settings, overcurrent thresholds, and fault timers should be selected to allow normal startup while still protecting the system from stalled-rotor and short-circuit events. PMBus telemetry can be used to monitor fan health trends over time.

Although BLDC fans contain internal commutation electronics, the motor windings and wiring harness remain inductive. When current is interrupted, stored energy can generate voltage transients. An external Schottky diode connected from the fan supply node to ground provides a controlled freewheel path, reducing output overshoot, negative transients, EMI, and MOSFET stress.




Figure 1. High Level Recommended Layout for Smart Fuse Products
C1 = Output MLCC Cap, D1 = Output Schottky, D2 = Input TVS

LAYOUT CONSIDERATIONS

Proper sizing of the output capacitor (COUT) is an important companion to the Schottky diode. During fault shutdown or rapid load-current transitions, the output capacitor absorbs a portion of the energy stored in the fan inductance and cable harness. Insufficient capacitance can result in excessive voltage excursions at VOUT, while adequate capacitance helps maintain a controlled output waveform and reduces stress on the Smart Fuse. In server applications, low-ESR ceramic or polymer capacitors located close to the fan connector are recommended. Designers should evaluate worst-case fan current, cable inductance, and shutdown conditions to ensure the capacitor can absorb transient energy without exceeding the maximum voltage rating of the fan electronics or the Smart Fuse. When long harnesses are present, additional bulk capacitance may be required. The combination of properly

sized COUT and a Schottky clamp diode provides the most robust protection against inductive transients.

Large VIN and VOUT copper regions, abundant thermal vias beneath the exposed pad, and short high-current paths improve thermal performance. Multiple fan channels should use consistent routing practices to achieve uniform current sharing and temperature rise.

CONCLUSION

The NCP81428 and NCP81295 provide a compact solution for protection in 12 V server fan power distribution. Combining current limiting, fault protection, telemetry, PMBus monitoring, properly sized output capacitance, and a Schottky freewheel diode results in a robust design capable of addressing startup surges, fault conditions, and inductive-load transients.

REVISION HISTORY

Revision	Description of Changes	Date
0	Initial document release.	9/29/2026



onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales