

Single IGBT for Automotive Application

1200 V, 40 A

AFGHL40T120RH

Description

This Insulated Gate Bipolar Transistor (IGBT) features a robust and cost effective Field Stop II Trench construction. Provides superior performance in demanding switching applications, offering both low on state voltage and minimal switching loss, which is AEC Q101 qualified offer the optimum performance for both hard and soft switching topology in automotive application.



Features

- Extremely Efficient Trench with Field Stop Technology
- Maximum Junction Temperature: $T_J = 175^{\circ}\text{C}$
- Short Circuit Withstand Time 9 μs
- 100% of the Parts Tested for I_{LM} (Note 2)
- Fast Switching
- Tighten Parameter Distribution
- AEC-Q101 Qualified and PPAP Capable
- This Device is Pb-Free, Halogen Free/BFR Free and is RoHS Compliant

Typical Applications


- Automotive HEV-EV E-Compressor
- Automotive HEV-EV PTC Heater
- Automotive HEV-EV Onboard Chargers
- Automotive HEV-EV DC-DC Converters

V_{CES}	I_C	$V_{CE(Sat)}$
1200 V	40 A	2.0 V (Typ.)



TO-247-3L
CASE 340CX

MARKING DIAGRAM



AFG40T120RH	= Specific Device Code
\$Y	= onsemi Logo
&Z	= Assembly Plant Code
&3	= 3-Digit Date Code
&K	= 2-Digit Lot Traceability Code

ORDERING INFORMATION

Device	Package	Shipping
AFGHL40T120RH	TO-247-3L	30 Units / Rail

AFGHL40T120RH

MAXIMUM RATINGS

Description	Symbol	Value	Unit
Collector – Emitter Voltage	V_{CE}	1200	V
Gate – Emitter Voltage	V_{GE}	± 20	V
Transient Gate – Emitter Voltage		± 30	
Collector Current @ $T_C = 25^\circ\text{C}$ (Note 1)	I_C	48	A
Collector Current @ $T_C = 100^\circ\text{C}$		40	
Pulsed Collector Current (Note 2)	I_{LM}	160	A
Pulsed Collector Current (Note 3)	I_{CM}	160	A
Maximum Power Dissipation @ $T_C = 25^\circ\text{C}$	P_D	588	W
Maximum Power Dissipation @ $T_C = 100^\circ\text{C}$		294	
Short Circuit Withstand Time $V_{GE} = 15\text{ V}$, $V_{CE} = 600\text{ V}$, $T_J = 150^\circ\text{C}$	SCWT	9	μs
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55 to $+175$	$^\circ\text{C}$
Maximum Lead Temp. For Soldering Purposes ($\frac{1}{8}$ " from case for 5 s)	T_L	260	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Value limited by bond wire.
2. $V_{CC} = 600\text{ V}$, $V_{GE} = 15\text{ V}$, $I_C = 160\text{ A}$, $R_G = 15\ \Omega$, Inductive Load, 100% Tested.
3. Repetitive rating: pulse width limited by max. Junction temperature.

THERMAL CHARACTERISTICS

Rating	Symbol	Max.	Unit
Thermal Resistance, Junction to Case, for IGBT	$R_{\theta JC}$	0.255	$^\circ\text{C/W}$
Thermal Resistance, Junction to Ambient, Max	$R_{\theta JA}$	40	$^\circ\text{C/W}$

AFGHL40T120RH

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Test Conditions	Symbol	Min.	Typ.	Max.	Unit
-----------	-----------------	--------	------	------	------	------

OFF CHARACTERISTICS

Collector-Emitter Breakdown Voltage	V _{GE} = 0 V, I _C = 1 mA	BV _{CES}	1280	–	–	V
Temperature Coefficient of Breakdown Voltage	V _{GE} = 0 V, I _C = 1 mA	$\frac{\Delta BV_{CES}}{\Delta T_J}$	–	1.9	–	V/°C
Collector-Emitter Cut-off Current	V _{GE} = 0 V, V _{CE} = 1200 V	I _{CES}	–	–	40	μA
Gate Leakage Current	V _{GE} = 20 V, V _{CE} = 0 V	I _{GES}	–	–	±400	nA

ON CHARACTERISTICS

Gate-Emitter Threshold Voltage	V _{GE} = V _{CE} , I _C = 40 mA	V _{GE(th)}	5.3	6.3	7.3	V
Collector-Emitter Saturation Voltage	V _{GE} = 15 V, I _C = 40 A, T _J = 25°C V _{GE} = 15 V, I _C = 40 A, T _J = 175°C	V _{CE(sat)}	– –	1.95 2.47	2.4 –	V

DYNAMIC CHARACTERISTICS

Input Capacitance	V _{CE} = 20 V, V _{GE} = 0 V, f = 1 MHz	C _{ies}	–	6172	–	pF
Output Capacitance		C _{oes}	–	246	–	
Reverse Transfer Capacitance		C _{res}	–	111	–	
Gate Charge Total	V _{CC} = 600 V, I _C = 40 A, V _{GE} = 15 V	Q _g	–	533	–	nC
Gate to Emitter Charge		Q _{ge}	–	104	–	
Gate to Collector Charge		Q _{gc}	–	271	–	

SWITCHING CHARACTERISTICS, INDUCTIVE LOAD

Turn-on Delay Time	T _J = 25°C V _{CC} = 600 V, I _C = 20 A R _g = 10 Ω V _{GE} = 15 V Inductive Load FWD: AFGHL40T120RHD	t _{d(on)}	–	30	–	ns
Rise Time		t _r	–	18	–	
Turn-off Delay Time		t _{d(off)}	–	150	–	
Fall Time		t _f	–	93	–	
Turn-on Switching Loss		E _{on}	–	0.98	–	mJ
Turn-off Switching Loss		E _{off}	–	0.59	–	
Total Switching Loss		E _{ts}	–	1.57	–	
Turn-on Delay Time	T _J = 25°C V _{CC} = 600 V, I _C = 40 A R _g = 10 Ω V _{GE} = 15 V Inductive Load FWD: AFGHL40T120RHD	t _{d(on)}	–	34	–	ns
Rise Time		t _r	–	38	–	
Turn-off Delay Time		t _{d(off)}	–	146	–	
Fall Time		t _f	–	96	–	
Turn-on Switching Loss		E _{on}	–	2.12	–	mJ
Turn-off Switching Loss		E _{off}	–	1.32	–	
Total Switching Loss		E _{ts}	–	3.44	–	
Turn-on Delay Time	T _J = 175°C V _{CC} = 600 V, I _C = 20 A R _g = 10 Ω V _{GE} = 15 V Inductive Load FWD: AFGHL40T120RHD	t _{d(on)}	–	28	–	ns
Rise Time		t _r	–	18	–	
Turn-off Delay Time		t _{d(off)}	–	176	–	
Fall Time		t _f	–	212	–	
Turn-on Switching Loss		E _{on}	–	1.63	–	mJ
Turn-off Switching Loss		E _{off}	–	1.34	–	
Total Switching Loss		E _{ts}	–	2.97	–	

AFGHL40T120RH

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified) (continued)

Parameter	Test Conditions	Symbol	Min.	Typ.	Max.	Unit
-----------	-----------------	--------	------	------	------	------

SWITCHING CHARACTERISTICS, INDUCTIVE LOAD

Turn-on Delay Time	$T_J = 175^\circ\text{C}$ $V_{CC} = 600\text{ V}$, $I_C = 40\text{ A}$ $R_g = 10\ \Omega$ $V_{GE} = 15\text{ V}$ Inductive Load FWD: AFGHL40T120RHD	$t_{d(on)}$	–	31	–	ns
Rise Time		t_r	–	39	–	
Turn-off Delay Time		$t_{d(off)}$	–	152	–	
Fall Time		t_f	–	220	–	
Turn-on Switching Loss		E_{on}	–	3.38	–	mJ
Turn-off Switching Loss		E_{off}	–	2.83	–	
Total Switching Loss		E_{ts}	–	6.21	–	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS




Figure 1. Typical Output Characteristics (25°C)




Figure 2. Typical Output Characteristics (175°C)




Figure 3. Typical Saturation Voltage Characteristics




Figure 4. Saturation Voltage vs. Junction Temperature




Figure 5. Saturation Voltage vs. V_{GE} (25°C)




Figure 6. Saturation Voltage vs. V_{GE} (175°C)

AFGHL40T120RH

TYPICAL CHARACTERISTICS (continued)




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristics




Figure 9. Turn-On Characteristics vs. Gate Resistance




Figure 10. Turn-Off Characteristics vs. Gate Resistance




Figure 11. Turn-On Characteristics vs. Collector Current




Figure 12. Turn-Off Characteristics vs. Collector Current

AFGHL40T120RH

TYPICAL CHARACTERISTICS (continued)




Figure 13. Switching Loss vs. Gate Resistance




Figure 14. Switching Loss vs. Collector Current




Figure 15. SOA Characteristics (FBSOA)








Figure 16. Transient Thermal Impedance of IGBT

TO-247-3LD
CASE 340CX
ISSUE A

DATE 06 JUL 2020



NOTES: UNLESS OTHERWISE SPECIFIED.

- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
B. ALL DIMENSIONS ARE IN MILLIMETERS.
C. DRAWING CONFORMS TO ASME Y14.5 - 2009.
D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

GENERIC
MARKING DIAGRAM*


XXXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
G = Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.58	4.70	4.82
A1	2.20	2.40	2.60
A2	1.40	1.50	1.60
D	20.32	20.57	20.82
E	15.37	15.62	15.87
E2	4.96	5.08	5.20
e	~	5.56	~
L	19.75	20.00	20.25
L1	3.69	3.81	3.93
ØP	3.51	3.58	3.65
Q	5.34	5.46	5.58
S	5.34	5.46	5.58
b	1.17	1.26	1.35
b2	1.53	1.65	1.77
b4	2.42	2.54	2.66
c	0.51	0.61	0.71
D1	13.08	~	~
D2	0.51	0.93	1.35
E1	12.81	~	~
ØP1	6.60	6.80	7.00

DOCUMENT NUMBER:	98AON93302G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-247-3LD	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales