

# Silicon Carbide (SiC) JFET - EliteSiC, Power N-Channel, TO247-3, 650 V, 80 mohm

## UJ3N065080K3S

### Description


onsemi offers the High-Performance G3 SiC normally-On JFET transistors. This Series Exhibits Ultra-low on resistance ( $R_{DS(on)}$ ) and Gate charge ( $Q_G$ ) allowing for Low Conduction and Switching loss. The device Normally-On Characteristics with low  $R_{DS(on)}$  at  $V_{GS} = 0\text{ V}$  is also ideal for current protection circuits without the need for active control, as well as for cascode operation.

### Features

- Typical On-Resistance  $R_{DS(on)}$ , typ of 80 m $\Omega$
- Voltage Controlled
- Maximum Operating Temperature of 175 °C
- Extremely Fast Switching not Dependent on Temperature
- Low Gate Charge
- Low Intrinsic Capacitance
- This Device is Pb-Free, Halogen Free and is RoHS Compliant

### Typical Applications

- Over Current Protection Circuits
- DC-AC Inverters
- Switch Mode Power Supplies
- Power Factor Correction Modules
- Motor Drives
- Induction Heating




TO247-3  
CASE 340AK

### MARKING DIAGRAM



UJ3N065080K3S = Specific Device Code  
A = Assembly Location  
YY = Year  
WW = Work Week  
ZZZ = Lot ID

### PIN CONNECTIONS



### ORDERING INFORMATION

See detailed ordering and shipping information on page 7 of this data sheet.

# UJ3N065080K3S

## MAXIMUM RATINGS

Parameter	Symbol	Test Conditions	Value	Unit
Drain-source Voltage	$V_{DS}$		650	V
Gate-Source Voltage	$V_{GS}$	DC	-20 to +3	V
		AC (Note 1)	-20 to +20	
Continuous Drain Current (Note 2)	$I_D$	$T_C = 25\text{ }^{\circ}\text{C}$	32	A
		$T_C = 100\text{ }^{\circ}\text{C}$	24	A
Pulsed Drain Current (Note 3)	$I_{DM}$	$T_C = 25\text{ }^{\circ}\text{C}$	72	A
Power Dissipation	$P_{TOT}$	$T_C = 25\text{ }^{\circ}\text{C}$	190	W
Maximum Junction Temperature	$T_{J,max}$		175	$^{\circ}\text{C}$
Operating and Storage Temperature	$T_J, T_{STG}$		-55 to 175	$^{\circ}\text{C}$
Max. Lead Temperature for Soldering, 1/8" from Case for 5 seconds	$T_L$		250	$^{\circ}\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. +20 V AC Rating Applies for Turn-on Pulses <200 ns applied with external  $R_G > 1\text{ }\Omega$
2. Limited by  $T_{J,max}$
3. Pulse width  $t_p$  limited by  $T_{J,max}$

## THERMAL CHARACTERISTICS

Parameter	Symbol	Test Conditions	Value			
			Min	Typ	Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$		–	0.61	0.79	$^{\circ}\text{C/W}$

# UJ3N065080K3S

## ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = +25 °C Unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
<b>TYPICAL PERFORMANCE – STATIC</b>						
Drain-Source Breakdown Voltage	BV <sub>DS</sub>	V <sub>GS</sub> = -20 V, I <sub>D</sub> = 1 mA	650	–	–	V
Total Drain Leakage Current	I <sub>D</sub>	V <sub>DS</sub> = 650 V, V <sub>GS</sub> = -20 V, T <sub>J</sub> = 25 °C	–	8	60	μA
		V <sub>DS</sub> = 650 V, V <sub>GS</sub> = -20 V, T <sub>J</sub> = 175 °C	–	30	–	
Total Gate Leakage Current	I <sub>G</sub>	V <sub>GS</sub> = -20 V, T <sub>J</sub> = 25 °C	–	10	50	μA
		V <sub>GS</sub> = -20 V, T <sub>J</sub> = 175 °C	–	32	–	μA
Drain-Source On-Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 2 V, I <sub>D</sub> = 10 A, T <sub>J</sub> = 25 °C	–	68	–	mΩ
		V <sub>GS</sub> = 0 V, I <sub>D</sub> = 10 A, T <sub>J</sub> = 25 °C	–	80	95	
		V <sub>GS</sub> = 2 V, I <sub>D</sub> = 10 A, T <sub>J</sub> = 175 °C	–	114	–	
		V <sub>GS</sub> = 0 V, I <sub>D</sub> = 10 A, T <sub>J</sub> = 175 °C	–	130	–	
Gate Threshold Voltage	V <sub>G(th)</sub>	V <sub>DS</sub> = 5 V, I <sub>D</sub> = 20 mA	-14	-11.5	-6	V
Gate Resistance	R <sub>G</sub>	f = 1 MHz, Open Drain	–	3.7	–	Ω

## TYPICAL PERFORMANCE – DYNAMIC

Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> = 100 V, V <sub>GS</sub> = -20 V, f = 100 kHz	–	630	–	pF
Output Capacitance	C <sub>oss</sub>		–	94	–	
Reverse Transfer Capacitance	C <sub>rss</sub>		–	88	–	
Effective Output Capacitance, Energy Related	C <sub>oss(er)</sub>	V <sub>DS</sub> = 0 V to 400 V, V <sub>GS</sub> = -20 V	–	69	–	pF
Total Gate Charge	Q <sub>G</sub>	V <sub>DS</sub> = 400 V, I <sub>D</sub> = 24 A, V <sub>GS</sub> = -18 V to 0 V	–	75	–	nC
Gate-Drain Charge	Q <sub>GD</sub>		–	43	–	
Gate-Source Charge	Q <sub>GS</sub>		–	7	–	
Turn-On Delay Time	t <sub>d(on)</sub>	V <sub>DS</sub> = 400 V, I <sub>D</sub> = 24 A, Gate Driver = -18 V to +0 V, R <sub>G, EXT</sub> = 1 Ω, Inductive Load, FWD: UJ3D06510TS, T <sub>J</sub> = 25 °C	–	6	–	ns
Rise Time	t <sub>r</sub>		–	25	–	
Turn-Off Delay Time	t <sub>d(off)</sub>		–	14	–	
Fall Time	t <sub>f</sub>		–	31	–	
Turn-On Energy	E <sub>ON</sub>		–	149	–	μJ
Turn-Off Energy	E <sub>OFF</sub>		–	183	–	
Total Switching Energy	E <sub>TOTAL</sub>		–	332	–	
Turn-On Delay Time	t <sub>d(on)</sub>	V <sub>DS</sub> = 400 V, I <sub>D</sub> = 24 A, Gate Driver = -18 V to +0 V, R <sub>G, EXT</sub> = 1 Ω, Inductive Load, FWD: UJ3D06510TS, T <sub>J</sub> = 150 °C	–	6	–	ns
Rise Time	t <sub>r</sub>		–	24	–	
Turn-Off Delay Time	t <sub>d(off)</sub>		–	14	–	
Fall Time	t <sub>f</sub>		–	14	–	
Turn-On Energy	E <sub>ON</sub>		–	134	–	μJ
Turn-Off Energy	E <sub>OFF</sub>		–	103	–	
Total Switching Energy	E <sub>TOTAL</sub>		–	237	–	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL PERFORMANCE DIAGRAMS




Figure 1. Typical Output Characteristics at  $T_J = -55^\circ\text{C}$




Figure 2. Typical Output Characteristics at  $T_J = 25^\circ\text{C}$




Figure 3. Typical Output Characteristics at  $T_J = 175^\circ\text{C}$




Figure 4. Typical Drain-Source Leakage at  $V_{DS} = -20\text{ V}$




Figure 5. Typical Capacitances at 100 kHz and  $V_{GS} = -20\text{ V}$






Figure 6. Typical Transfer Characteristics at  $V_{DS} = 5\text{ V}$


TYPICAL PERFORMANCE DIAGRAMS (continued)




**Figure 7. Normalized On-Resistance Vs. Temperature at  $V_{GS} = 0$  V and  $I_D = 10$  A**




**Figure 8. Typical Drain-Source On-Resistance  $V_{GS} = 0$  V**




**Figure 9. Threshold Voltage vs.  $T_J$  at  $V_{DS} = 5$  V and  $I_D = 20$  mA**



**Figure 10. Typical Stored Energy in  $C_{OSS}$  at  $V_{GS} = -20$  V**



**Figure 11. Total Power Dissipation**



**Figure 12. Safe Operation Area at  $T_C = 25$  °C, Parameter  $t_p$**

TYPICAL PERFORMANCE DIAGRAMS (continued)




Figure 13. Typical Gate Leakage Current at  $V_{DS} = 0\text{ V}$




Figure 14. Typical Gate Forward Current at  $V_{DS} = 0\text{ V}$




Figure 15. Maximum Transient Thermal Impedance




Figure 16. Typical Gate Charge at  $V_{DS} = 400\text{ V}$  and  $I_D = 24\text{ A}$




Figure 17. Clamped Inductive Switching Energy vs. Drain Current at  $T_J = 150\text{ °C}$





Figure 18. Clamped Inductive Switching Energy vs. Gate Resistor  $R_G$

# UJ3N065080K3S

## TYPICAL PERFORMANCE DIAGRAMS (continued)



**Figure 19. Clamped Inductive Switching Energy vs. Junction Temperature at  $I_D = 24\text{ A}$**

### ORDERING INFORMATION


Part Number	Marking	Package	Shipping
UJ3N065080K3S	UJ3N065080K3S	TO247-3 (Pb-Free, Halogen Free)	600 Units / Tube

## UJ3N065080K3S

### REVISION HISTORY





Revision	Description of Changes	Date
4	Converted the Data Sheet to onsemi format.	06/17/2025





**TO247-3 15.90x20.96x5.03, 5.44P**  
**CASE 340AK**  
**ISSUE B**

DATE 14 APR 2025



**NOTE:**

1. Dimensioning and tolerancing as per ASME Y14.5 - 2018
2. Controlling dimension : millimeters
3. Package Outline in compliance with JEDEC standard var. AD.
4. Dimensions D & E does not include mold flash.
5. ØP to have max draft angle of 1.7° to the top with max. hole diameter of 3.91mm.

SYM	millimeters		
	MIN	NOM	MAX
A	4.70	5.03	5.31
A1	2.21	2.40	2.59
A2	1.50	2.03	2.49
b	0.99	1.20	1.40
b2	1.65	2.03	2.39
b4	2.59	3.00	3.43
c	0.38	0.60	0.89
D	20.70	20.96	21.46
D1	13.08	—	—
D2	0.51	1.19	1.35
E	15.49	15.90	16.26
e	5.44 BSC		
E1	13.00	13.30	13.60
E2	3.43	3.89	5.20
L	19.62	20.27	20.32
L1	—	—	4.50
ØP	3.40	3.60	3.80
ØP1	7.06	7.19	7.39
Q	5.38	5.62	6.20
S	6.15 BSC		
Ø	3°		
Ø1	20°		
Ø2	10°		

<b>DOCUMENT NUMBER:</b>	<b>98AON88794E</b>	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
<b>DESCRIPTION:</b>	<b>TO247-3 15.90x20.96x5.03, 5.44P</b>	<b>PAGE 1 OF 1</b>

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)