


High Voltage Switching Diodes



BASH16MX2W

The BASHxxMX2W Switching Diode is a spin-off of our popular SOT-23 three-leaded device. It is designed for switching applications and is housed in the X2DFNW2 (1.0x0.6mm) surface mount package. This device is ideal for low-power surface mount applications, where board space is at a premium.

Features

- 175°C T_{J(max)} – Rated for High Temperature, Mission Critical Applications
- Wettable Flank Package for optimal Automated Optical Inspection (AOI)
- NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Continuous Reverse Voltage BASH16 BASH19 BASH20 BASH21	V _R , V _{RRM}	100 120 200 250	Vdc
Continuous Forward Current	I _F	200	mAdc
Repetitive Peak Forward Current (Pulse Wave = 1 sec, Duty Cycle = 66%)	I _{FRM}	500	mA
Non-Repetitive Peak Forward Current (Square Wave, T _J = 25°C prior to surge)	I _{FSM}		A
BASH16 t = 1 μs t = 1 ms t = 1 s		5.0 2.0 0.5	
BASH19/20/21 t = 1 μs t = 1 ms t = 1 s		9.0 3.0 1.7	

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Total Device Dissipation FR-5 Board T _A = 25°C (Note 1)	P _D	300	mW
Thermal Resistance Junction-to-Ambient (Note 1)	R _{θJA}	400	°C/W
Thermal Resistance Junction-to-Solder Point (Note 1)	R _{θJSP}	105	°C/W
Junction and Storage Temperature Range	T _J , T _{stg}	-55 to +175	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Mounted onto a 4 in square FR-4 board 10 mm sq. 1 oz. Cu 0.06" thick single sided. Operating to steady state.



X2DFNW2
CASE 711BG

MARKING DIAGRAM



XX = Specific Device Code
M = Date Code

ORDERING INFORMATION


See detailed ordering, marking and shipping information on page 4 of this data sheet.

BASH16MX2W

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS				
Reverse Voltage Leakage Current ($V_R = 80\text{ Vdc}$) BASH16 ($V_R = 100\text{ Vdc}$) BASH19 ($V_R = 150\text{ Vdc}$) BASH20 ($V_R = 200\text{ Vdc}$) BASH21 ($V_R = 80\text{ Vdc}, T_J = 150^\circ\text{C}$) BASH16 ($V_R = 25\text{ Vdc}, T_J = 150^\circ\text{C}$) BASH16 ($V_R = 100\text{ Vdc}, T_J = 150^\circ\text{C}$) BASH19 ($V_R = 150\text{ Vdc}, T_J = 150^\circ\text{C}$) BASH20 ($V_R = 200\text{ Vdc}, T_J = 150^\circ\text{C}$) BASH21	I_R	-	0.5 0.1 0.1 0.1 50 30 100 100 100	$\mu\text{A dc}$
Reverse Breakdown Voltage ($I_{BR} = 100\ \mu\text{A dc}$) BASH16 BASH19 BASH20 BASH21	$V_{(BR)}$	100 120 200 250	- - - -	Vdc
Forward Voltage ($I_F = 100\text{ mA dc}$) ($I_F = 200\text{ mA dc}$)	V_F	- -	1.0 1.25	Vdc
Diode Capacitance ($V_R = 0, f = 1.0\text{ MHz}$)	C_D	-	3.0	pF
Reverse Recovery Time ($I_F = I_R = 10\text{ mA dc}, R_L = 50\ \Omega$) BASH16 ($I_F = I_R = 30\text{ mA dc}, R_L = 100\ \Omega$) BASH19/20/21	t_{rr}	- -	6.0 50	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.



- Notes: 1. A 2.0 k Ω variable resistor adjusted for a Forward Current (I_F) of 10 mA.
2. Input pulse is adjusted so $I_{R(\text{peak})}$ is equal to 10 mA.
3. $t_p \gg t_{rr}$

Figure 1. Recovery Time Equivalent Test Circuit

BASH16MX2W

TYPICAL CHARACTERISTICS




Figure 2. Forward Voltage




Figure 3. Total Capacitance




Figure 4. Reverse Current - BASH16




Figure 5. Reverse Current - BASH19




Figure 6. Reverse Current - BASH20




Figure 7. Reverse Current - BASH21

BASH16MX2W


DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping†
BASH16MX2WT5G, NSVBASH16MX2WT5G*	MF	X2DFN2 (Pb-Free)	8000 / Tape & Reel
BASH19MX2WT5G, NSVBASH19MX2WT5G*	ME		
BASH20MX2WT5G, NSVBASH20MX2WT5G*	MG		
BASH21MX2WT5G, NSVBASH21MX2WT5G*	MH		

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.





*NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS




X2DFNW2 1.00x0.60x0.37, 0.65P
CASE 711BG
ISSUE D

DATE 29 FEB 2024



DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.34	0.37	0.40
A1	---	---	0.05
b	0.45	0.50	0.55
D	1.00 BSC		
D1	---	---	0.05
E	0.60 BSC		
e	0.65 BSC		
L	0.22 REF		
L1	0.24	0.28	0.34



RECOMMENDED MOUNTING FOOTPRINT*

* FOR ADDITIONAL INFORMATION ON OUR Pb-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

GENERIC MARKING DIAGRAM*



XX = Specific Device Code
M = Date Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G", may or not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON15241G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	X2DFNW2 1.00x0.60x0.37, 0.65P	PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales