



N-Channel Logic Level Enhancement Mode Field Effect Transistor

BSS138K




Features

- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Ultra-Small Surface Mount Package
- Green Compound
- ESD HBM = 2000 V as per JEDEC A114A;
ESD CDM = 2000 V as per JEDEC C101C
- This Device is Pb-Free and is RoHS Compliant



SOT-23-3
CASE 318-08

MARKING DIAGRAM



- SK = Specific Device Code
M = Assembly Operation Month
▪ = Pb-Free Package

(Note: Microdot may be in either location)

ABSOLUTE MAXIMUM RATINGS

($T_A = 25^\circ\text{C}$ unless otherwise noted) (Note 1)

| Symbol | Parameter | Value | Unit |
|-----------|-----------------------------------------|-------------|----------------------|
| V_{DSS} | Drain-Source Voltage | 50 | V |
| V_{GSS} | Gate-Source Voltage | ± 12 | V |
| I_D | Drain Current – Continuous | 0.22 | A |
| | Drain Current – Pulsed | 0.88 | |
| P_D | Total Device Dissipation | 350 | mW |
| | Derating above $T_A = 25^\circ\text{C}$ | 2.8 | mW/ $^\circ\text{C}$ |
| T_J | Operating Junction Temperature Range | -55 to +150 | $^\circ\text{C}$ |
| T_{STG} | Storage Temperature Range | -55 to +150 | $^\circ\text{C}$ |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

THERMAL CHARACTERISTICS

| Symbol | Parameter | Value | Unit |
|-----------------|--------------------------------------------------|-------|---------------------------|
| $R_{\theta JA}$ | Thermal Resistance, Junction-to-Ambient (Note 2) | 350 | $^\circ\text{C}/\text{W}$ |

2. Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch. Minimum land pad size.

ORDERING INFORMATION

| Device | Package | Shipping [†] |
|---------|-----------------------|-----------------------|
| BSS138K | SOT-23-3 (Pb-Free) | 3000 / Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

BSS138K

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

| Symbol | Parameter | Test Conditions | Min | Typ | Max | Unit |
|--------|-----------|-----------------|-----|-----|-----|------|
|--------|-----------|-----------------|-----|-----|-----|------|

OFF CHARACTERISTICS

| | | | | | | |
|------------------------|-------------------------------------------|------------------------------------------------|----|------|-------|------|
| BV _{DSS} | Drain–Source Breakdown Voltage | V _{GS} = 0 V, I _D = 10 μA | 50 | – | – | V |
| $\frac{BV_{DSS}}{T_J}$ | Breakdown Voltage Temperature Coefficient | I _D = 250 μA, Referenced to 25°C | – | 0.11 | – | V/°C |
| I _{DSS} | Zero Gate Voltage Drain Current | V _{DS} = 50 V, V _{GS} = 0 V | – | – | 0.1 | μA |
| I _{GSS} | Gate–Body Leakage | V _{GS} = ±12 V, V _{DS} = 0 V | – | – | ±1 | μA |
| | | V _{GS} = ±10 V, V _{DS} = 0 V | – | – | ±0.5 | |
| | | V _{GS} = ±5 V, V _{DS} = 0 V | – | – | ±0.05 | |

ON CHARACTERISTICS

| | | | | | | |
|--------------------------|------------------------------------------------|-------------------------------------------------------------|-----|------|-----|-------|
| V _{GS(th)} | Gate Threshold Voltage | V _{DS} = V _{GS} , I _D = 250 μA | 0.6 | – | 1.2 | V |
| $\frac{V_{GS(th)}}{T_J}$ | Gate Threshold Voltage Temperature Coefficient | I _D = 1 mA, Referenced to 25°C | – | –1.4 | – | mV/°C |
| R _{DS(on)} | Static Drain–Source On–Resistance | V _{GS} = 1.8 V, I _D = 50 mA | – | – | 2.5 | Ω |
| | | V _{GS} = 2.5 V, I _D = 50 mA | – | – | 2.0 | |
| | | V _{GS} = 5 V, I _D = 50 mA, | – | – | 1.6 | |
| I _{D(ON)} | On–State Drain Current | V _{GS} = 10 V, V _{DS} = 5 V | 0.2 | – | – | A |
| g _{FS} | Forward Transconductance | V _{DS} = 10 V, I _D = 200 mA | 200 | – | – | mS |

DYNAMIC CHARACTERISTICS

| | | | | | | |
|------------------|------------------------------|---------------------------------------------------------------|---|------|---|----|
| C _{iss} | Input Capacitance | V _{DS} = 25 V, V _{GS} = 0 V, f = 1.0 MHz | – | 58 | – | pF |
| C _{oss} | Output Capacitance | | – | 9.75 | – | |
| C _{rss} | Reverse Transfer Capacitance | | – | 5.2 | – | |
| R _G | Gate Resistance | V _{DS} = 5 V, V _{GS} = 10 mV | – | 281 | – | Ω |

SWITCHING CHARACTERISTICS

| | | | | | | |
|---------------------|---------------------|----------------------------------------------------------------------------------------------------|---|---|-----|----|
| t _{D(ON)} | Turn–On Delay Time | V _{DD} = 30 V, I _D = 0.29 A, V _{GS} = 10 V, R _{GEN} = 6 Ω | – | – | 5 | ns |
| t _r | Turn–On Rise Time | | – | – | 5 | |
| t _{D(OFF)} | Turn–Off Delay Time | | – | – | 60 | |
| t _f | Turn–Off Fall Time | | – | – | 35 | |
| Q _g | Total Gate Charge | V _{DS} = 25 V, I _D = 0.2 A, V _{GS} = 10 V, I _G = 0.1 mA | – | – | 2.4 | nC |
| Q _{gs} | Gate–Source Charge | | – | – | 0.5 | |
| Q _{gd} | Gate–Drain Charge | | – | – | 0.5 | |

DRAIN–SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS

| | | | | | | |
|-----------------|------------------------------------|------------------------------------------------|---|---|-----|---|
| V _{sd} | Drain–Source Diode Forward Voltage | V _{GS} = 0 V, I _S = 115 mA | – | – | 1.2 | V |
|-----------------|------------------------------------|------------------------------------------------|---|---|-----|---|

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. On-Resistance Variation with Gate Voltage and Drain Current




Figure 3. On-Resistance Variation with Temperature




Figure 4. On-Resistance Variation with Gate-Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Gate Threshold Variation with Temperature

TYPICAL CHARACTERISTICS (continued)




Figure 7. Reverse Drain Current Variation with Diode Forward Voltage and Temperature

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

