CPH6341

P-Channel Power MOSFET -30V, -5A, 59mΩ, Single CPH6

Features

- $\cdot \,$ Low ON-resistance
- · High-speed switching
- 4V drive
- · Protection diode in

Specifications

Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Conditions	Ratings	Unit
Drain-to-Source Voltage	VDSS		-30	V
Gate-to-Source Voltage	VGSS		±20	V
Drain Current (DC)	ID		-5	А
Drain Current (Pulse)	IDP	PW≤10µs, duty cycle≤1%	-20	А
Allowable Power Dissipation	PD	When mounted on ceramic substrate (900mm ² ×0.8mm)	1.6	W
Channel Temperature	Tch		150	°C
Storage Temperature	Tstg		-55 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Package Dimensions

unit : mm (typ) 7018A-003



Product & Package Information

- Package
- JEITA, JEDEC
- Minimum Packing Quantity : 3,000 pcs./reel

Packing Type: TL



Marking

: CPH6



: SC-74, SOT-26, SOT-457

Electrical Connection



ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.



http://onsemi.com

Electrical	Characteristics	at	Ta=25°C	
------------	------------------------	----	---------	--

Deremeter	Oursels al	Que ditions		Ratings		
Parameter	Symbol	Conditions	min	typ	max	Unit
Drain-to-Source Breakdown Voltage	V(BR)DSS	ID=-1mA, VGS=0V	-30			V
Zero-Gate Voltage Drain Current	IDSS	VDS=-30V, VGS=0V			-1	μΑ
Gate-to-Source Leakage Current	IGSS	V _{GS} =±16V, V _{DS} =0V			±10	μΑ
Cutoff Voltage	V _{GS} (off)	V _{DS} =-10V, I _D =-1mA	-1.2		-2.6	V
Forward Transfer Admittance	yfs	V _{DS} =-10V, I _D =-3A	2.8	4.8		S
Static Drain-to-Source On-State Resistance	RDS(on)1	ID=-3A, VGS=-10V		45	59	mΩ
	R _{DS} (on)2	ID=-1.5A, VGS=-4.5V		71	100	mΩ
	R _{DS} (on)3	ID=-1.5 A, VGS=-4V		82	115	mΩ
Input Capacitance	Ciss			430		pF
Output Capacitance	Coss	V _{DS} =-10V, f=1MHz		105		pF
Reverse Transfer Capacitance	Crss			75		pF
Turn-ON Delay Time	t _d (on)			7.5		ns
Rise Time	tr			26		ns
Turn-OFF Delay Time	t _d (off)	See specified Test Circuit.		45		ns
Fall Time	tf			35		ns
Total Gate Charge	Qg			10		nC
Gate-to-Source Charge	Qgs	V _{DS} =-15V, V _{GS} =-10V, I _D =-5A		2.0		nC
Gate-to-Drain "Miller" Charge	Qgd	1		2.5		nC
Diode Forward Voltage	V _{SD}	IS=-5A, VGS=0V		-0.87	-1.2	V

Switching Time Test Circuit



Ordering Information

Device	Package	Shipping	memo	
CPH6341-TL-E	CPH6		Pb-Free	
CPH6341-TL-W	СРно	3,000pcs./reel	Pb-Free and Halogen Free	







Outline Drawing

СРН6341-ТL-Е, СРН6341-ТL-W



Land Pattern Example



Note on usage : Since the CPH6341 is a MOSFET product, please avoid using this device in the vicinity of highly charged objects.

ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and itsributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal