

Is Now Part of

OR NEW DESIGN

IN Semiconductor®

To k an more about CH Semiconductor, please visit our website at

Please note. As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild guestions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and safety requirements or standards, regardless of any support or application provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauth



FAN7361, FAN7362 High-Side Gate Driver

Features

- Floating Channel Designed for Bootstrap Operation to +600V
- Typically 250mA/500mA Sourcing/Sinking Current Driving Capability
- Common-Mode dv/dt Noise Canceling Circuit
- V_{CC} & V_{BS} Supply Range from 10V to 20V
- UVLO Function for V_{BS}
- Output In-phase with Input Signal
- 8-SOP

Applications

- PDP Scan Driver
- Motor Control
- SMPS
- Electronic Ballast

Description

The FAN7361/FAN7362, a monolithic high-side gate drive IC, can drive MOSFETs and IGBTs that operate up to +600V. Fairchild's high-voltage process and common-mode noise canceling techniques provide stable operation of the high-side driver under $gn a_{\rm v}$ the noise circumstances. An advanced level ship incuit clerk high-side gate driver operation un $v_{\rm S}$ =9.8 typ for $V_{\rm BS}$ =15V

The UVLO circuit, rev. s malf-inction when V_{BS} is lower than this specified in the fraction of the V_{BS} is lower than this specified in the fraction of the voltage Cutput drivers typically urc mink 2. mA/500mA, respectively, which is set table of fluctor in that any ballast, PDP scan driver, note in the normal solon S-S5P

Ordering Information

Part Number	Package	Operating Temperature Range	Eco Status	Packing Method
FAN7361M ⁽¹⁾	8-SOP	-40°C ~ 125°C	RoHS	Tube
FAN7361MX ⁽¹⁾				Tape & Reel
FAN7362M ⁽¹⁾				Tube
FAN7362MX ⁽¹⁾				Tape & Reel

Note:

1. These devices passed wave soldering test by JESD22A-111.

For Fairchild's definition of Eco Status, please visit: <u>http://www.fairchildsemi.com/company/green/rohs_green.html</u>.

May 2024





Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. $T_A=25^{\circ}C$, unless otherwise specified.

Symbol	Characteristics	Min.	Max.	Unit
Vs	High-Side Offset Voltage	V _B -25	V _B +0.3	
V _B	High-Side Floating Supply Voltage	-0.3	625	
V _{HO}	High-Side Floating Output Voltage	V _S -0.3	V _B +0.3	V
V _{CC}	Logic Fixed Supply Voltage	-0.3	25	
V _{IN}	Logic Input Voltage	-0.3	V _C r ^{**} .s	
dV _S /dt	Allowable Offset Voltage Slew Rate		±	V/ns
P _D ⁽²⁾⁽³⁾⁽⁴⁾	Power Dissipation		62	<u></u>
θ_{JA}	Thermal Resistance, Junction-to-Ambient		200	°C.W
TJ	Junction Temperature		. 150	°C
Τ _S	Storage Temperature		+159	°C
Τ _Α	Ambient Temperature	-40	+125	°C

Notes:

- 2. Mounted on 76.2 x 114.3 x 1.6mm PCB (FR-4 reass et y mail al)
- 3. Refer to the following standards:
 - JESD51-2: Integral circuits thermal test vironmental conditions Natural convection JESD51-3: Low effective therm con includes up and for leaded surface mount backages
- 4. Do not exceed P_D under any ci umstan s.

Recommen C erat g Conditions

The Recommended operation derives the conditions for actual device operation. Recommended operating and titions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recall and the or designing to Absolute Maximum Ratings.

אר איז	Palameter	Min.	Max.	Unit
	High Side Floating Supply Voltage	V _S +10	V _S +20	1
Ve	High-Sice Floating Supply Offset Voltage	6-V _{CC}	600	
V _{HO}	High-Side Output voltage	V _S	V _B	V
S V _{IN}	Logic Input Voltage	GND	V _{CC}	
V _{cc}	Logic Supply Voltage	10	20	

Electrical Characteristics

 $V_{BIAS}(V_{CC}, V_{BS})$ =15.0V, T_A = 25°C, unless otherwise specified. The V_{IN} and I_{IN} parameters are referenced to GND. The V_O and I_O parameters are referenced to V_S and are applicable to the respective output HO.

Symbol	Characteristics Test Condition		Min.	Тур.	Max.	Unit		
V +	V _{BS} Supply Under-Voltage Positive Going	FAN7361	8.2	9.2	10.2	-		
V _{BSUV} +	Threshold	V _{BS} =Sweep FAN7362		7.6	8.6		9.6	
Vacuura	V _{BS} Supply Under-Voltage Negative	V _{BS} =Sweep	FAN7361	7.4	8.6	9.2	v	
V _{BSUV} -	Going Threshold		FAN7362	7.2	8.2	9.2	v	
Vpouvo	V _{BS} Supply Under-Current Lockout	V _{BS} =Sweep	FAN7361		0.5			
V _{BSHYS}	Hysteresis	v _{BS} -Sweep	FAN7362		0.1			
I _{LK}	Offset Supply Leakage Current	$V_B = V_S = 600V$	V _B =V _S =600V V _{IN} =0V or 5V			10		
I _{QBS}	Quiescent V _{BS} Supply Current	V _{IN} =0V or 5V			50	80	Αų	
I _{QCC}	Quiescent V _{CC} Supply Current	V _{IN} =0V				75	μ	
I _{PBS}	Operating V _{BS} Supply Current	C _L =1nF, f=10kHz			420	.550		
V _{IH}	Logic "1" Input Voltage		TAN73	J.Ó		3		
ЧН			E 77 2	2.9				
V _{IL}	Logic "0" Input Voltage		FAN7361	$D_{\overline{D}}$		1.0	v	
۴IL		F	FAN7๖๖2			0.8	v	
V _{OH}	High Level Output Voltage, V _B -V _{HO}	Nc ad	<u>EV</u>	3		0.1		
V _{OL}	Low Level Output Voltage, V _{HC}	No Ic	γ_{α}		Sr.	0.1		
I _{IN+}	Logic "1" Input Bias Current	′ _{!N} =5V			50	90		
I _{IN-}	Logic "0" Input Bias Creent	V _{IN} ¹ 0V		\mathcal{O}	1.0	2.0	μA	
I _{O+}	Output High S ^L irc Pulse urrent	V'HO-0V, VII =5V, F	⊃W ≤ 1∂µຣ	200	250		mA	
I _{O-}	Output Low nort Circuit re Current	V _{HO} =1.5V, V _{IN} =0V	י∕י∕י≤ 10µs	400	500			
Vs	Allo Ne ive V Pin Vollage for IN Signal P gauge to HO	ALEFC)		-9.8	-7.0	v	

nan. : E octrical Charactoristics

 V_{BL} (V_C V_{BS})=15 GV V_S=GND, G_L=1000pr and T_A = 25°C, unless otherwise specified.

Symool	Characteristics	Test Condition	Min.	Тур.	Max.	Unit
t _{in}	Turn-on Propagation Delay	V _S =0V		120	200	
t _{off}	Turn-off Propagation Delay ⁽⁵⁾	V _S =0V or 600V		90	180	20
t _r	Turn-on Ris : Time			70	160	ns
t _f	Turn-off Fall Time			30	100	

Note:

5. This parameter guaranteed by design.









9

NOT RECONNENDED FOR MENDESIGN ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC