MOSFET – P-Channel, POWERTRENCH®, Logic Level

60 V

FDC5614P

V_{DSS}	$R_{DS(on)}$ MAX	I_D MAX
−60 V	0.105 Ω @ −10 V	−3 A
	0.135 Ω @ −4.5 V	



TSOT23 6−Lead (SUPERSOT™−6) CASE 419BL

Description

This 60 V P−Channel MOSFET uses **onsemi**'s high voltage POWERTRENCH process. It has been optimized for power management applications.

Features

- −3 A, −60 V
  - $R_{DS(on)}$ = 0.105 Ω @ V_{GS} = −10 V
  - $R_{DS(on)}$ = 0.135 Ω @ V_{GS} = −4.5 V
- Fast Switching Speed
- High Performance Trench Technology for Extremely Low $R_{DS(on)}$
- This is a Pb−Free and Halide Free Device

Applications

- DC−DC Converters
- Load Switch
- Power Management

MARKING DIAGRAM



564 = Specific Device Code
M = Date Code
▪ = Pb−Free Package

(Note: Microdot may be in either location)

PIN ASSIGNMENT



ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{DSS}	Drain−Source Voltage	−60	V
V_{GSS}	Gate−Source Voltage	±20	V
I_D	Drain Current − Continuous (Note 1a) − Pulsed	 −3 −20	A
P_D	Maximum Power Dissipation (Note 1a) (Note 1b)	 1.6 0.8	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	−55 to 150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
$R_{\theta JA}$	Thermal Resistance, Junction−to−Ambient (Note 1a)	78	°C/W
$R_{\theta JC}$	Thermal Resistance, Junction−to−Case (Note 1)	30	°C/W

ORDERING INFORMATION

Device	Package	Shipping†
FDC5614P	TSOT−23−6 (SUPERSOT™−6) (Pb−Free)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

© Semiconductor Components Industries, LLC, 2022

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
BV_{DSS}	Drain–Source Breakdown Voltage	V_{GS} = 0 V, I_D = −250 μA	−60	–	–	V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I_D = −250 μA, Referenced to 25°C	–	−49	–	mV/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = −48 V, V_{GS} = 0 V	–	–	−1	μA
I_{GSSF}	Gate–Body Leakage, Forward	V_{GS} = 20 V, V_{DS} = 0 V	–	–	100	nA
I_{GSSR}	Gate–Body Leakage, Reverse	V_{GS} = −20 V, V_{DS} = 0 V	–	–	−100	
ON CHARACTERISTICS (Note 2)						
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS} = V_{GS}, I_D = −250 μA	−1	−1.6	−3	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate Threshold Voltage Temperature Coefficient	I_D = −250 μA, Referenced to 25°C	–	4	–	mV/°C
$R_{DS(on)}$	Static Drain–Source On–Resistance	V_{GS} = −10 V, I_D = −3 A	–	82	105	mΩ
		V_{GS} = −4.5 V, I_D = −2.7 A	–	105	135	
		V_{GS} = −10 V, I_D = −3 A, T_J = 125°C	–	130	190	
$I_{D(on)}$	On–State Drain Current	V_{GS} = −10 V, V_{DS} = −5 V	−20	–	–	A
g_{FS}	Forward Transconductance	V_{DS} = −5 V, I_D = −3 A	–	8	–	S
DYNAMIC CHARACTERISTICS						
C_{iss}	Input Capacitance	V_{DS} = −30 V, V_{GS} = 0 V, f = 1.0 MHz	–	759	–	pF
C_{oss}	Output Capacitance		–	90	–	
C_{rss}	Reverse Transfer Capacitance		–	39	–	
SWITCHING CHARACTERISTICS (Note 2)						
$t_{d(on)}$	Turn–On Delay Time	V_{DD} = −30 V, I_D = −1 A, V_{GS} = −10 V, R_{GEN} = 6 Ω	–	7	14	ns
t_r	Turn–On Rise Time		–	10	20	
$t_{d(off)}$	Turn–Off Delay Time		–	19	34	
t_f	Turn–Off Fall Time		–	12	22	
Q_g	Total Gate Charge	V_{DS} = −30 V, I_D = −3.0 A, V_{GS} = −10 V	–	15	24	nC
Q_{gs}	Gate–Source Charge		–	2.5	–	
Q_{gd}	Gate–Drain Charge		–	3.0	–	
DRAIN−SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS						
I_S	Maximum Continuos–Source Diode Forward Current		–	–	−1.3	A
V_{SD}	Drain–Source Diode Forward Voltage	V_{GS} = 0 V, I_S = −1.3 A (Note 2)	–	−0.8	−1.2	V

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. $R_{\theta JA}$ is the sum of the junction−to−case and case−to−ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design while $R_{\theta JA}$ is determined by the user's board design.
   a) 78°C/W when mounted on a 1in^2 pad of 2oz copper on FR−4 board.
   b) 156°C/W when mounted on a minimum pad.
2. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2.0%

TYPICAL CHARACTERISTICS



Figure 1. On−Region Characteristics



Figure 2. On−Resistance Variation with Drain Current and Gate Voltage



Figure 3. On−Resistance Variation with Temperature



Figure 4. On−Resistance Variation with Gate−to−Source Voltage



Figure 5. Transfer Characteristics



Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature

TYPICAL CHARACTERISTICS (continued)



Figure 7. Gate Charge Characteristics



Figure 8. Capacitance Characteristics



Figure 9. Maximum Safe Opening Area



Figure 11. Single Pulse Maximum Power Dissipation



Figure 10. Transient Thermal Response Curve

NOTE: Thermal characterization performed using the conditions described in Note 1b. Transient thermal response will change depending on the circuit board design.

POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries.
SUPERSOT is a trademark of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries.

1
SCALE 2:1

TSOT23 6−Lead
CASE 419BL
ISSUE A

DATE 31 AUG 2020



TOP VIEW



FRONT VIEW

NOTE 4



SIDE VIEW



DETAIL A



LAND PATTERN
RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: MILLIMETERS
3. DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.25MM PER END. DIMENSIONS D AND E1 ARE DETERMINED AT DATUM H.
4. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.90	1.00	1.10
A1	0.00	0.05	0.10
A2	0.70	0.85	1.00
A3		0.25 BSC	
b	0.25	0.38	0.50
c	0.10	0.18	0.26
D	2.80	2.95	3.10
d		0.30 REF	
E	2.50	2.75	3.00
E1	1.30	1.50	1.70
e		0.95 BSC	
e1		1.90 BSC	
L1		0.60 REF	
L2	0.20	0.40	0.60
θ	0°	---	10°

GENERIC MARKING DIAGRAM*



XXX = Specific Device Code
M = Date Code
▪ = Pb−Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, "G" or microdot " ▪", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON83292G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**TSOT23 6−Lead**	**PAGE 1 OF 1**

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales