

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild guestions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



June 2014

FDB016N04AL7

N-Channel PowerTrench[®] MOSFET 40 V, 306 A, 1.6 m Ω

Features

- $R_{DS(on)}$ = 1.16 m Ω (Typ.) @ V_{GS} = 10 V, I_D = 80 A
- · Fast Switching Speed
- · Low Gate Charge
- High Performance Trench Technology for Extremely Low $R_{\mbox{\footnotesize{DS(on)}}}$
- · High Power and Current Handling Capability
- · RoHS Compliant

Description


This N-Channel MOSFET is produced using Fairchild Semiconductor's advance PowerTrench® process that has been tailored to minimize the on-state resistance while maintaining superior switching performance.

Applications

- Synchronous Rectification for ATX / Server / Telecom PSU
- · Battery Protection Circuit
- Motor drives and Uninterruptible Power Supplies



1. Gate
2. Source
3. Source
4. Drain
5. Source
6. Source
7. Source



MOSFET Maximum Ratings T_C = 25°C unless otherwise noted.

Symbol		Parameter	FDB016N04AL7	Unit
V_{DSS}	Drain to Source Voltage		40	V
V _{GSS}	Gate to Source Voltage		±20	V
1		- Continuous (T _C = 25°C, Silicon Limited)	306*	
D	Drain Current	- Continuous (T _C = 100°C, Silicon Limited)	216*	Α
		- Continuous (T _C = 25°C, Package Limited)	160	
DM	Drain Current	- Pulsed (Note 1)	1224	Α
- AS	Single Pulsed Avalanche	Energy (Note 2)	1350	mJ
dv/dt	Peak Diode Recovery dv/d	dt (Note 3)	6.0	V/ns
n	Power Dissipation	(T _C = 25°C)	283	W
D	Power Dissipation	- Derate Above 25°C	1.89	W/°C
Γ _J , T _{STG}	Operating and Storage Te	mperature Range	-55 to +175	°C
Γ _L	Maximum Lead Temperat 1/8" from Case for 5 Seco	300	°C	

^{*}Calculated continuous current based on maximum allowable junction temperature. Package limitation current is 160 A.

Thermal Characteristics

Symbol	Parameter FDB016N04AL7		Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case, Max.	0.53	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient, Max. 62.5		C/VV

Package Marking and Ordering Information

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Quantity
FDB016N04AL7	FDB016N04A	D2PAK-7L	Tape and Reel	330 mm	24 mm	800 units

Electrical Characteristics $T_C = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	lest Conditions	win.	ıyp.	wax.	Unit
Off Chara	cteristics					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V, T_C = 25^{\circ} C$	40	-	-	V
$\frac{\Delta BV_{DSS}}{\Delta T_{J}}$	Breakdown Voltage Temperature Coefficient	I_D = 250 μ A, Referenced to 25°C	-	0.03	-	V/°C
1	Zero Gate Voltage Drain Current	$V_{DS} = 32 \text{ V}, V_{GS} = 0 \text{ V}$	-	-	10	μА
IDSS	Zero Gate Voltage Drain Current	$V_{DS} = 32 \text{ V}, T_{C} = 150^{\circ}\text{C}$	-	-	500	μΑ
I _{GSS}	Gate to Body Leakage Current	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$	-	-	±100	nA

On Characteristics

V _{GS(th)}	Gate Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = 250 \mu A$	1.0	-	3.0	V
R _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 80 A	-	1.16	1.6	mΩ
9 _{FS}	Forward Transconductance	$V_{DS} = 10 \text{ V}, I_{D} = 80 \text{ A}$	-	381	-	S

Dynamic Characteristics

C _{iss}	Input Capacitance	V = 25 V V = 0 V		-	8715	11600	pF
C _{oss}	Output Capacitance	$V_{DS} = 25 \text{ V}, V_{GS} = 0 \text{ V},$ f = 1 MHz		-	2035	2710	pF
C _{rss}	Reverse Transfer Capacitance	1 – 1 101112		-\	230	-	pF
Q _{g(tot)}	Total Gate Charge at 10V			- \	129	167	nC
Q _{gs}	Gate to Source Gate Charge	$V_{DS} = 32 \text{ V}, I_{D} = 80 \text{ A},$		-	28	-	nC
Q _{gs2}	Gate Charge Threshold to Plateau	V_{GS} = 10 V		-	12	-	nC
Q_{gd}	Gate to Drain "Miller" Charge	(Note	4)	-	17	-	nC

Switching Characteristics

$t_{d(on)}$	Turn-On Delay Time		-	21	52	ns
t _r		$V_{DD} = 20 \text{ V}, I_{D} = 80 \text{ A},$	-	14	38	ns
t _{d(off)}	Turn-Off Delay Time	$R_G = 4.7 \Omega, V_{GS} = 10 V$	-	118	246	ns
t _f	Turn-Off Fall Time	(Note 4)	- //	33	76	ns
ESR	Equivalent Series Resistance (G-S)	f = 1 MHz	- /	1.25	-	Ω

Drain-Source Diode Characteristics

I _S	Maximum Continuous Drain to Source Dio	Maximum Continuous Drain to Source Diode Forward Current		-	306	Α
I _{SM}	Maximum Pulsed Drain to Source Diode Forward Current		-	-	1224	Α
V_{SD}	Drain to Source Diode Forward Voltage	V _{GS} = 0 V, I _{SD} = 80 A	-	-	1.3	V
t _{rr}	Reverse Recovery Time	V _{GS} = 0 V, I _{SD} = 80 A,	-	68	-	ns
Q _{rr}	Reverse Recovery Charge	dI _F /dt = 100 A/μs	-	84	-	nC

Notes

- 1. Repetitive rating: pulse-width limited by maximum junction temperature.
- 2. L = 3 mH, I_{AS} = 30 A, V_{DD} = 25 V, R_G = 25 Ω , starting T_J = 25°C.
- 3. I $_{SD} \leq$ 80 A, di/dt \leq 200 A/µs, V $_{DD} \leq$ BV $_{DSS},$ starting T $_{J}$ = 25°C.
- 4. Essentially independent of operating temperature typical characteristics.

Typical Performance Characteristics

Figure 1. On-Region Characteristics




Figure 3. On-Resistance Variation vs.

Drain Current and Gate Voltage




Figure 5. Capacitance Characteristics




Figure 2. Transfer Characteristics




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature





Figure 6. Gate Charge Characteristics



Typical Performance Characteristics (Continued)

Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Safe Operating Area




Figure 11. Unclamped Inductive Switching Capability




Figure 8. On-Resistance Variation vs. Temperature






Figure 10. Maximum Drain Current vs.

Case Temperature



Typical Performance Characteristics (Continued)

Figure 12. Transient Thermal Response Curve



5

Figure 13. Gate Charge Test Circuit & Waveform




Figure 14. Resistive Switching Test Circuit & Waveforms







Figure 15. Unclamped Inductive Switching Test Circuit & Waveforms





DUT

Figure 16. Peak Diode Recovery dv/dt Test Circuit & Waveforms









Mechanical Dimensions




Figure 17. TO263 (D²PAK), Molded, 7-Lead, Surface Mount

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

http://www.fairchildsemi.com/package/packageDetails.html?id=PN_TO263-0R7





TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

AccuPower™
AX-CAP®*
BitSiC™
Build it Now™
CorePLUS™
CorePOWER™
CROSSVOLT™
CTL™

Current Transfer Logic™ DEUXPEED® Dual Cool™ EcoSPARK® EfficentMax™ ESBC™

Fairchild®

Fairchild Semiconductor[®]
FACT Quiet Series[™]
FACT[®]

FACT®
FAST®
FastvCore™
FETBench™
FPS™

F-PFS™ FRFET® Global Power ResourceSM

GreenBridge™
Green FPS™
Green FPS™ e-Series™

Gmax[™] GTO[™] IntelliMAX[™] ISOPLANAR[™]

Marking Small Speakers Sound Louder and Better™

MegaBuck™
MICROCOUPLER™
MICROFET™
MicroPak™
MicroPak2™
MillerDrive™
MotionMax™
mWSaver®
OptoHiT™
OPTOLOGIC®

OPTOPLANAR®

PowerTrench® PowerXS™

Programmable Active Droop™

OFFT®

QS™ Quiet Series™ RapidConfig

Saving our world, 1mW/W/kW at a time™ SignalWise™

SignalWise™ SmartMax™ SMART START™

Solutions for Your Success™

SPM®
STEALTH™
SUPERFET®
SUPERSOT™-3
SUPERSOT™-6
SUPERSOT™-8
SUPERSOT™-8
SUPERSOT™-8
SUPERSOFET™
SYNCFET™
SYNC-LOCK™

SYSTEM ®*
GENERAL
TinyBoost®
TinyBuck®
TinyCalc™
TinyLogic®
TINYOPTO™
TinyPower™
TinyPWM™
TinyWire™
TranSiC™
TriFault Detect™
TRUECURRENT®*
µSerDes™

Serides*
UHC®
Ultra FRFET™
UniFET™
VCX™
VisualMax™
VoltagePlus™
Mmar™

*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.Fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors

PRODUCT STATUS DEFINITIONS Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary First Production		Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed Full Production		Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete Not In Production		Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev. 168

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative