ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari



ON Semiconductor®

FDMC2514SDCN-Channel Dual CoolTM 33 PowerTrench[®] SyncFETTM25 V, 40 A, 3.5 mΩGeneral Description

Features

- Dual CoolTM Top Side Cooling PQFN package
- Max $r_{DS(on)}$ = 3.5 m Ω at V_{GS} = 10 V, I_D = 22.5 A
- Max $r_{DS(on)}$ = 4.7 m Ω at V_{GS} = 4.5 V, I_D = 18 A
- High performance technology for extremely low r_{DS(on)}
- SyncFET Schottky Body Diode
- RoHS Compliant



Synchronous Rectifier for DC/DC Converters

Applications

N-Channel

Semiconductor's

This

- Telecom Secondary Side Rectification
- High End Server/Workstation Vcore Low Side

MOSFET

advanced

Advancements in both silicon and Dual $\operatorname{Cool}^{\mathsf{TM}}$

technologies have been combined to offer the lowest r_{DS(on)} while maintaining excellent switching performance by extremely


low Junction-to-Ambient thermal resistance. This device has the

added benefit of an efficient monolithic Schottky body diode.

is

produced

PowerTrench[®]



MOSFET Maximum Ratings $T_A = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter			Ratings	Units	
V _{DS}	Drain to Source Voltage			25	V	
V _{GS}	Gate to Source Voltage		(Note 4)	±20	V	
ID	Drain Current -Continuous (Package limited)	T _C = 25 °C		40		
	-Continuous (Silicon limited)	T _C = 25 °C	25 °C 10		•	
	-Continuous	T _A = 25 °C	(Note 1a)	24	Α	
	-Pulsed			200		
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	84	mJ	
dv/dt	Peak Diode Recovery dv/dt		(Note 5)	2.0	V/ns	
D	Power Dissipation	T _C = 25 °C		60	W	
P _D	Power Dissipation	T _A = 25 °C	(Note 1a)	3.0	vv	
T _J , T _{STG}	Operating and Storage Junction Temperature Range			-55 to +150	°C	
Thermal Cl	naracteristics				· · ·	
$R_{\theta JC}$	Thermal Resistance, Junction to Case		(Top Source)	5.8	°C/W	
$R_{\theta JC}$	Thermal Resistance, Junction to Case		(Bottom Drain)	2.1		
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient		(Note 1a)	42		
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient		(Note 1b)	105		
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient		(Note 1i)	17		
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient		(Note 1j)	26		
R_{\thetaJA}	Thermal Resistance, Junction to Ambient		(Note 1k)	12		

Device Marking	Device	Package Reel Size		Tape Width	Quantity		
2514S	FDMC2514SDC	Dual Cool [™] 33	13"	12 mm	3000 units		

ON

using

process.

package

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Chara	octeristics					
BV _{DSS}	Drain to Source Breakdown Voltage	I _D = 1 mA, V _{GS} = 0 V	25	1		V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	$I_D = 10$ mA, referenced to 25 °C		21		mV/°C
IDSS	Zero Gate Voltage Drain Current	$V_{DS} = 20 V, V_{GS} = 0 V$			500	μΑ
I _{GSS}	Gate to Source Leakage Current, Forward	V _{GS} = 20 V, V _{DS} = 0 V			100	nA
On Chara	cteristics					
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 1 \text{ mA}$	1.2	1.7	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 10$ mA, referenced to 25 °C		-5		mV/°C
		V _{GS} = 10 V, I _D = 22.5 A		2.5	3.5	
r _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 4.5 V, I _D = 18 A		3.6	4.7	mΩ
		V_{GS} = 10 V, I_{D} = 22.5 A, T_{J} = 125 °C		3.5	4.5	
9 _{FS}	Forward Transconductance	$V_{DS} = 5 \text{ V}, \text{ I}_{D} = 22.5 \text{ A}$		122		S
Dynamic	Characteristics					
C _{iss}	Input Capacitance			2031	2705	pF
C _{oss}	Output Capacitance	V _{DS} = 13 V, V _{GS} = 0 V, f = 1 MHz		596	795	pF
C _{rss}	Reverse Transfer Capacitance			134	205	pF
R _g	Gate Resistance			1.1	2.4	Ω
Switching	g Characteristics					
t _{d(on)}	Turn-On Delay Time			11	22	ns
t _r	Rise Time	V _{DD} = 13 V, I _D = 22.5 A,		3.6	10	ns
t _{d(off)}	Turn-Off Delay Time	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$		26	41	ns
t _f	Fall Time	1		3	10	ns
Q _g	Total Gate Charge	V _{GS} = 0 V to 10 V		31	44	nC
Q _g	Total Gate Charge	$V_{GS} = 0 \text{ V to } 4.5 \text{ V}$ $V_{DD} = 13 \text{ V},$		14	20	nC
Q _{gs}	Gate to Source Gate Charge	I _D = 22.5 A		6.5		nC
Q _{gd}	Gate to Drain "Miller" Charge			3.9		nC
Drain-Soເ	urce Diode Characteristics					
Vaa	Source to Drain Diode Forward Voltage	$V_{GS} = 0 V, I_S = 22.5 A$ (Note 2)		0.79	1.2	V
V _{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 V, I_S = 2 A$ (Note 2)		0.47	0.8	
t _{rr}	Reverse Recovery Time	-I _F = 22.5 A, di/dt = 300 A/μs		24	39	ns
Q _{rr}	Reverse Recovery Charge	$r_{\rm F} = 22.0 \text{A}, \text{avat} = 300 \text{A} \mu \text{s}$		19	34	nC

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case	(Top Source)	5.8	
$R_{ ext{ heta}JC}$	Thermal Resistance, Junction to Case	(Bottom Drain)	2.1	
$R_{ extsf{ heta}JA}$	Thermal Resistance, Junction to Ambient	(Note 1a)	42	
$R_{ extsf{ heta}JA}$	Thermal Resistance, Junction to Ambient	(Note 1b)	105	
R_{\thetaJA}	Thermal Resistance, Junction to Ambient	(Note 1c)	29	
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1d)	40	
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1e)	19	00.001
R_{\thetaJA}	Thermal Resistance, Junction to Ambient	(Note 1f)	23	°C/W
$R_{ extsf{ heta}JA}$	Thermal Resistance, Junction to Ambient	(Note 1g)	30	
$R_{ extsf{ heta}JA}$	Thermal Resistance, Junction to Ambient	(Note 1h)	79	
R_{\thetaJA}	Thermal Resistance, Junction to Ambient	(Note 1i)	17	
$R_{ extsf{ heta}JA}$	Thermal Resistance, Junction to Ambient	(Note 1j)	26	
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1k)	12	
$R_{ ext{ heta}JA}$	Thermal Resistance, Junction to Ambient	(Note 1I)	16	

NOTES:

1. R_{0JA} is determined with the device mounted on a FR-4 board using a specified pad of 2 oz copper as shown below. R_{0JC} is guaranteed by design while R_{0CA} is determined by the user's board design.



a. 42 °C/W when mounted on a 1 in² pad of 2 oz copper



b. 105 °C/W when mounted on a minimum pad of 2 oz copper

c. Still air, 20.9x10.4x12.7mm Aluminum Heat Sink, 1 in² pad of 2 oz copper
d. Still air, 20.9x10.4x12.7mm Aluminum Heat Sink, minimum pad of 2 oz copper

e. Still air, 45.2x41.4x11.7mm Aavid Thermalloy Part # 10-L41B-11 Heat Sink, 1 in² pad of 2 oz copper

f. Still air, 45.2x41.4x11.7mm Aavid Thermalloy Part # 10-L41B-11 Heat Sink, minimum pad of 2 oz copper

g. 200FPM Airflow, No Heat Sink,1 in² pad of 2 oz copper

h. 200FPM Airflow, No Heat Sink, minimum pad of 2 oz copper

i. 200FPM Airflow, 20.9x10.4x12.7mm Aluminum Heat Sink, 1 in² pad of 2 oz copper

j. 200FPM Airflow, 20.9x10.4x12.7mm Aluminum Heat Sink, minimum pad of 2 oz copper

k. 200FPM Airflow, 45.2x41.4x11.7mm Aavid Thermalloy Part # 10-L41B-11 Heat Sink, 1 in² pad of 2 oz copper


I. 200FPM Airflow, 45.2x41.4x11.7mm Aavid Thermalloy Part # 10-L41B-11 Heat Sink, minimum pad of 2 oz copper

2. Pulse Test: Pulse Width < 300 $\mu s,$ Duty cycle < 2.0%.


3. E_{AS} of 84 mJ is based on starting T_J = 25 °C, L = 1 mH, I_{AS} = 13 A, V_{DD} = 23 V, V_{GS} = 10 V. 100% test at L = 0.3 mH, I_{AS} = 20 A.

4. As an N-ch device, the negative Vgs rating is for low duty cycle pulse ocurrence only. No continuous rating is implied.


5. $I_{SD} \leq$ 22.5 A, di/dt \leq 200 A/µs, $V_{DD} \leq$ $BV_{DSS},$ Starting T_J = 25 $^oC.$



www.onsemi.com 4



FDMC2514SDC N-Channel Dual CoolTM 33 PowerTrench[®] SyncFETTM



FDMC2514SDC N-Channel Dual CoolTM 33 PowerTrench[®] SyncFETTM

Typical Characteristics (continued)

SyncFET Schottky body diode Characteristics

ON Semiconductor's SyncFET process embeds a Schottky diode in parallel with PowerTrench MOSFET. This diode exhibits similar characteristics to a discrete external Schottky diode in parallel with a MOSFET. Figure 13 shows the reverse recovery characteristic of the FDMC2514SDC.

Schottky barrier diodes exhibit significant leakage at high temperature and high reverse voltage. This will increase the power in the device.




Figure 13. FDMC2514SDC SyncFET body diode reverse recovery characteristic




Figure 14. SyncFET body diode reverse leakage versus drain-source voltage

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative