MOSFET – P-Channel, POWERTRENCH®

-30 V, -18 A, 20 mΩ

FDMS4435BZ, FDMS4435BZ-NC

V_{DS}	$R_{DS(ON)}$ MAX	I_D MAX
−30 V	20 mΩ @ −10 V	−18 A
	37 mΩ @ −4.5 V	



PQFN8 5X6, 1.27P
(Power 56)
CASE 483AE

General Description

This P-Channel MOSFET is produced using **onsemi**'s advanced POWERTRENCH process that has been especially tailored to minimize the on-state resistance. This device is well suited for Power Management and load switching applications common in Notebook Computers and Portable Battery Packs.

Features

- Max $r_{DS(on)}$ = 20 mΩ at V_{GS} = −10 V, I_D = −9.0 A
- Max $r_{DS(on)}$ = 37 mΩ at V_{GS} = −4.5 V, I_D = −6.5 A
- Extended VGSS range (−25 V) for battery applications
- High Performance Trench Technology for Extremely Low $r_{DS(on)}$
- High Power and Current Handling Capability
- HBM ESD Protection Level >7 kV Typical (Note 4)
- 100% UIL Tested
- This Device is Pb-Free, Halide Free and is RoHS Compliant

Applications

- High Side in DC-DC Buck Converters
- Notebook Battery Power Management
- Load Switch in Notebook

MARKING DIAGRAM

&Z = Assembly Plant Code
&3 = 3-Digit Date Code
&K = 2-Digits Lot Run Code
FDMS4435BZ = Specific Device Code

PIN ASSIGNMENT



ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet.

© Semiconductor Components Industries, LLC, 2011

MAXIMUM RATINGS (T_C = 25 °C unless otherwise noted)

Symbol	Parameter			Value	Unit
V_{DS}	Drain to Source Voltage			−30	V
V_{GS}	Gate to Source Voltage			±25	V
I_D	Drain Current	Continuous (Package limited)	T_C = 25 °C	−18	A
		Continuous (Silicon limited)	T_C = 25 °C	−35	
		Continuous (Note 1a)	T_A = 25 °C	−9.0	
		Pulsed		−50	
E_{AS}	Single Pulse Avalanche Energy (Note 3)			18	mJ
P_D	Power Dissipation		T_C = 25 °C	39	W
			T_A = 25 °C (Note 1a)	2.5	
T_J, T_{STG}	Operating and Storage Junction Temperature Range			−55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)

Symbol	Parameter	Ratings	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case	3.2	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	50	

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise noted)

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
BV_{DSS}	Drain to Source Breakdown Voltage	I_D = −250 μA, V_{GS} = 0 V	−30	–	–	V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I_D = −250 μA, referenced to 25 °C	–	−23	–	mV/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = −24 V, V_{GS} = 0 V	–	–	−1	μA
I_{GSS}	Gate to Source Leakage Current	V_{GS} = ±25 V, V_{DS} = 0 V	–	–	±10	μA
ON CHARACTERISTICS						
$V_{GS(th)}$	Gate to Source Threshold Voltage	V_{GS} = V_{DS}, I_D = −250 μA	−1.0	−1.9	−3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = −250 μA, referenced to 25 °C	–	6	–	mV/°C
$r_{DS(on)}$	Static Drain to Source On Resistance	V_{GS} = −10 V, I_D = −9.0 A	–	15	20	mΩ
		V_{GS} = −4.5 V, I_D = −6.5 A	–	22	37	
		V_{GS} = −10 V, I_D = −9.0 A T_J = 125 °C	–	21	28	
g_{FS}	Forward Transconductance	V_{DS} = −5 V, I_D = −9.0 A	–	25	–	S
DYNAMIC CHARACTERISTICS						
C_{iss}	Input Capacitance	V_{DS} = −15 V, V_{GS} = 0 V, f = 1 MHz	–	1540	2050	pF
C_{oss}	Output Capacitance		–	290	390	pF
C_{rss}	Reverse Transfer Capacitance		–	260	385	pF
R_g	Gate Resistance		–	5	–	Ω
SWITCHING CHARACTERISTICS						
$t_{d(on)}$	Turn-On Delay Time	V_{DD} = −15 V, I_D = −9.0 A, V_{GS} = −10 V, R_{GEN} = 6 Ω	–	9	17	ns
t_r	Rise Time		–	10	18	ns
$t_{d(off)}$	Turn-Off Delay Time		–	35	56	ns
t_f	Fall Time		–	19	33	ns
Q_g	Total Gate Charge	V_{GS} = 0 V to −10 V, V_{DD} = −15 V, I_D = −9.0 A	–	34	47	nC
Q_g	Total Gate Charge	V_{GS} = 0 V to −4.5 V, V_{DD} = −15 V, I_D = −9.0 A	–	18	25	nC
Q_{gs}	Gate to Source Charge	V_{GS} = 10 V, V_{DD} = −15 V, I_D = −9.0 A	–	5	–	nC
Q_{gd}	Gate to Drain “Miller” Charge		–	9	–	nC
DRAIN-SOURCE CHARACTERISTICS						
V_{SD}	Source to Drain Diode Forward Voltage	V_{GS} = 0 V, I_S = −1.9 A (Note 2)	–	0.75	1.2	V
		V_{GS} = 0 V, I_S = −9.0 A (Note 2)	–	0.86	1.5	
t_{rr}	Reverse Recovery Time	I_F = −9.0 A, di/dt = 100 A/μs	–	25	39	ns
Q_{rr}	Reverse Recovery Charge		–	12	21	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. $R_{\theta JA}$ is determined with the device mounted on a 1 in^2 pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user’s board design.



a. 50 °C/W when mounted on a 1 in^2 pad of 2 oz copper



b. 125 °C/W when mounted on a minimum pad of 2 oz copper

2. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.
3. E_{AS} of 18 mJ is based on starting T_J = 25 °C, L = 1 mH, I_{AS} = −6 A, V_{DD} = −27 V, V_{GS} = −10 V. 100% tested at L = 0.3 mH, I_{AS} = −8 A.
4. The diode connected between the gate and source serves only as protection against ESD. No gate overvoltage rating is implied.

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS (T_J = 25 °C, unless otherwise noted)



Figure 1. On-Region Characteristics



Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage



Figure 3. Normalized On- Resistance vs. Junction Temperature



Figure 4. On-Resistance vs. Gate to Source Voltage



Figure 5. Transfer Characteristics



Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS (T_J = 25 °C, unless otherwise noted) (continued)



Figure 7. Gate Charge Characteristics



Figure 8. Capacitance vs. Drain to Source Voltage



Figure 9. Unclamped Inductive Switching Capability



Figure 10. Maximum Continuous Drain Current vs. Case Temperature



Figure 11. Gate Leakage Current vs. Gate to Source Voltage



Figure 12. Forward Bias Safe Operating Area

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS (T_J = 25 °C, unless otherwise noted) (continued)



Figure 13. Single Pulse Maximum Power Dissipation



Figure 14. Junction-to-Ambient Transient Thermal Response Curve

PACKAGE MARKING AND ORDERING INFORMATION

Device	Device Marking	Package	Reel Size	Tape Width	Shipping†
FDMS4435BZ	FDMS4435BZ	PQFN8 5X6, 1.27P (Power 56) (Pb-Free, Halide Free)	13”	12 mm	3000 / Tape & Reel
FDMS4435BZ-NC					

† For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries.

Share Feedback
Your Opinion Matters

REVISION HISTORY

Revision	Description of Changes	Date
4	Added –NC OPN.	6/1/2026

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.

Share Feedback
Your Opinion Matters



PQFN8 5X6, 1.27P
CASE 483AE
ISSUE C

DATE 21 JAN 2022



TOP VIEW



OPTIONAL DRAFT
ANGLE MAY APPEAR
ON FOUR SIDES
OF THE PACKAGE



SIDE VIEW



DETAIL C
SCALE: 2:1



DETAIL B
SCALE: 2:1



BOTTOM VIEW



LAND PATTERN
RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: MILLIMETERS
3. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
4. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
5. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.
6. IT IS RECOMMENDED TO HAVE NO TRACES OR VIAS WITHIN THE KEEP OUT AREA.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.90	1.00	1.10
A1	0.00	-	0.05
b	0.21	0.31	0.41
b1	0.31	0.41	0.51
A3	0.15	0.25	0.35
D	4.90	5.00	5.20
D1	4.80	4.90	5.00
D2	3.61	3.82	3.96
E	5.90	6.15	6.25
E1	5.70	5.80	5.90
E2	3.38	3.48	3.78
E3	0.30 REF		
E4	0.52 REF		
e	1.27 BSC		
e/2	0.635 BSC		
e1	3.81 BSC		
e2	0.50 REF		
L	0.51	0.66	0.76
L2	0.05	0.18	0.30
L4	0.34	0.44	0.54
z	0.34 REF		
θ	0°	-	12°

DOCUMENT NUMBER:	**98AON13655G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	**PQFN8 5X6, 1.27P**		**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales