ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari





ON Semiconductor®

FDS4465-F085

P-Channel 1.8V Specified PowerTrench MOSFET

General Description

This P-Channel 1.8V specified MOSFET is a rugged gate version of ON Semiconductor's advanced PowerTrench process. It has been optimized for power management applications with a wide range of gate drive voltage (1.8V - 8V).

Applications


- Power management
- Load switch
- Battery protection




Features

• -13.5 A, -20 V. $R_{DS(ON)} = 8.5 \text{ m}\Omega \textcircled{0} \text{ V}_{GS} = -4.5 \text{ V}$ $R_{DS(ON)} = 10.5 \text{ m}\Omega \textcircled{0} \text{ V}_{GS} = -2.5 \text{ V}$ $R_{DS(ON)} = 14 \text{ m}\Omega \textcircled{0} \text{ V}_{GS} = -1.8 \text{ V}$

- Fast switching speed
- High performance trench technology for extremely low R_{DS(ON)}
- High current and power handling capability
- Qualified to AEC Q101
- RoHS Compliant





Absolute Maximum Ratings T_A=25°C unless otherwise noted

Symbol	Parameter		Ratings	Units
V _{DSS}	Drain-Source Voltage		-20	V
V _{GSS}	Gate-Source Voltage		±8	V
ID	Drain Current – Continuous	(Note 1a)	-13.5	A
	– Pulsed		-50	
P _D	Power Dissipation for Single Operation	(Note 1a)	2.5	W
		(Note 1b)	1.2	
		(Note 1c)	1	
T _J , T _{STG}	Operating and Storage Junction Temperat	ure Range	-55 to +150	°C
Therma	I Characteristics			
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	85	°C/W
R _{0JA}	Thermal Resistance, Junction-to-Ambient	(Note 1c)	125	°C/W
R _{eJC}	Thermal Resistance, Junction-to-Case	(Note 1)	25	°C/W


Package Marking and Ordering Information

 Device Marking	Device	Reel Size	Tape width	Quantity
 FDS4465	FDS4465-F085	13"	12mm	2500 units

©2012 Semiconductor Components Industries, LLC. September-2017, Rev. 2

Publication Order Number: FDS4465-F085/D


	Parameter	Test Conditions	Min	Тур	Max	Units
Off Char	acteristics					
BV _{DSS}	Drain–Source Breakdown Voltage	$V_{GS} = 0 V, I_D = -250 \mu A$	-20			V
<u>ΔBV_{DSS}</u> ΔT _J	Breakdown Voltage Temperature Coefficient	I_D = -250 µA, Referenced to 25°C		-12		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = -16 V$, $V_{GS} = 0 V$			-1	μA
I _{GSSF}	Gate–Body Leakage, Forward	$V_{GS} = 8 V$, $V_{DS} = 0 V$			100	nA
I _{GSSR}	Gate–Body Leakage, Reverse	$V_{GS} = -8 V$, $V_{DS} = 0 V$			-100	nA
On Char	acteristics (Note 2)					
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = -250 \ \mu A$	-0.4	-0.6	-1.5	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate Threshold Voltage Temperature Coefficient	I_D = -250 µA, Referenced to 25°C		3		mV/°C
R _{DS(on)}	Static Drain–Source On–Resistance	$ \begin{array}{l} V_{GS} = -4.5 \ V, I_D = -13.5 \ A \\ V_{GS} = -2.5 \ V, I_D = -12 \ A \\ V_{GS} = -1.8 \ V, I_D = -10.5 \ A \\ V_{GS} = -4.5 \ V, \ I_D = -13.5 \ A, \ T_J = 125^{\circ} C \end{array} $		6.7 8.0 9.8 9.0	8.5 10.5 14 13	mΩ
I _{D(on)}	On–State Drain Current	$V_{GS} = -4.5 \text{ V}, V_{DS} = -5 \text{ V}$	-50			Α
g _{FS}	Forward Transconductance	$V_{DS} = -5 V$, $I_D = -13.5 A$		70		S
	Characteristics					
	Input Capacitance	$V_{DS} = -10 V$, $V_{GS} = 0 V$,		8237		pF
	Output Capacitance	f = 1.0 MHz		1497	ł – –	pF
Crss	Reverse Transfer Capacitance			750		pF
						r
t _{d(on)}	Turn–On Delay Time	$V_{DD} = -10V, I_D = -1 A,$		20	36	ns
t _r	Turn–On Rise Time	$V_{GS} = -4.5 \text{ V}, R_{GEN} = 6 \Omega$		24	38	ns
t _{d(off)}	Turn–Off Delay Time	-		300	480	ns
t _f	Turn–Off Fall Time			140	224	ns
Q _g	Total Gate Charge	$V_{DS} = -10 \text{ V}, \qquad I_D = -13.5 \text{ A},$		86	120	nC
Q _{gs}	Gate–Source Charge	$V_{GS} = -4.5 V$		20		nC
Q _{gd}	Gate–Drain Charge	1		11		nC
Drain_S	ource Diode Characteristics	and Maximum Ratings				
	Maximum Continuous Drain–Source				-2.1	Α
V _{SD}	Drain–Source Diode Forward Voltage	$V_{GS} = 0 V$, $I_S = -2.1 A$ (Note 2)		-0.6	-1.2	V




Scale 1 : 1 on letter size paper

2. Pulse Test: Pulse Width < 300 μ s, Duty Cycle < 2.0%

www.onsemi.com 2



FDS4465-F085 P-Channel 1.8V Specified PowerTrench[®] MOSFET



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative