


NPN Silicon Transistor

FJPF5027



TO-220 Fullpack, 3-Lead
CASE 221AT

High Voltage and High Reliability

- High Speed Switching
- Wide SOA
- This is a Pb-Free Device

MAXIMUM RATINGS (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
V _{CBO}	Collector-Base Voltage	1100	V
V _{CEO}	Collector-Emitter Voltage	800	V
V _{EBO}	Emitter-Base Voltage	7	V
I _C	Collector Current (DC)	3	A
I _{CP}	Collector Current (Pulse)	10	A
I _B	Base Current	1.5	A
P _C	Collector Dissipation (T _C = 25°C)	40	W
T _J	Junction Temperature	150	°C
T _{STG}	Storage Temperature	-55~150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

h_{FE} CLASSIFICATION


Classification	N	R	O
h _{FE1}	10~20	15~30	20~40

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
BV _{CBO}	Collector-Base Breakdown Voltage	I _C = 1 mA, I _E = 0	1100	-	-	V
BV _{CEO}	Collector-Emitter Breakdown Voltage	I _C = 5 mA, I _B = 0	800	-	-	V
BV _{EBO}	Emitter-Base Breakdown Voltage	I _E = 1 mA, I _C = 0	7	-	-	V
V _{CEX(sus)}	Collector-Emitter Sustaining Voltage	I _C = 1.5 A, I _{B1} = -I _{B2} = 0.3 A L = 2 mH, Clamped	800	-	-	V
I _{CBO}	Collector Cut-off Current	V _{CB} = 800 V, I _E = 0	-	-	10	μA
I _{EBO}	Emitter Cut-off Current	V _{EB} = 5 V, I _C = 0	-	-	10	μA
h _{FE1} h _{FE2}	DC Current Gain	V _{CE} = 5 V, I _C = 0.2 A V _{CE} = 5 V, I _C = 1 A	10 8	-	40 -	
V _{CE(sat)}	Collector-Emitter Saturation Voltage	I _C = 1.5 A, I _B = 0.3 A	-	-	2	V
V _{BE(sat)}	Base-Emitter Saturation Voltage	I _C = 1.5 A, I _B = 0.3 A	-	-	1.5	V
C _{ob}	Output Capacitance	V _{CB} = 10 V, I _E = 0, f = 1 MHz	-	60	-	pF
f _T	Current Gain Bandwidth Product	V _{CE} = 10 V, I _C = 0.2 A	-	15	-	MHz
t _{ON}	Turn On Time	V _{CC} = 400 V, I _C = 5 I _{B1} = -2.5 I _{B2} = 2 A, R _L = 200 Ω	-	-	0.5	μs
t _{STG}	Storage Time		-	-	3	μs
t _F	Fall Time		-	-	0.3	μs

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

MARKING DIAGRAM



J5027- = Specific Device Code
O = h_{FE} Grade
A = Site Code
Y = Year
WW = Work Week
ZZ = Assembly Lot Code

ORDERING INFORMATION

Device	Package	Shipping [†]
FJPF5027OTU	TO-220 Fullpack	1000 Units / Tube

TYPICAL CHARACTERISTICS




Figure 1. Static Characteristic




Figure 2. DC Current Gain




Figure 3. Saturation Voltage




Figure 4. Saturation Voltage




Figure 5. Reverse Bias Safe Operating Area




Figure 6. Forward Bias Safe Operating Area

FJPF5027

TYPICAL CHARACTERISTICS (CONTINUED)




Figure 7. Resistive Load Switching Characteristics




Figure 8. Power Derating

MECHANICAL CASE OUTLINE


PACKAGE DIMENSIONS

ON Semiconductor®






TO-220 Fullpack, 3-Lead / TO-220F-3SG
CASE 221AT
ISSUE B

DATE 19 JAN 2021



Scale 1:1



DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.50	4.70	4.90
A1	2.56	2.76	2.96
A2	2.34	2.54	2.74
b	0.70	0.80	0.90
b2	~	~	1.47
c	0.45	0.50	0.60
D	15.67	15.87	16.07
D1	15.60	15.80	16.00
E	9.96	10.16	10.36
e	2.34	2.54	2.74
F	~	0.84	~
H1	6.48	6.68	6.88
L	12.78	12.98	13.18
L1	3.03	3.23	3.43
∅ P	2.98	3.18	3.38
∅ P1	~	1.00	~
Q	3.20	3.30	3.40

NOTES:

- A. DIMENSION AND TOLERANCE AS ASME Y14.5-2009
- B. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUCTIONS.
- C. OPTION 1 - WITH SUPPORT PIN HOLE
OPTION 2 - NO SUPPORT PIN HOLE

DOCUMENT NUMBER:	98AON67439E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-220 FULLPACK, 3-LEAD / TO-220F-3SG	PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales