

# IGBT – Power, Co-PAK N-Channel, Field Stop VII (FS7), TO247-4L 1200 V, 1.7 V, 140 A FGY4L140T120SWD

## Description

Using the novel field stop 7th generation IGBT technology and the Gen7 Diode in TO247 4-lead package, FGY4L140T120SWD offers the optimum performance with low switching and conduction losses for high-efficiency operations in various applications like Solar Inverter, UPS and ESS.

## Features

- Maximum Junction Temperature  $T_J = 175^\circ\text{C}$
- Positive Temperature Coefficient for Easy Parallel Operation
- High Current Capability
- Smooth and Optimized Switching
- Low Switching Loss
- RoHS Compliant

## Applications

- Solar Inverter
- UPS
- Energy Storage System

## MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)



Parameter	Symbol	Value	Unit
Collector-to-Emitter Voltage	$V_{CE}$	1200	V
Gate-to-Emitter Voltage	$V_{GE}$	$\pm 20$	
Transient Gate-to-Emitter Voltage		$\pm 30$	
Collector Current	$I_C$	$T_C = 25^\circ\text{C}$ (Note 1)	200
		$T_C = 100^\circ\text{C}$	140
Power Dissipation	$P_D$	$T_C = 25^\circ\text{C}$	1250
		$T_C = 100^\circ\text{C}$	625
Pulsed Collector Current	$I_{CM}$	560	A
Diode Forward Current	$I_F$	$T_C = 25^\circ\text{C}$ (Note 1)	200
		$T_C = 100^\circ\text{C}$	140
Pulsed Diode Forward Current	$I_{FM}$	560	
Operating Junction and Storage Temperature Range	$T_J, T_{stg}$	-55 to +175	$^\circ\text{C}$
Lead Temperature for Soldering Purposes	$T_L$	265	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Value limited by bond wire
2. Repetitive rating: Pulse width limited by max. junction temperature.


$BV_{CES}$	$V_{CE(SAT\_TYP)}$	$I_C$
1200 V	1.7 V	140 A

## PIN CONNECTIONS



TO-247-4LD  
CASE 340BW

## MARKING DIAGRAM



A = Assembly Location  
YWW = Date code (Year & week)  
ZZ = Assembly Lot  
Y4L140120SWD = Specific Device Code

## ORDERING INFORMATION

Device	Package	Shipping
FGY4L140T120SWD	TO-247-4LD (Pb-Free)	30 Units / Tube

# FGY4L140T120SWD

## THERMAL CHARACTERISTICS

Parameter	Symbol	Value			Unit
		Min	Typ	Max	
Thermal Resistance, Junction-to-Case for IGBT	$R_{\theta JC}$	-	0.09	0.12	°C/W
Thermal Resistance, Junction-to-Case for Diode	$R_{\theta JCD}$	-	0.15	0.2	
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	-	-	40	

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
-----------	--------	-----------------	-----	-----	-----	------

### OFF CHARACTERISTICS

Collector-to-Emitter Breakdown Voltage	$BV_{CES}$	$V_{GE} = 0\text{ V}, I_C = 1\text{ mA}$	1200	-	-	V
Breakdown Voltage Temperature Coefficient	$\frac{\Delta BV_{CES}}{\Delta T_J}$	$V_{GE} = 0\text{ V}, I_C = 9.99\text{ mA}$	-	1256	-	mV/°C
Collector-to-Emitter Cut-Off Current	$I_{CES}$	$V_{GE} = 0\text{ V}, V_{CE} = V_{CES}$	-	-	40	μA
Gate-to-Emitter Leakage Current	$I_{GES}$	$V_{GE} = \pm 20\text{ V}, V_{CE} = 0\text{ V}$	-	-	±400	nA

### ON CHARACTERISTICS

Gate-to-Emitter Threshold Voltage	$V_{GE(th)}$	$V_{GE} = V_{CE}, I_C = 140\text{ mA}$	5.6	6.5	7.4	V
Collector-to-Emitter Saturation Voltage	$V_{CE(sat)}$	$V_{GE} = 15\text{ V}, I_C = 140\text{ A}, T_J = 25^\circ\text{C}$	-	1.7	2.0	
		$V_{GE} = 15\text{ V}, I_C = 140\text{ A}, T_J = 175^\circ\text{C}$	-	2.4	-	

### DYNAMIC CHARACTERISTICS

Input Capacitance	$C_{ies}$	$V_{CE} = 30\text{ V}, V_{GE} = 0\text{ V}, f = 1\text{ MHz}$	-	13600	-	pF
Output Capacitance	$C_{oes}$		-	389	-	
Reverse Transfer Capacitance	$C_{res}$		-	53.2	-	
Total Gate Charge	$Q_g$	$V_{CE} = 600\text{ V}, V_{GE} = 15\text{ V}, I_C = 140\text{ A}$	-	426	-	nC
Gate-to-Emitter Charge	$Q_{ge}$		-	114	-	
Gate-to-Collector Charge	$Q_{gc}$		-	148	-	

### SWITCHING CHARACTERISTIC, INDUCTIVE LOAD

Turn-on Delay Time	$t_{d(on)}$	$V_{CE} = 600\text{ V}, V_{GE} = 15\text{ V}, I_C = 70\text{ A}, R_G = 4.7\ \Omega, T_J = 25^\circ\text{C}$	-	56	-	ns
Rise Time	$t_r$		-	16	-	
Turn-off Delay Time	$t_{d(off)}$		-	254.4	-	
Fall Time	$t_f$		-	65.6	-	
Turn-on Switching Loss	$E_{on}$		-	2.2	-	mJ
Turn-off Switching Loss	$E_{off}$		-	2.1	-	
Total Switching Loss	$E_{ts}$		-	4.2	-	
Turn-on Delay Time	$t_{d(on)}$	$V_{CE} = 600\text{ V}, V_{GE} = 15\text{ V}, I_C = 140\text{ A}, R_G = 4.7\ \Omega, T_J = 25^\circ\text{C}$	-	60.8	-	ns
Rise Time	$t_r$		-	27.2	-	
Turn-off Delay Time	$t_{d(off)}$		-	232	-	
Fall Time	$t_f$		-	57.6	-	
Turn-on Switching Loss	$E_{on}$		-	3.9	-	mJ
Turn-off Switching Loss	$E_{off}$		-	4.6	-	
Total Switching Loss	$E_{ts}$		-	8.5	-	

# FGY4L140T120SWD

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted) (continued)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
<b>SWITCHING CHARACTERISTIC, INDUCTIVE LOAD</b>						
Turn-on Delay Time	$t_{d(on)}$	$V_{CE} = 600\text{ V}, V_{GE} = 15\text{ V}$ $I_C = 70\text{ A } R_G = 4.7\ \Omega T_J = 175^\circ\text{C}$	-	49.6	-	ns
Rise Time	$t_r$		-	22.4	-	
Turn-off Delay Time	$t_{d(off)}$		-	305.6	-	
Fall Time	$t_f$		-	107.2	-	
Turn-on Switching Loss	$E_{on}$		-	4.8	-	mJ
Turn-off Switching Loss	$E_{off}$		-	3.0	-	
Total Switching Loss	$E_{ts}$		-	7.9	-	
Turn-on Delay Time	$t_{d(on)}$	$V_{CE} = 600\text{ V}, V_{GE} = 15\text{ V}$ $I_C = 140\text{ A } R_G = 4.7\ \Omega T_J = 175^\circ\text{C}$	-	52.8	-	ns
Rise Time	$t_r$		-	35.2	-	
Turn-off Delay Time	$t_{d(off)}$		-	280	-	
Fall Time	$t_f$		-	99.6	-	
Turn-on Switching Loss	$E_{on}$		-	8.6	-	mJ
Turn-off Switching Loss	$E_{off}$		-	7.0	-	
Total Switching Loss	$E_{ts}$		-	15.5	-	

## DIODE CHARACTERISTICS

Forward Voltage	$V_F$	$I_F = 140\text{ A}, T_J = 25^\circ\text{C}$	1.74	2.04	2.34	V
		$I_F = 140\text{ A}, T_J = 175^\circ\text{C}$	-	2.2	-	

## DIODE SWITCHING CHARACTERISTICS, INDUCTIVE LOAD

Reverse Recovery Time	$t_{rr}$	$V_R = 600\text{ V}, I_F = 70\text{ A},$ $di_F/dt = 1000\text{ A}/\mu\text{s}, T_J = 25^\circ\text{C}$	-	192.4	-	ns
Reverse Recovery Charge	$Q_{rr}$		-	4.4	-	$\mu\text{C}$
Reverse Recovery Energy	$E_{REC}$		-	1.5	-	mJ
Peak Reverse Recovery Current	$I_{RRM}$		-	45.9	-	A
Reverse Recovery Time	$t_{rr}$	$V_R = 600\text{ V}, I_F = 140\text{ A},$ $di_F/dt = 1000\text{ A}/\mu\text{s}, T_J = 25^\circ\text{C}$	-	266.9	-	ns
Reverse Recovery Charge	$Q_{rr}$		-	6.95	-	$\mu\text{C}$
Reverse Recovery Energy	$E_{REC}$		-	2.4	-	mJ
Peak Reverse Recovery Current	$I_{RRM}$		-	52.4	-	A
Reverse Recovery Time	$t_{rr}$	$V_R = 600\text{ V}, I_F = 70\text{ A},$ $di_F/dt = 1000\text{ A}/\mu\text{s}, T_J = 175^\circ\text{C}$	-	304.6	-	ns
Reverse Recovery Charge	$Q_{rr}$		-	10.6	-	$\mu\text{C}$
Reverse Recovery Energy	$E_{REC}$		-	3.9	-	mJ
Peak Reverse Recovery Current	$I_{RRM}$		-	68.7	-	A
Reverse Recovery Time	$t_{rr}$	$V_R = 600\text{ V}, I_F = 140\text{ A},$ $di_F/dt = 1000\text{ A}/\mu\text{s}, T_J = 175^\circ\text{C}$	-	431.9	-	ns
Reverse Recovery Charge	$Q_{rr}$		-	16.3	-	$\mu\text{C}$
Reverse Recovery Energy	$E_{REC}$		-	6.1	-	mJ
Peak Reverse Recovery Current	$I_{RRM}$		-	76.6	-	A

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# FGY4L140T120SWD

## TYPICAL CHARACTERISTICS




Figure 1. Output Characteristics




Figure 2. Output Characteristics




Figure 3. Output Characteristics




Figure 4. Transfer Characteristics




Figure 5. Saturation Characteristics




Figure 6. Saturation Voltage vs. Junction Temperature

# FGY4L140T120SWD

## TYPICAL CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristics




Figure 9. SOA Characteristics




Figure 10. Switching Time vs. Gate Resistance ( $T_J = 25^\circ\text{C}$ )




Figure 11. Switching Time vs. Gate Resistance ( $T_J = 175^\circ\text{C}$ )






Figure 12. Switching Time vs. Collector Current ( $T_J = 25^\circ\text{C}$ )

# FGY4L140T120SWD


## TYPICAL CHARACTERISTICS




**Figure 13. Switching Time vs. Collector Current ( $T_J = 175^\circ\text{C}$ )**




**Figure 14. Switching Loss vs. Gate Resistance**




**Figure 15. Switching Loss vs. Collector Current**



**Figure 16. Diode Forward Characteristics**



**Figure 17. Diode Reverse Recovery Current**



**Figure 18. Diode Reverse Recovery Time**

# FGY4L140T120SWD

## TYPICAL CHARACTERISTICS




Figure 19. Diode Stored Charge




Figure 20. Max Transient Thermal Impedance of IGBT






Figure 21. Max Transient Thermal Impedance of Diode




TO-247-PLUS-4L 15.80x22.54x5.00, 2.54P  
CASE 340BW  
ISSUE A

DATE 07 SEPT 2023



- NOTES:  
 A. NO INDUSTRY STANDARDS APPLIES TO THIS PACKAGE.  
 B. ALL DIMENSIONS ARE IN MILLIMETERS.  
 C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.  
 D. DRAWING CONFORMS TO ASME Y14.5-2009.

GENERIC MARKING DIAGRAM\*



XXXX = Specific Device Code  
 A = Assembly Location  
 Y = Year  
 WW = Work Week  
 ZZ = Assembly Lot Code

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "μ", may or may not be present. Some products may not follow the Generic Marking.

	MILLIMETERS		
	MIN	NOM	MAX
A	4.80	5.00	5.20
A1	2.21	2.41	2.61
A2	1.80	2.00	2.20
A3	1.00	1.10	1.20
b	1.07	1.20	1.33
b1	0.57	0.70	0.83
b2	1.20	1.40	1.60
b3	2.47	2.67	2.87
c	0.50	0.60	0.70
D	22.34	22.54	22.74
D1	16.00	16.20	16.40
D2	0.96	1.16	1.36
D3	1.52	1.72	1.92
e	2.54BSC		
e1	2.79BSC		
e2	5.08BSC		
E	15.60	15.80	16.00
E1	13.10	13.30	13.50
L	18.12	18.42	18.72
L1	2.52	2.72	2.92
R	1.90	2.00	2.10
N	2.75	2.95	3.15

DOCUMENT NUMBER:	98AON51847H	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-247-PLUS-4L 15.80x22.54x5.00, 2.54P	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

