ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari




N Semiconductor® KA317 / LM317 3-Terminal Positive Adjustable Regulator

Features

- Output-Current In Excess of 1.5 A
- Output-Adjustable Between 1.2 V and 37 V
- Internal Thermal Overload Protection
- Internal Short-Circuit Current Limiting
- Output-Transistor Safe Operating Area Compensation
- TO-220 Package

Description


This monolithic integrated circuit is an adjustable 3-terminal positive-voltage regulator designed to supply more than 1.5 A of load current with an output voltage adjustable over a 1.2 V to 37 V range. It employs internal current limiting, thermal shutdown, and safe area compensation.



Ordering Information

Product Number	Package	Packing Method	Operating Temperature
LM317T	TO-220 (Single Gauge)	Rail	0°C to +125°C
KA317TU	TO-220 (Dual Gauge)	Rail	0°C to +125°C

Block Diagram



KA317 / LM317 — 3-Terminal Positive Adjustable Regulator

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at $T_A = 25^{\circ}$ C unless otherwise noted.

Symbol	Parameter	Value	Unit	
V _I - V _O	Input-Output Voltage Differential	40	V	
T _{LEAD}	Lead Temperature	230	°C	
TJ	Operating Junction Temperature Range	0 to +125	°C	
T _{STG}	Storage Temperature Range	-65 to +125	°C	
$\Delta V_O / \Delta T$	Temperature Coefficient of Output Voltage	±0.02	%/°C	

Thermal Characteristics

Values are at $T_A = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Value	Units
PD	Power Dissipation	Internally Limited	W
$R_{ extsf{ heta}JA}$	Thermal Resistance, Junction to Ambient	80	°C/W
$R_{ extsf{ heta}JC}$	Thermal Resistance, Junction to Case	5	°C/W

Electrical Characteristics


 V_I - V_O = 5 V, I_O = 0.5 A, 0°C \leq $T_J \leq$ +125°C, I_{MAX} = 1.5 A, P_{DMAX} = 20 W, unless otherwise specified.

Symbol	Parameter	Conditions		Min.	Тур.	Max.	Unit
R _{LINE}	Line Regulation ⁽¹⁾	$T_A = +25^{\circ}C, 3 V \le V_I - V_O \le 40 V$			0.01	0.04	— %/ V
	Line Regulation (*)	$3 V \le V_1 - V_0 \le 40 V$			0.02	0.07	
R _{LOAD}	Load Regulation ⁽¹⁾	$T_A = +25^{\circ}C,$ 10mA $\leq I_O \leq I_{MAX}$	V _O < 5 V		18	25	mV
			$V_{O} \ge 5 V$		0.4	0.5	%/V _C
		$10 \text{ mA} \le I_O \le I_{MAX}$	V _O < 5 V		40	70	mV
			$V_{O} \ge 5 V$		0.8	1.5	%/V _C
I _{ADJ}	Adjustable Pin Current				46	100	μA
ΔI_{ADJ}	Adjustable Pin Current Change	$\begin{array}{c} 3 \ V \leq V_{I} - V_{O} \leq 40 \ V, \\ 10 \ mA \leq I_{O} \leq I_{MAX}, \ P_{D} \leq P_{MAX} \end{array}$			2.0	5.0	μA
V _{REF}	Reference Voltage	$\begin{array}{l} 3 \text{ V} \leq \text{V}_{\text{IN}} \text{ - } \text{V}_{\text{O}} \leq 40 \text{ V}, \\ 10 \text{ mA} \leq \text{I}_{\text{O}} \leq \text{I}_{\text{MAX}}, \text{P}_{\text{D}} \leq \text{P}_{\text{MAX}} \end{array}$		1.20	1.25	1.30	V
STT	Temperature Stability	· · · ·			0.7		%/V _C
I _{L(MIN)}	Minimum Load Current to Maintain Regulation	V _I - V _O = 40 V			3.5	12.0	mA
I _{O(MAX)}	Maximum Output Current	T _A = 25°C	$V_{I} - V_{O} \le 15 V,$ $P_{D} \le P_{MAX}$	1.5	2.2		A
			$V_{I} - V_{O} \le 40 \text{ V},$ $P_{D} \le P_{MAX}$		0.3		
e _N	RMS Noise,% of V _{OUT}	$T_A = +25^{\circ}C$, 10 Hz $\leq f \leq 10$ kHz			0.003	0.010	%/V _C
RR	Ripple Rejection ⁽²⁾	V _O = 10 V,	without C _{ADJ}		60		dB
		f = 120 Hz	$C_{ADJ} = 10 \mu F$	66	75		
ST	Long-Term Stability, T _J = T _{HIGH}	$T_A = +25^{\circ}C$ for End Point Measurements, 1000 HR			0.3	1.0	%


Notes:

1. Load and line regulation are specified at constant junction temperature. Change in V_D due to heating effects must be taken into account separately. Pulse testing with low duty is used ($P_{MAX} = 20$ W).

2. C_{ADJ} , when used, is connected between the adjustment pin and ground.



Typical Application⁽³⁾




 $V_0 = 1.25 V (1 + R_2 / R_1) + I_{ADJ}R_2$

Figure 7. Typical Application

Note:

3. C_I is required when the regulator is located an appreciable distance from power supply filter. C_O is not needed for stability; however, it does improve transient response. Since I_{ADJ} is controlled to less than 100 μ A, the error associated with this term is negligible in most applications.



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative