


NPN Triple Diffused Planar Silicon Transistor

KSC5338D



TO-220-3LD
CASE 340AT

Features

- High Voltage Power Switch Switching Application
- Wide Safe Operating Area
- Built-in Free-Wheeling Diode
- Suitable for Electronic Ballast Application
- Small Variance in Storage Time
- Package Choice: TO-220
- This is a Pb-Free and a Halide Free Device

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise noted.)

Symbol	Parameter	Value	Unit
V _{CB0}	Collector-Base Voltage	1000	V
V _{CEO}	Collector-Emitter Voltage	450	V
V _{EBO}	Emitter-Base Voltage	12	V
I _C	Collector Current (DC)	5	A
I _{CP}	Collector Current (Pulse) (Note 1)	10	A
I _B	Base Current (DC)	2	A
I _{BP}	Base Current (Pulse) (Note 1)	4	A
P _C	Power Dissipation (T _C = 25°C)	75	W
T _J	Junction Temperature	150	°C
T _{STG}	Storage Temperature	-55 to 150	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Pulse Test: Pulse Width = 5 ms, Duty Cycle ≤ 10%

THERMAL CHARACTERISTICS

Symbol	Characteristic	Value	Unit
R _{θjc}	Thermal Resistance	Junction to Case	1.65 °C/W
		Junction to Ambient	62.5 °C/W
T _L	Maximum Lead Temperature for Soldering	270	°C


MARKING DIAGRAM



1. Base
2. Collector
3. Emitter

YWW = Date Code (Year and Week)
ZZ = Lot Code
C5338D = Specific Device Code

EQUIVALENT CIRCUIT



ORDERING INFORMATION

Device	Package	Shipping
KSC5338D	TO-220-3LD	1200 Units / Bulk
KSC5338DTU	(Pb-Free, Halide Free)	1000 Units / Tube

KSC5338D

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units	
BV _{CBO}	Collector-Base Breakdown Voltage	I _C = 1 mA, I _E = 0	1000	-	-	V	
BV _{CEO}	Collector-Emitter Breakdown Voltage	I _C = 5 mA, I _B = 0	450	-	-	V	
BV _{EBO}	Emitter-Base Breakdown Voltage	I _E = 1 mA, I _C = 0	12	-	-	V	
I _{CBO}	Collector Cut-off Current	V _{CB} = 800 V, I _E = 0	-	-	10	μA	
I _{CES}	Collector Cut-off Current	V _{CEs} = 1000 V, I _{EB} = 0	T _a = 25°C	-	-	100	μA
			T _a = 125°C	-	-	500	μA
I _{CEO}	Collector Cut-off Current	V _{CE} = 450 V, I _B = 0	T _a = 25°C	-	-	100	μA
			T _a = 125°C	-	-	500	μA
I _{EBO}	Emitter Cut-off Current	V _{EB} = 10 V, I _C = 0	-	-	10	μA	
h _{FE}	DC Current Gain	V _{CE} = 1 V, I _C = 0.8 A	T _a = 25°C	15	25	-	
			T _a = 125°C	10	14	-	
		V _{CE} = 1 V, I _C = 2 A	T _a = 25°C	6	9	-	
			T _a = 125°C	4	6	-	
		V _{CE} = 2.5 V, I _C = 1 A	T _a = 25°C	18	25	-	
			T _a = 125°C	14	18	-	
V _{CE(sat)}	Collector-Emitter Saturation Voltage	I _C = 0.8 A, I _B = 0.08 A	T _a = 25°C	-	0.35	0.5	V
			T _a = 125°C	-	0.55	0.75	V
		I _C = 2 A, I _B = 0.4 A	T _a = 25°C	-	0.47	0.75	V
			T _a = 125°C	-	0.9	1.1	V
		I _C = 0.8 A, I _B = 0.04 A	T _a = 25°C	-	0.9	1.5	V
			T _a = 125°C	-	1.8	2.5	V
		I _C = 1 A, I _B = 0.2 A	T _a = 25°C	-	0.22	0.5	V
			T _a = 125°C	-	0.3	0.6	V
V _{BE(sat)}	Base-Emitter Saturation Voltage	I _C = 0.8 A, I _B = 0.08 A	T _a = 25°C	-	0.8	1.0	V
			T _a = 125°C	-	0.65	0.9	V
		I _C = 2 A, I _B = 0.4 A	T _a = 25°C	-	0.9	1.0	V
			T _a = 125°C	-	0.8	0.9	V
C _{ib}	Input Capacitance	V _{EB} = 10 V, I _C = 0.5 A, f = 1 MHz	-	550	750	pF	
C _{ob}	Output Capacitance	V _{CB} = 10 V, I _E = 0, f = 1 MHz	-	60	100	pF	
f _T	Current Gain Bandwidth Product	I _C = 0.5 A, V _{CE} = 10 V	-	11	-	MHz	
V _F	Diode Forward Voltage	I _F = 1 A, I _C = 1 mA, I _E = 0	T _a = 25°C	-	0.86	1.3	V
			T _a = 125°C	-	0.79	-	V
		I _F = 2 A	T _a = 25°C	-	0.95	1.5	V
			T _a = 125°C	-	0.88	-	V
t _{fr}	Diode Forward Recovery Time (di/dt = 10 A/μs)	I _F = 0.4 A	-	460	-	ns	
		I _F = 1 A	-	360	-		
		I _F = 2 A	-	325	-		
V _{CE(DSAT)}	Dynamic Saturation Voltage	I _C = 1 A, I _{B1} = 100 mA V _{CC} = 300 V at 1 μs	T _a = 25°C	-	8	-	V
			T _a = 125°C	-	15	-	V
		I _C = 1 A, I _{B1} = 100 mA V _{CC} = 300 V at 3 μs	T _a = 25°C	-	2.9	-	V
			T _a = 125°C	-	8	-	V
		I _C = 2 A, I _{B1} = 400 mA V _{CC} = 300 V at 1 μs	T _a = 25°C	-	9	-	V
			T _a = 125°C	-	17	-	V
		I _C = 2 A, I _{B1} = 400 mA V _{CC} = 300 V at 3 μs	T _a = 25°C	-	1.9	-	V
			T _a = 125°C	-	8.5	-	V

KSC5338D

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted) (continued)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units	
RESISTIVE LOAD SWITCHING (D.C. \leq 10%, Pulse Width = 40 μs)							
t_{ON}	Turn On Time	$I_C = 2.5 \text{ A}$, $I_{B1} = 500 \text{ mA}$, $I_{B2} = -1 \text{ A}$, $V_{CC} = 250 \text{ V}$, $R_L = 100 \Omega$	-	500	750	ns	
t_{STG}	Storage Time		1.2	-	1.5	μs	
t_F	Fall Time		-	100	200	ns	
t_{ON}	Turn On Time	$I_C = 2 \text{ A}$, $I_{B1} = 400 \text{ mA}$, $I_{B2} = -1 \text{ A}$, $V_{CC} = 300 \text{ V}$, $R_L = 150 \Omega$	$T_a = 25^\circ\text{C}$	-	100	150	ns
			$T_a = 125^\circ\text{C}$	-	150	-	ns
t_{STG}	Storage Time		$T_a = 25^\circ\text{C}$	-	1.4	2.2	μs
			$T_a = 125^\circ\text{C}$	-	1.7	-	μs
t_F	Fall Time		$T_a = 25^\circ\text{C}$	-	90	150	ns
			$T_a = 125^\circ\text{C}$	-	150	-	ns
t_{ON}	Turn On Time	$I_C = 2.5 \text{ A}$, $I_{B1} = 500 \text{ mA}$, $I_{B2} = -5 \text{ mA}$, $V_{CC} = 300 \text{ V}$, $R_L = 120 \Omega$	$T_a = 25^\circ\text{C}$	-	120	150	ns
			$T_a = 125^\circ\text{C}$	-	150	-	ns
t_{STG}	Storage Time		$T_a = 25^\circ\text{C}$	1.8	-	2.1	μs
			$T_a = 125^\circ\text{C}$	-	2.6	-	μs
t_F	Fall Time		$T_a = 25^\circ\text{C}$	-	110	150	ns
			$T_a = 125^\circ\text{C}$	-	160	-	ns

INDUCTIVE LOAD SWITCHING ($V_{CC} = 15 \text{ V}$)

t_{STG}	Storage Time	$I_C = 2.5 \text{ A}$, $I_{B1} = 500 \text{ mA}$, $I_{B2} = -0.5 \text{ A}$, $V_Z = 350 \text{ V}$, $L_C = 300 \mu\text{H}$	$T_a = 25^\circ\text{C}$	-	1.9	2.2	μs
			$T_a = 125^\circ\text{C}$	-	2.4	-	μs
t_F	Fall Time		$T_a = 25^\circ\text{C}$	-	160	200	ns
			$T_a = 125^\circ\text{C}$	-	330	-	ns
t_C	Cross-over Time		$T_a = 25^\circ\text{C}$	-	350	500	ns
			$T_a = 125^\circ\text{C}$	-	750	-	ns
t_{STG}	Storage Time	$I_C = 2 \text{ A}$, $I_{B1} = 400 \text{ mA}$, $I_{B2} = -0.4 \text{ A}$, $V_Z = 300 \text{ V}$, $L_C = 200 \mu\text{H}$	$T_a = 25^\circ\text{C}$	1.95	-	2.25	μs
			$T_a = 125^\circ\text{C}$	-	2.9	-	μs
t_F	Fall Time		$T_a = 25^\circ\text{C}$	-	120	150	ns
			$T_a = 125^\circ\text{C}$	-	270	-	ns
t_C	Cross-over Time		$T_a = 25^\circ\text{C}$	-	300	450	ns
			$T_a = 125^\circ\text{C}$	-	700	-	ns
t_{STG}	Storage Time	$I_C = 1 \text{ A}$, $I_{B1} = 100 \text{ mA}$, $I_{B2} = -0.5 \text{ A}$, $V_Z = 300 \text{ V}$, $L_C = 200 \mu\text{H}$	$T_a = 25^\circ\text{C}$	-	0.6	0.8	μs
			$T_a = 125^\circ\text{C}$	-	1.0	-	μs
t_F	Fall Time		$T_a = 25^\circ\text{C}$	-	70	-	ns
			$T_a = 125^\circ\text{C}$	-	110	-	ns
t_C	Cross-over Time		$T_a = 25^\circ\text{C}$	-	80	130	ns
			$T_a = 125^\circ\text{C}$	-	170	-	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS




Figure 1. Static Characteristic




Figure 2. DC Current Gain




Figure 3. DC Current Gain




Figure 4. Collector-Emitter Saturation Voltage




Figure 5. Collector-Emitter Saturation Voltage




Figure 6. Base-Emitter Saturation Voltage

TYPICAL CHARACTERISTICS (continued)




Figure 7. Base-Emitter Saturation Voltage




Figure 8. Collector Output Capacitance




Figure 9. Forward Recovery Time




Figure 10. Switching Time




Figure 11. Induction Storage Time




Figure 12. Inductive Crossover Time

TYPICAL CHARACTERISTICS (continued)




Figure 13. Inductive Fall Time




Figure 14. Safe Operating Area




Figure 15. Reverse Bias Safe Operating




Figure 16. Power Derating





Figure 17. RBSOA Saturation

MECHANICAL CASE OUTLINE

PACKAGE DIMENSIONS


ON Semiconductor®



Scale 1:1

TO-220-3LD CASE 340AT ISSUE A

DATE 03 OCT 2017



- NOTES:
- A) REFERENCE JEDEC, TO-220, VARIATION AB
 - B) ALL DIMENSIONS ARE IN MILLIMETERS.
 - C) DIMENSIONS COMMON TO ALL PACKAGE SUPPLIERS EXCEPT WHERE NOTED [].
 - D) LOCATION OF MOLDED FEATURE MAY VARY (LOWER LEFT CORNER, LOWER CENTER AND CENTER OF THE PACKAGE)
 - E) DOES NOT COMPLY JEDEC STANDARD VALUE.
 - F) "A1" DIMENSIONS AS BELOW:
 SINGLE GAUGE = 0.51 - 0.61
 DUAL GAUGE = 1.10 - 1.45
 - G) PRESENCE IS SUPPLIER DEPENDENT
 - H) SUPPLIER DEPENDENT MOLD LOCKING HOLES IN HEATSINK.

DOCUMENT NUMBER:	98AON13818G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-220-3LD	PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales