

# Surface Mount Schottky Power Rectifier SMA Power Surface Mount Package

## MBRA340, NRVBA340, NRVBA340N

Employing the Schottky Barrier principle in a large area metal-to-silicon power diode. State of the art geometry features epitaxial construction with oxide passivation and metal overlay contact. Ideally suited for low voltage, high frequency rectification, or as free wheeling and polarity diodes in surface mount applications where compact size and weight are critical to the system.

### Features

- Small Compact Surface Mountable Package with J-Bent Leads
- Rectangular Package for Automated Handling
- Highly Stable Oxide Passivated Junction
- Very Low Forward Voltage Drop
- Guardring for Stress Protection
- NRVBA Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable\*
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant


### Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 70 mg (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Polarity: Cathode Lead Indicated by Polarity Band
- ESD Ratings:
  - ♦ Machine Model = C
  - ♦ Human Body Model = 3B
- Device Meets MSL 1 Requirements

## SCHOTTKY BARRIER RECTIFIER 3.0 AMPERES 40 VOLTS



SMA  
CASE 403D  
STYLE 1



### MARKING DIAGRAM



A34 = Device Code  
 A = Assembly Location\*\*  
 Y = Year  
 WW = Work Week  
 ■ = Pb-Free Package

(Note: Microdot may be in either location)

\*\*The Assembly Location code (A) is front side optional. In cases where the Assembly Location is stamped in the package bottom (molding ejecter pin), the front side assembly code may be blank.

### ORDERING INFORMATION

| Device                                                         | Package          | Shipping <sup>†</sup>  |
|----------------------------------------------------------------|------------------|------------------------|
| MBRA340T3G<br>NRVBA340T3G<br>NRVBA340T3G-VF01<br>NRVBA340NT3G* | SMA<br>(Pb-Free) | 5,000 /<br>Tape & Reel |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

# MBRA340, NRVBA340, NRVBA340N

## MAXIMUM RATINGS

| Rating                                                                                                      | Symbol                          | Value       | Unit                   |
|-------------------------------------------------------------------------------------------------------------|---------------------------------|-------------|------------------------|
| Peak Repetitive Reverse Voltage<br>Working Peak Reverse Voltage<br>DC Blocking Voltage                      | $V_{RRM}$<br>$V_{RWM}$<br>$V_R$ | 40          | V                      |
| Average Rectified Forward Current<br>(At Rated $V_R$ , $T_L = 100^\circ\text{C}$ )                          | $I_O$                           | 3.0         | A                      |
| Non-Repetitive Peak Surge Current<br>(Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz) | $I_{FSM}$                       | 100         | A                      |
| Storage/Operating Case Temperature                                                                          | $T_{stg}, T_C$                  | -55 to +150 | $^\circ\text{C}$       |
| Operating Junction Temperature (Note 1)                                                                     | $T_J$                           | -55 to +150 | $^\circ\text{C}$       |
| Voltage Rate of Change<br>(Rated $V_R$ , $T_J = 25^\circ\text{C}$ )                                         | $dv/dt$                         | 10,000      | $\text{V}/\mu\text{s}$ |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The heat generated must be less than the thermal conductivity from Junction-to-Ambient:  $dP_D/dT_J < 1/R_{\theta JA}$ .

## THERMAL CHARACTERISTICS

| Characteristic                                    | Symbol          | Value | Unit                      |
|---------------------------------------------------|-----------------|-------|---------------------------|
| Thermal Resistance – Junction-to-Lead (Note 2)    | $R_{\theta JL}$ | 15    | $^\circ\text{C}/\text{W}$ |
| Thermal Resistance – Junction-to-Ambient (Note 2) | $R_{\theta JA}$ | 81    | $^\circ\text{C}/\text{W}$ |

2. Mounted on 2" Square PC Board with 1" Square Total Pad Size, PC Board FR4.

## ELECTRICAL CHARACTERISTICS

| Characteristic                                                              | Symbol | Value                    |                           | Unit  |
|-----------------------------------------------------------------------------|--------|--------------------------|---------------------------|-------|
| Maximum Instantaneous Forward Voltage (Note 3)<br>( $I_F = 3.0 \text{ A}$ ) | $V_F$  | $T_J = 25^\circ\text{C}$ | $T_J = 100^\circ\text{C}$ | Volts |
|                                                                             |        | 0.450                    | 0.390                     |       |
| Maximum Instantaneous Reverse Current<br>( $V_R = 40 \text{ V}$ )           | $I_R$  | $T_J = 25^\circ\text{C}$ | $T_J = 100^\circ\text{C}$ | mA    |
|                                                                             |        | 0.3                      | 15                        |       |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Pulse Test: Pulse Width  $\leq 250 \mu\text{s}$ , Duty Cycle  $\leq 2.0\%$ .

## TYPICAL CHARACTERISTICS




Figure 1. Typical Forward Voltage




Figure 2. Maximum Forward Voltage

# MBRA340, NRVBA340, NRVBA340N




Figure 3. Typical Reverse Current




Figure 4. Maximum Reverse Current




Figure 5. Current Derating




Figure 6. Forward Power Dissipation




Figure 7. Capacitance




Figure 8. Typical Operating Temperature Derating

# MBRA340, NRVBA340, NRVBA340N




Figure 9. Thermal Response, Junction-to-Ambient (min pad)




Figure 10. Thermal Response, Junction to Ambient (1 inch pad)




STYLE 1    STYLE 2

SCALE 1:1

### SMA CASE 403D ISSUE J



DATE 22 OCT 2021



#### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCHES
3. DIMENSION  $b$  SHALL BE MEASURED WITHIN DIMENSION  $L$ .


| DIM   | MILLIMETERS |      |      | INCHES |       |       |
|-------|-------------|------|------|--------|-------|-------|
|       | MIN.        | NOM. | MAX. | MIN.   | NOM.  | MAX.  |
| A     | 1.97        | 2.10 | 2.20 | 0.078  | 0.083 | 0.087 |
| A1    | 0.05        | 0.10 | 0.20 | 0.002  | 0.004 | 0.008 |
| $b$   | 1.27        | 1.45 | 1.63 | 0.050  | 0.057 | 0.064 |
| c     | 0.15        | 0.28 | 0.41 | 0.006  | 0.011 | 0.016 |
| D     | 2.29        | 2.60 | 2.92 | 0.090  | 0.103 | 0.115 |
| E     | 4.06        | 4.32 | 4.57 | 0.160  | 0.170 | 0.180 |
| $H_E$ | 4.83        | 5.21 | 5.59 | 0.190  | 0.205 | 0.220 |
| L     | 0.76        | 1.14 | 1.52 | 0.030  | 0.045 | 0.060 |



STYLE 1:  
PIN 1. CATHODE (POLARITY BAND)  
2. ANODE

STYLE 2:  
NO POLARITY

#### GENERIC MARKING DIAGRAM\*




STYLE 1

STYLE 2

XXXX = Specific Device Code  
A = Assembly Location  
Y = Year  
WW = Work Week  
▪ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.



#### RECOMMENDED MOUNTING FOOTPRINT

|                         |                    |                                                                                                                                                                                  |
|-------------------------|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON04079D</b> | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SMA</b>         | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)