

MOSFET – Power, Single MCPH6, P-Channel

-12 V, -6.0 A, 35 mΩ

MCH6353

Features


- ON-Resistance $R_{DS(on)}$ 1 = 29 mΩ (typ)
- 1.5 V Drive
- Protection Diode in
- This Device is Pb-Free and Halogen Free and RoHS Compliant

ABSOLUTE MAXIMUM RATINGS (Ta = 25°C)


Parameter	Symbol	Conditions	Value	Unit
Drain-to-Source Voltage	V_{DSS}		-12	V
Gate-to-Source Voltage	V_{GSS}		±10	V
Drain Current (DC)	I_D		-6.0	A
Drain Current (Pulse)	I_{DP}	$PW \leq 10 \mu s$, duty cycle $\leq 1\%$	-24	A
Allowable Power Dissipation	P_D	When mounted on ceramic substrate (1500 mm ² × 0.8 mm)	1.4	W
Channel Temperature	Tch		150	°C
Storage Temperature	Tstg		-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

V_{DSS}	$R_{DS(on)}$ MAX	I_D MAX
-12 V	35 mΩ @ -4.5 V	-6.0 A
	48 mΩ @ -2.5 V	
	78 mΩ @ -1.8 V	
	140 mΩ @ -1.5 V	




ELECTRICAL CONNECTION P-CHANNEL



**SC-88FL / MCPH6
CASE 419AS**

MARKING DIAGRAM



- XX = Specific Device Code, NC
M = Date Code
Left Side = Jan to Jun
Right Side = Jul to Dec
A = Location Code

ORDERING INFORMATION

Device	Package	Shipping†
MCH6353-TL-W	MCPH6 SC-88, SOT-363 (Pb-Free, Halogen Free)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

MCH6353

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition	Value			Unit
			Min	Typ	Max	
Drain to Source Breakdown Voltage	V _{(BR)DSS}	I _D = -1 mA, V _{GS} = 0 V	-12	-	-	V
Zero-Gate Voltage Drain Current	I _{DSS}	V _{DS} = -12 V, V _{GS} = 0 V	-	-	-1	μA
Gate to Source Leakage Current	I _{GSS}	V _{GS} = ±8 V, V _{DS} = 0 V	-	-	±1	μA
Cutoff Voltage	V _{GS(off)}	V _{DS} = -6 V, I _D = -1 mA	-0.4	-	-1.4	V
Forward Transfer Admittance	y _{fs}	V _{DS} = -6 V, I _D = -3 A	-	11	-	S
Static Drain to Source On-State Resistance	R _{DS(on)1}	I _D = -3 A, V _{GS} = -4.5 V	-	29	35	mΩ
	R _{DS(on)2}	I _D = -1.5 A, V _{GS} = -2.5 V	-	38	48	mΩ
	R _{DS(on)3}	I _D = -0.5 A, V _{GS} = -1.8 V	-	52	78	mΩ
	R _{DS(on)4}	I _D = -0.5 A, V _{GS} = -1.5 V	-	70	140	mΩ
Input Capacitance	C _{iss}	V _{DS} = -6 V, f = 1 MHz	-	1250	-	pF
Output Capacitance	C _{oss}		-	160	-	pF
Reverse Transfer Capacitance	C _{rss}		-	150	-	pF
Turn-ON Delay Time	t _{d(on)}	See specified Test Circuit	-	8.4	-	ns
Rise Time	t _r		-	48	-	ns
Turn-OFF Delay Time	t _{d(off)}		-	165	-	ns
Fall Time	t _f		-	68	-	ns
Total Gate Charge	Q _g	V _{DS} = -6 V, V _{GS} = -4.5 V, I _D = -6.0 A	-	12	-	nC
Gate to Source Charge	Q _{gs}		-	1.7	-	nC
Gate to Drain "Miller" Charge	Q _{gd}		-	2.1	-	nC
Diode Forward Voltage	V _{SD}	I _S = -6 A, V _{GS} = 0 V	-	-0.9	-1.2	V

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.










Figure 1. Switching Time Test Circuit

TYPICAL CHARACTERISTICS

Figure 2. $I_D - V_{DS}$ Figure 3. $I_D - V_{GS}$ Figure 4. $R_{DS(on)} - V_{GS}$ Figure 5. $R_{DS(on)} - T_a$ Figure 6. $|y_{fs}| - I_D$ Figure 7. $I_S - V_{DS}$

TYPICAL CHARACTERISTICS (CONTINUED)




Figure 8. S/W Time - I_D




Figure 9. C_{iss} , C_{oss} , C_{rss} - V_{DS}




Figure 10. Q_g - V_{GS}




Figure 11. ASO







Figure 12. P_D - T_a


SC-88FL / MCPH6
CASE 419AS
ISSUE A


DATE 28 SEP 2022




TOP VIEW



SIDE VIEW



FRONT VIEW




BOTTOM VIEW

NOTES:

1. NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
2. ALL DIMENSIONS ARE IN MILLIMETERS.
3. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND THE BAR PROTRUSIONS.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.80	0.85	0.90
A1	0.00	---	0.02
b	0.25	0.30	0.40
c	0.12	0.15	0.25
D	1.94	2.00	2.06
E	1.54	1.60	1.66
He	2.05	2.10	2.15
L	0.19	0.25	0.31
L1	0.00	0.07	0.12
e	0.65 BSC		

GENERIC
MARKING DIAGRAM*


XXX = Specific Device Code
 M = Date Code
 ■ = Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON65646E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	SC-88FL / MCPH6	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales