

Ultra High Accuracy, Low I_q, 500 mA Low Dropout Regulator

NCP3334A

The NCP3334A is a high performance, low dropout regulator with accuracy of $\pm 0.9\%$ over line and load. This device features ultra-low quiescent current and noise which encompasses all necessary characteristics demanded by today's consumer electronics. This unique device is guaranteed to be stable without a minimum load current requirement and stable with any type of capacitor as small as 1.0 μF . The NCP3334A offers reverse bias protection. The device is available in a small 3x3 mm WDFN8 package.

Features

- High Accuracy Over Line and Load ($\pm 0.9\%$ at 25°C)
- Ultra-Low Dropout Voltage at Full Load
- No Minimum Output Current Required for Stability
- Low Noise
- Low Shutdown Current
- Reverse Bias Protected
- 2.6 V to 12 V Supply Range
- Thermal Shutdown Protection
- Current Limitation
- Requires Only 1.0 μF Output Capacitance for Stability
- Stable with Any Type of Capacitor (including MLCC)
- These are Pb-Free Devices


Applications

- Telecom Applications
- Cellular Base Stations
- Camcoders and Cameras
- Networking Systems, DSL/Cable Modems
- Cable Set-Top Box
- MP3/CD Players
- DSP Supply
- Displays and Monitors



WDFN8
MT SUFFIX
CASE 511CF


MARKING DIAGRAM



3334A = Specific Device Code
A = Assembly Location
L = Wafer Lot
Y = Year
W = Work Week
▪ = Pb-Free Package

(Note: Microdot may be in either location)

PIN CONNECTIONS



(Top View)

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 7 of this data sheet.

NCP3334A




Figure 1. Typical Adjustable Version Application Schematic

NCP3334A

PIN FUNCTION DESCRIPTION

| Pin No. | Pin Name | Description |
|---------|------------------|--|
| 1, 2 | V _{out} | Regulated output voltage. Bypass to ground with C _{out} ≥ 1.0 μF. |
| 3 | FB | Adjustable pin; reference voltage = 1.178 V. |
| 4 | NC | Not Connected |
| 5 | GND | Power Supply Ground |
| 6 | SD | Shutdown pin. Pulling this pin Low turns on the regulator |
| 7, 8 | V _{in} | Power Supply Input Voltage |
| – | EPAD | Exposed thermal pad should be connected to ground or V _{in} . The EPAD is electrically isolated from the die. |

MAXIMUM RATINGS

| Rating | Symbol | Value | Unit |
|----------------------------|------------------|---------------------------------------|------|
| Input Voltage | V _{in} | –0.3 to +16 | V |
| Output Voltage | V _{out} | –0.3 to V _{in} +0.3 or 10 V* | V |
| Shutdown Pin Voltage | V _{sh} | –0.3 to +16 | V |
| Junction Temperature Range | T _J | –40 to +150 | °C |
| Storage Temperature Range | T _{stg} | –65 to +150 | °C |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

NOTE: This device series contains ESD protection and exceeds the following tests:

Human Body Model (HBM) JESD 22–A114–B

*Which ever is less. Reverse bias protection feature valid only if V_{out} – V_{in} ≤ 7 V.

THERMAL CHARACTERISTICS

| Characteristic | Test Conditions (Typical Value) | | Unit |
|----------------|---------------------------------|-----------------------|------|
| | Min Pad Board | 1" Pad Board (Note 1) | |

WDFN 8

| | | | |
|----------------------|-----|----|------|
| Junction-to-Air, θJA | 220 | 48 | °C/W |
|----------------------|-----|----|------|

1. As mounted on 4–Layer FR4 Substrate of a specified copper area of 2 oz copper traces in accordance with JEDEC 51.7.

NCP3334A

ELECTRICAL CHARACTERISTICS – Adjustable

($V_{out} = 1.178$ V typical, $V_{in} = 6.0$ V, $T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$, $C_{in} = C_{out} = 1$ μF , unless otherwise noted, Note 2, 3, 4)

| Characteristic | Symbol | Min | Typ | Max | Unit |
|---|--|----------------|--|--|---|
| Reference Voltage Accuracy $V_{in} = V_{outnom} + 0.4$ V to 11 V, $I_{load} = 0.1$ mA to 500 mA, $T_J = 25^{\circ}\text{C}$ | V_{ref} | -0.9% 1.167 | 1.178 | +0.9% 1.189 | V |
| Reference Voltage Accuracy $V_{in} = V_{outnom} + 0.4$ V to 11 V, $I_{load} = 0.1$ mA to 500 mA, $T_J = 85^{\circ}\text{C}$ | V_{ref} | -1.4% 1.162 | 1.178 | +1.4% 1.194 | V |
| Reference Voltage Accuracy (Note 5) $V_{in} = V_{outnom} + 0.4$ V to 11 V, $I_{load} = 0.1$ mA to 500 mA, $T_J = 150^{\circ}\text{C}$ | V_{ref} | -1.5% 1.160 | 1.178 | +1.5% 1.196 | V |
| Line Regulation $V_{in} = (V_{outnom} + 0.4$ V) to 11 V, $I_{load} = 0.1$ mA, $T_J = 25^{\circ}\text{C}$ | $Line_{Reg}$ | | 0.04 | | mV/V |
| Load Regulation $I_{load} = 0.1$ mA to 500 mA, $T_J = 25^{\circ}\text{C}$ | $Load_{Reg}$ | | 0.04 | | mV/mA |
| Dropout Voltage, $V_{out} = 98\%$ of V_{outnom} $I_{load} = 500$ mA $I_{load} = 300$ mA $I_{load} = 100$ mA $I_{load} = 1$ mA | V_{DO} | | – – – 10 | 340 230 140 – | mV |
| Peak Output Current ($V_{in} = V_{outnom} + 1.0$ V) | I_{pk} | 500 | 700 | 860 | mA |
| Thermal Shutdown | T_J | | 160 | | $^{\circ}\text{C}$ |
| Ground Current In Regulation $I_{load} = 500$ mA (Note 3) $I_{load} = 300$ mA (Note 3) $I_{load} = 50$ mA $I_{load} = 0.1$ mA In Dropout $V_{in} = V_{out} - 0.1$ V, $I_{load} = 0.1$ mA In Shutdown $V_{SD} = 6.0$ V, $V_{in} = 11$ V | I_{GND} I_{GNDsh} | | 6.0 3.5 0.7 130 – 8 | 10 6 1.5 180 450 20 | mA μA |
| Output Noise $I_{load} = 500$ mA, $f = 10$ Hz to 100 kHz, $C_{out} = 10$ μF , $C_{nr} = 10$ nF $I_{load} = 500$ mA, $f = 10$ Hz to 100 kHz, $C_{out} = 10$ μF , $C_{nr} = 0$ nF | V_{noise} | | 26 38 | | μV_{rms} |
| Shutdown Threshold Voltage OFF Threshold Voltage ON | V_{THSD} | 2.0 | | 0.4 | V V |
| SD Input Current, $V_{SD} = 0$ V to 0.4 V or $V_{SD} = 2.0$ V to V_{in} | I_{SD} | | 1.2 | 3.0 | μA |
| Output Current In Shutdown Mode, $V_{SD} = 2.0$ V, $V_{in} = 11$ V | I_{OSD} | | 0.07 | 1.0 | μA |
| Reverse Bias Protection, Current Flowing from the Output Pin to GND ($V_{in} = 0$ V, $V_{out_forced} = V_{out(nom)} \leq 7$ V) (Note 6) | I_{OUTR} | | 1.0 | | μA |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

- All limits at temperature extremes are guaranteed via correlation using standard statistical quality control (SQC) methods.
- Ambient temperature of 85°C corresponds to a junction temperature of 125°C under pulsed full load test conditions.
- Application stable with no load.
- $V_{IN} = 2.6$ V to 11 V for $V_{OUT(NOM)} \leq 2.2$ V and $T_J > 0^{\circ}\text{C}$, otherwise $V_{IN} = 2.9$ V to 11 V.
- Reverse bias protection feature valid only if $V_{out} - V_{in} \leq 7$ V.

TYPICAL CHARACTERISTICS




Figure 2. Output Voltage vs. Temperature




Figure 3. Ground Current vs. Output Current




Figure 4. Dropout Voltage vs. Output Current




Figure 5. Quiescent Current vs. Input Voltage




Figure 6. Enable OFF Threshold




Figure 7. Peak and Short Current vs. Temperature

TYPICAL CHARACTERISTICS




Figure 8. PSRR vs. Frequency




Figure 9. Output Noise Density

APPLICATIONS INFORMATION

Reverse Bias Protection

Reverse bias is a condition caused when the input voltage goes to zero, but the output voltage is kept high either by a large output capacitor or another source in the application which feeds the output pin.

Normally in a bipolar LDO all the current will flow from the output pin to input pin through the PN junction with limited current capability and with the potential to destroy the IC.

Due to an improved architecture, the NCP3334A can withstand up to 7.0 V on the output pin with virtually no current flowing from output pin to input pin, and only negligible amount of current (tens of μA) flowing from the output pin to ground for infinite duration.

Input Capacitor

An input capacitor of at least 1.0 μF , any type, is recommended to improve the transient response of the regulator and/or if the regulator is located more than a few inches from the power source. It will also reduce the circuit's sensitivity to the input line impedance at high frequencies. The capacitor should be mounted with the shortest possible track length directly across the regular's input terminals.

Output Capacitor

The NCP3334A remains stable with any type of capacitor as long as it fulfills its 1.0 μF requirement. There are no constraints on the minimum ESR and it will remain stable up to an ESR of 5.0 Ω . Larger capacitor values will improve the noise rejection and load transient response.

Adjustable Operation

The output voltage can be set by using a resistor divider with a range of 1.178 to 10 V. The appropriate resistor divider can be found by solving the equation below. The recommended current through the resistor divider is from 10 μA to 100 μA . This can be accomplished by selecting resistors in the $\text{k}\Omega$ range. As result, the $I_{\text{adj}} \cdot R_2$ becomes negligible in the equation and can be ignored.

$$V_{\text{out}} = 1.178 \cdot \left(1 + \frac{R_1}{R_2}\right) + I_{\text{adj}} \cdot R_2 \quad (\text{eq. 1})$$

Dropout Voltage

The voltage dropout is measured at 97% of the nominal output voltage.

Thermal Considerations

Internal thermal limiting circuitry is provided to protect the integrated circuit in the event that the maximum junction temperature is exceeded. This feature provides protection from a catastrophic device failure due to accidental overheating. This protection feature is not intended to be used as a substitute to heat sinking. The maximum power that can be dissipated, can be calculated with the equation below:

$$P_D = \frac{T_J(\text{max}) - T_A}{R_{\theta JA}} \quad (\text{eq. 2})$$

For improved thermal performance, contact the factory for the WDFN package option. The WDFN package includes an exposed metal pad that is specifically designed to reduce the junction to air thermal resistance, $R_{\theta JA}$.

ORDERING INFORMATION

| Device | Nominal Output Voltage | Marking | Package | Shipping [†] |
|------------------|------------------------|--------------|--------------------|-----------------------|
| NCP3334AMTADJTBG | Adj. | 3334A ADJ | WDFN8 (Pb-Free) | 3000 / Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


*Please contact factory for other voltage options.



SCALE 2:1


WDFN8 3x3, 0.5P
CASE 511CF
ISSUE O

DATE 23 MAR 2015


NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.05 AND 0.15 MM FROM TERMINAL TIP.
4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.
5. POSITIONAL TOLERANCE APPLIES TO ALL OF THE EXPOSED PADS.

| MILLIMETERS | | |
|-------------|------|------|
| DIM | MIN | MAX |
| A | 0.70 | 0.80 |
| A1 | 0.00 | 0.05 |
| A3 | 0.20 | REF |
| b | 0.20 | 0.30 |
| D | 3.00 | BSC |
| D2 | 1.65 | 1.85 |
| E | 3.00 | BSC |
| E2 | 1.35 | 1.55 |
| e | 0.50 | BSC |
| L | 0.30 | 0.50 |
| L1 | 0.00 | 0.15 |



GENERIC
MARKING DIAGRAM*


XXXXX = Specific Device Code
A = Assembly Location
L = Wafer Lot
Y = Year
W = Work Week
▪ = Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking.

Pb-Free indicator, "G" or microdot "▪", may or may not be present.


RECOMMENDED
SOLDERING FOOTPRINT*


DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

| | | |
|-------------------------|-------------------------|---|
| DOCUMENT NUMBER: | 98AON97082F | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION: | WDFN8, 3X3, 0.5P | PAGE 1 OF 1 |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales