ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

Intelligent Power Module (IPM) 1200 V, 5 A

Advance Information

NFAM0512L5BT

General Description

The NFAM0512L5BT is a fully-integrated inverter power module consisting of an independent High side gate driver, LVIC, six IGBT's and a temperature sensor (VTS and NTC Thermistor), suitable for driving permanent magnet synchronous (PMSM) motors, brushless DC (BLDC) motors and AC asynchronous motors. The IGBT's are configured in a three-phase bridge with separate emitter connections for the lower legs for maximum flexibility in the choice of control algorithm.

The power stage has under-voltage lockout protection (UVP). Internal boost diodes are provided for high side gate boost drive.

Features

- Three–phase 1200 V, 5 A IGBT Module with Independent Drivers
- Active Logic Interface
- Built-in Under-voltage Protection (UVP)
- Integrated Bootstrap Diodes and Resistors
- Separate Low-side IGBT Emitter Connections for Individual Current Sensing of Each Phase
- Temperature Sensor (VTS or NTC Thermistor)
- UL 1557 Certified (File No.339285)
- This Device is Pb-Free and RoHS Compliant

Typical Application

- Industrial Drives
- Industrial Pumps
- Industrial Fans
- Industrial Automation





Figure 1. Application Schematic

This document contains information on a new product. Specifications and information herein are subject to change without notice.



ON Semiconductor®

www.onsemi.com



DIP39 54.5 x 31.0 CASE MODGC

MARKING DIAGRAM

O NFAM0512L5BT O ZZZATYWW

Device marking is on package top side

NFAM0512L5BT = Specific Device Code
ZZZ = Assembly Lot Code
A = Assembly Location
T = Test Location
Y = Year
WW = Work Week

ORDERING INFORMATION

Device	Package	Shipping [†] (Qty / Packing)
NFAM0512L5BT	DIP39, 31.0x54.5 (Pb-Free)	90 / BOX

APPLICATION SCHEMATIC




Figure 2. Application Schematic - Adjustable Option

BLOCK DIAGRAM




Figure 3. Equivalent Block Diagram

PIN FUNCTION DESCRIPTION

Pin	Name	Description
1	VS(U)	High-Side Bias Voltage GND for U Phase IGBT Driving
(2)	ı	Dummy
3	VB(U)	High-Side Bias Voltage for U Phase IGBT Driving
4	VDD(UH)	High-Side Bias Voltage for U Phase IC
(5)	ı	Dummy
6	HIN(U)	Signal Input for High-Side U Phase
7	VS(V)	High-Side Bias Voltage GND for V Phase IGBT Driving
(8)	-	Dummy
9	VB(V)	High-Side Bias Voltage for V Phase IGBT Driving
10	VDD(VH)	High-Side Bias Voltage for V Phase IC
(11)	-	Dummy
12	HIN(V)	Signal Input for High-Side V Phase
13	VS(W)	High-Side Bias Voltage GND for W Phase IGBT Driving
(14)	-	Dummy
15	VB(W)	High-Side Bias Voltage for W Phase IGBT Driving
16	VDD(WH)	High-Side Bias Voltage for W Phase IC
(17)	-	Dummy
18	HIN(W)	Signal Input for High–Side W Phase
(19)	-	Dummy
20	VTS	Voltage Output for LVIC Temperature Sensing Unit
21	LIN(U)	Signal Input for Low–Side U Phase
22	LIN(V)	Signal Input for Low–Side V Phase
23	LIN(W)	Signal Input for Low–Side W Phase
24	VFO	Fault Output
25	CFOD	Capacitor for Fault Output Duration Selection
26	CIN	Input for Current Protection
27	VSS	Low-Side Common Supply Ground
28	VDD(L)	Low–Side Bias Voltage for IC and IGBTs Driving
(29)	-	Dummy
(30)	-	Dummy
31	NW	Negative DC-Link Input for U Phase
32	NV	Negative DC-Link Input for V Phase
33	NU	Negative DC-Link Input for W Phase
34	W	Output for U Phase
35	V	Output for V Phase
36	U	Output for W Phase
37	Р	Positive DC–Link Input
38	VTH	Thermistor Bias Voltage (T) / Not connection
39	RTH	Series Resister for Thermistor (Temperature Detection) *optional for T

^{1.} Pins of () are the dummy for internal connection. These pins should be no connection.

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^{\circ}C$) (Note 2)

Rating	Symbol	Conditions	Value	Unit
Supply Voltage	VPN	P – NU, NV, NW	900	V
Supply Voltage (Surge)	VPN(Surge)	P – NU, NV, NW, (Note 3)	1000	V
Self Protection Supply Voltage Limit (Short–Circuit Protection Capability	VPN(PROT)	VDD = VBS = 13.5 V ~ 16.5 V, Ti = 150°C, Vces < 1200 V, Non–Repetitive, < 2 μs	800	V
Collector-Emitter Voltage	Vces		1200	V
Maximum Repetitive Revers Voltage	VRRM		1200	V
Each IGBT Collector Current	±lc		±5	Α
Each IGBT Collector Current (Peak)	±lcp	Under 1 ms Pulse Width	±10	Α
Control Supply Voltage High-Side	VDD	VDD(UH, VH, WH), VDD(L) – VSS	-0.3 to 20	V
Control Bias Voltage	VBS	VB(U) - VS(U), VB(V) - VS(V), VB(W) - VS(W)	-0.3 to 20	V
Input Signal Voltage	VIN	HIN(U), HIN(V), HIN(W), LIN(U), LIN(V), LIN(W) – VSS	-0.3 to VDD	V
Fault Output Supply Voltage	VFO	VFO - VSS	-0.3 to VDD	V
Fault Output Current	IFO	Sink Current at VFO pin	2	mA
Current Sensing Input Voltage	VCIN	CIN - VSS	-0.3 to VDD	V
Corrector Dissipation	Pc	Per One Chip	59	W
Operating Junction Temperature	Tj		-40 to +150	°C
Storage Temperature	Tstg		-40 to +125	°C
Module Case Operation Temperature	Tc		-40 to +125	°C
Isolation Voltage	Viso	60 Hz, Sinusoidal, AC 1 minute, Connection Pins to Heat Sink Plate	2500	V rms

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

2. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe

THERMAL CHARACTERISTICS

Rating	Symbol	Conditions	Min	Тур	Max	Unit
Junction to Case Thermal Resistance	Rth(j-c)Q	Inverter IGBT Part (per 1/6 Module)	-	-	2.1	°C/W
	Rth(j-c)F	Inverter FRD Part (per 1/6 Module)	_	_	2.6	°C/W

^{4.} Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe Operating parameters.

RECOMMENDED OPERATING RANGES (Note 5)

Rating	Symbol	Conditions	Min	Тур	Max	Unit
Supply Voltage	VPN	P – NU, NV, NW	-	600	800	V
Gate Driver Supply Voltages	VDD	VDD(UH, VH, WH), VDD(L) – VSS	13.5	15	16.5	V
	VBS	VB(U) – VS(U), VB(V) – VS(V), VB(W) – VS(W)	13.0	15	18.5	V
Supply Voltage Variation	dVDD / dt dVBS / dt		-1	-	1	V/μs
PWM Frequency	fPWM		1		20	kHz
Dead Time	DT	Turn-off to Turn-on (external)	3	-	-	μS

Operating parameters.

^{3.} This surge voltage developed by the switching operation due to the wiring inductance between P and NU, NV, NW terminal.

RECOMMENDED OPERATING RANGES (Note 5) (continued)

Rating	Symbol	Conditions	Conditions		Тур	Max	Unit
Allowable r.m.s. Current	lo	VPN = 600 V, VDD = VBS = 15 V, P.F. = 0.8.	f _{PWM} = 5 kHz	ı	ı	7.7	A rms
	F.F. = 0.6, Tc ≤ 125°C, Tj ≤ 150°C, (Note 5)		f _{PWM} = 15 kHz	-	-	4.0	
Allowable Input Pulse Width	PWIN (on)	VPN ≤ 800 V, 13.5 V ≤ VDD ≤ 16.5 V, 13.0 V ≤ VBS ≤ 18.5 V, -40°C ≤ Tc ≤ 150°C		2.0	-	-	μs
	PWIN (off)			2.5	-	-	
Package Mounting Torque		M3 Type Screw		0.6	0.7	0.9	Nm

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

- 5. Allowable r.m.s Current depends on the actual conditions.
- 6. Flatness tolerance of the heatsink should be within –50 μ m to +100 μ m.

ELECTRICAL CHARACTERISTICS (Tc = 25°C, VDD = 15 V, VBS = 15 V, unless otherwise noted) (Note 7)

P	arameter	Test Conditions		Symbol	Min	Тур	Max	Unit
INVERTER	SECTION				-	-		
Collector–Emitter Leakage		Vce = Vces, Tj = 25°C	Ices	_	_	1	mA	
Current		Vce = Vces, Tj = 150°C			_	_	10	mA
Collector-En Voltage	nitter Saturation	VDD = VBS = 15 V, IN = 5 V Ic = 5 A, Tj = 25°C		VCE(sat)	_	1.75	2.5	V
		VDD = VBS = 15 V, IN = 5 V Ic = 5 A, Tj = 150°C			_	1.90	-	V
FWDi Forwa	rd Voltage	IN = 0 V, If = 5 A, Tj = 25°C		VF	-	1.70	2.5	V
		IN = 0 V, If = 5 A, Tj = 150°C			_	1.50	-	V
High Side	Switching Times	VPN = 600 V, VDD(H) = VDD(L)	ton	0.80	1.40	2.00	μs	
		Ic = 5 A, Tj = 25° C, IN = $0 \Leftrightarrow 5$ Inductive Load	tc (on)	-	0.30	0.60	μS	
				toff	_	2.00	2.70	μS
			tc (off)	-	0.20	0.60	μS	
			trr	-	0.40	-	μS	
Low Side	Switching Times	VPN = 600 V, VDD(H) = VDD(L	ton	0.90	1.50	2.10	μs	
		Ic = 5 A, Tj = 25°C, IN = $0 \Leftrightarrow 5$ Inductive Load	tc (on)	_	0.30	0.60	μS	
			toff	_	2.10	2.80	μS	
			tc (off)	_	0.20	0.60	μS	
			trr	_	0.40	-	μS	
DRIVER SE	CTION							
Quiescent V	DD Supply Current	VDD(UH,VH,WH) = 15 V, HIN(U,V,W) = 0 V	VDD(UH) – VSS VDD(VH) – VSS VDD(WH) – VSS	IQDDH	-	_	0.30	mA
		VDD(L) = 15 V, LIN(U, V, W) = 0 V	VDD(L) - VSS	IQDDL	-	-	3.50	mA
Operating VDD Supply Current		VDD(UH, VH, WH) = 15 V, f _{PWM} = 20 kHz, Duty = 50%, Applied to one PWM Signal Input for High–Side	VDD(UH) - VSS VDD(VH) - VSS VDD(WH) - VSS	IPDDH	-	-	0.40	mA
		VDD(L) = 15 V, f _{PWM} = 20 kHz, Duty = 50%, Applied to one PWM Signal Input for Low–Side	VDD(L) – VSS	IPDDL	-	-	9.00	mA

ELECTRICAL CHARACTERISTICS (Tc = 25°C, VDD = 15 V, VBS = 15 V, unless otherwise noted) (Note 7) (continued)

Parameter	Test Conditions		Symbol	Min	Тур	Max	Unit
DRIVER SECTION			•	•	•	•	
Quiescent VBS Supply Current	VBS = 15 V HIN(U, V, W) = 0 V	VB(U) - VS(U) VB(V) - VS(V) VB(W) - VS(W)	IQBS	-	_	0.30	mA
Operating VBS Supply Current	VDD = VBS = 15 V, f _{PWM} = 20 kHz, Duty = 50%, Applied to one PWM Signal Input for High–Side	VB(U) - VS(U) VB(V) - VS(V) VB(W) - VS(W)	IPBS	-	-	8.00	mA
ON Threshold Voltage	HIN(U, V, W) - VSS, LIN(U, V,	W) – VSS	VIN(ON)	-	-	2.6	V
OFF Threshold Voltage]	VIN(OFF)	0.8	-	-	V	
Short Circuit Trip Level	VDD = 15 V, CIN-VSS		VCIN(ref)	0.46	0.48	0.50	V
Supply Circuit Under–Voltage	Detection Level	UVDDD	10.3	-	12.5	V	
Protection	Reset Level	UVDDR	10.8	_	13.0	V	
	Detection Level Reset Level		UVBSD	10.0	-	12.0	V
			UVBSR	10.5	_	12.5	V
Voltage Output for LVIC Temperature Sensing Unit	VTS-VSS = 10 nF, Temp. = 25	°C	VTS	0.905	1.030	1.155	V
Fault Output Voltage	VDD = 0 V, CIN = 0 V, VFO Circuit: 10 kΩ to 5 V Pull–	VFOH	4.9	-	-	V	
	VDD = 0 V, CIN = 1 V, VFO Circuit: 10 kΩ to 5 V Pull–up		VFOL	-	-	0.95	V
Fault-Output Pulse Width	CFOD = 22 nF		tFOD	1.6	2.4	_	ms
BOOTSTRAP SECTION							
Bootstrap Diode Forward Current	If = 0.1 A		VF	3.4	4.6	5.8	V
Built-in Limiting Resistance			RBOOT	30	38	46	Ω

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

^{9.} Values based on design and/or characterization.




Figure 4. Temperature of LVIC versus VOT Characteristics

^{7.} Performance guaranteed over the indicated operating temperature range by design and/or characterization tested at T_J = T_A = 25°C. Low duty cycle pulse techniques are used during testing to maintain the junction temperature as close to ambient as possible.

^{8.} The fault—out pulse width tFOD depends on the capacitance value of CFOD according to the following approximate equation: tFOD = 0.1 x 10⁶ x CFOD (s).

THERMISTOR CHARACTERISTIC

Parameter	Symbol	Condition	Min	Тур	Max	Unit
Resistance	R ₂₅	Tc = 25°C	46.530	47	47.47	kΩ
Resistance	R ₁₂₅	Tc = 125°C	1.344	1.406	1.471	kΩ
B-Constant (25-50°C)	-	В	4009.5	4050	4090.5	K
Temperature Range	-	-	-40	1	+125	°C




Figure 5. Thermistor Resistance versus Case Temperature

PACKAGE DIMENSIONS

MINI DIP39, 31.0x54.5 CASE MODGC **ISSUE A**

DETAIL C

DETAIL


NOTES

SEATING PLANE

- DIMENSIONING AND TOLERANCING PER. ASME Y14.5M, 2009. 1.
- CONTROLLING DIMENSION: MILLIMETERS
 DIMENSION 6 and c APPLY TO THE PLATED LEADS
 AND ARE MEASURED BETWEEN 1.00 AND 2.00
 FROM THE LEAD TIP.
- POSITION OF THE LEAD IS DETERMINED AT THE ROOT OF THE LEAD WHERE IT EXITS THE PACKAGE BODY.


-e6

SHORTENED/CUT PINS ARE 2,5,8,11,14,17,19,29 AND 30.





0

	MILLIMETERS					
DIM	MIN.	NDM.	MAX.			
Ε	30.90	31.00	31.10			
E1	33.50 REF					
E2	í	26.14 REI	-			
E3	1	2.35 REI	4			
E4		8.00 REF				
E5	35.40	35.90	36.40			
e		2.81 REF				
el		7.62 BSC	;			
e2		6.60 BSC	;			
e3		3.30 BSC	:			
e4		5.35 REF	•			
e5		6.10 BSC	:			
e6		8.02 REF	•			
e7		1.78 BSC	:			
e8	1	0.35 REI	•			
e9	1	0.25 REI				
e10		3.60 REF	•			
e11	1.00 REF					
e12	0.89 BSC					
F	3.20 3.30 3.40					
F1	1.40	1.50	1.60			
L		5.60 REF				



€7





DETAIL C

П:3

ON Semiconductor and IN are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com TECHNICAL SUPPORT

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada

ON Semiconductor Website: www.onsemi.com Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative