Schottky Barrier Diode

NSR0630P2

Schottky barrier diodes are optimized for very low forward voltage drop and low leakage current and are used in a wide range of dc-dc converter, clamping and protection applications in portable devices. NSR0630P2 in a SOD-923 miniature package enables designers to meet the challenging task of achieving higher efficiency and meeting reduced space requirements.

Features

- Very Low Forward Voltage Drop 370 mV @ 100 mA
- Low Reverse Current 1.4 µA @ 10 V VR
- 600 mA of Continuous Forward Current
- Power Dissipation of 190 mW with Minimum Trace
- Very High Switching Speed
- Low Capacitance CT = 10 pF
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- LCD and Keypad Backlighting
- Camera Photo Flash
- Buck and Boost dc-dc Converters

Buck and Boost dc–dc Converters			NE
• Reverse Voltage and Current Protecti	ion		Win
Clamping & Protection		COV	"
Markets Makila Handarta		2ENT	AC (
Mobile HandsetsMP3 Players	10,5	COLLI	NE
 Digital Camera and Camcorders 	15	17/	
• Notebook PCs & PDAs	ch cs	· W	
Notebook PCs & PDAsGPS	RES		
	RES		
• GPS	Symbol	Value	Unit
• GPS MAXIMUM RATINGS	Symbol V _R	Value 30	Unit V
GPS MAXIMUM RATINGS Rating			
GPS MAXIMUM RATINGS Rating Reverse Voltage	V _R	30	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1



ON Semiconductor®

www.onsemi.com

30 V SCHOTTKY BARRIER DIODE





Specific Device Code = Month Code

ORDERING INFORMATION

Device	Package	Shipping†
NSR0630P2T5G	SOD-923 (Pb-Free)	2 mm Pitch 8000/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

NSR0630P2

THERMAL CHARACTERISTICS

Characteristic	Symbol	Min	Тур	Max	Unit
Thermal Resistance Junction-to-Ambient (Note 1) Total Power Dissipation @ T _A = 25°C	R _{θJA} P _D			520 190	°C/W mW
Thermal Resistance Junction-to-Ambient (Note 2) Total Power Dissipation @ T _A = 25°C	R _{θJA} P _D			175 570	°C/W mW
Junction and Storage Temperature Range	T _J , T _{stg}			-55 to +125	°C

- Mounted onto a 4 in square FR-4 board 10 mm sq. 1 oz. Cu 0.06" thick single sided. Operating to steady state.
 Mounted onto a 4 in square FR-4 board 1 in sq. 1 oz. Cu 0.06" thick single sided. Operating to steady state.

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
Reverse Leakage (V _R = 10 V) (V _R = 30 V)	I _R		1.4	10 200	μΑ
Forward Voltage (I _F = 10 mA) (I _F = 100 mA) (I _F = 500 mA)	V _F		0.28 0.37 0.52	0.37 0.46 0.62	V
Total Capacitance (V _R = 1.0 V, f = 1 MHz)	СТ		10		pF




Figure 1. Forward Voltage

Figure 2. Leakage Current






Figure 3. Total Capacitance






SOD-923 0.80x0.60x0.37 CASE 514AB ISSUE E

DATE 08 FEB 2024




NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018. CONTROLLING DIMENSION: MILLIMETERS.
- MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
- DIMENSION L WILL NOT EXCEED 0.30mm.




N	MILLIM	IETER:	2	
DIM	MIN.	N□M.	MAX.	
Α	0.34	0.37	0.40	
b	0.15	0,20	0.25	
C	0.07	0.12	0.17	
D	0.75	0.80	0.85	
Е	0,55	0,60	0.65	
Н	0.95	1.00	1.05	
L	0.19 REF			
L2	0.05	0.10	0.15	



RECOMMENDED MOUNTING FUUTPRINT

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC MARKING DIAGRAM*



Χ = Specific Device Code = Date Code М

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "=", may or may not be present. Some products may not follow the Generic Marking.

PIN 1. CATHODE (POLARITY BAND) NO POLARITY 2. ANODE

DESCRIPTION	SOD-923 0.80x0.60x0.37		PAGE 1 OF 1	
DOCUMENT NUMBER:	98AON23284D	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales