

MOSFET – Power, P-Channel, SOT-223

-5.2 A, -30 V

NTF5P03, NVF5P03


Features

- Ultra Low $R_{DS(on)}$
- Higher Efficiency Extending Battery Life
- Logic Level Gate Drive
- Miniature SOT-223 Surface Mount Package
- Avalanche Energy Specified
- AEC-Q101 Qualified and PPAP Capable – NVF5P03T3G
- These Devices are Pb-Free and are RoHS Compliant


Applications

- DC-DC Converters
- Power Management
- Motor Controls
- Inductive Loads
- Replaces MMFT5P03HD

-5.2 AMPERES, -30 VOLTS
 $R_{DS(on)} = 100 \text{ m}\Omega$




P-Channel MOSFET



**SOT-223
CASE 318E
STYLE 3**

MARKING DIAGRAM & PIN ASSIGNMENT



A = Assembly Location
Y = Year
M = Date Code
5P03 = Specific Device Code
▪ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping [†]
NTF5P03T3G	SOT-223 (Pb-Free)	4000 / Tape & Reel
NVF5P03T3G	SOT-223 (Pb-Free)	4000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

NTF5P03, NVF5P03

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Negative sign for P-Channel devices omitted for clarity

Rating		Symbol	Max	Unit
Drain-to-Source Voltage		V _{DSS}	-30	V
Drain-to-Gate Voltage (R _{GS} = 1.0 MΩ)		V _{DGR}	-30	V
Gate-to-Source Voltage – Continuous		V _{GS}	± 20	V
1 sq in FR-4 or G-10 PCB 10 seconds	Thermal Resistance – Junction-to-Ambient	R _{THJA}	40	°C/W
	Total Power Dissipation @ T _A = 25°C	P _D	3.13	Watts
	Linear Derating Factor		25	mW/°C
	Drain Current – Continuous @ T _A = 25°C	I _D	-5.2	A
	Continuous @ T _A = 70°C	I _D	-4.1	A
Pulsed Drain Current (Note 1)		I _{DM}	-26	A
Minimum FR-4 or G-10 PCB 10 seconds	Thermal Resistance – Junction-to-Ambient	R _{THJA}	80	°C/W
	Total Power Dissipation @ T _A = 25°C	P _D	1.56	Watts
	Linear Derating Factor		12.5	mW/°C
	Drain Current – Continuous @ T _A = 25°C	I _D	-3.7	A
	Continuous @ T _A = 70°C	I _D	-2.9	A
Pulsed Drain Current (Note 1)		I _{DM}	-19	A
Operating and Storage Temperature Range		T _J , T _{stg}	- 55 to 150	°C
Single Pulse Drain-to-Source Avalanche Energy – Starting T _J = 25°C (V _{DD} = -30 Vdc, V _{GS} = -10 Vdc, Peak I _L = -12 Apk, L = 3.5 mH, R _G = 25 Ω)		E _{AS}	250	mJ

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Repetitive rating; pulse width limited by maximum junction temperature.

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
----------------	--------	-----	-----	-----	------

OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage (C _{pk} ≥ 2.0) (Notes 2 and 4) (V _{GS} = 0 Vdc, I _D = -250 μAdc) Temperature Coefficient (Positive)	V _{(BR)DSS}	-30	-	-	Vdc
		-	-28	-	mV/°C
Zero Gate Voltage Drain Current (V _{DS} = -24 Vdc, V _{GS} = 0 Vdc) (V _{DS} = -24 Vdc, V _{GS} = 0 Vdc, T _J = 125°C)	I _{DSS}	-	-	-1.0	μAdc
		-	-	-25	
Gate-Body Leakage Current (V _{GS} = ± 20 Vdc, V _{DS} = 0 Vdc)	I _{GSS}	-	-	± 100	nAdc

ON CHARACTERISTICS (Note 2)

Gate Threshold Voltage (C _{pk} ≥ 2.0) (Notes 2 and 4) (V _{DS} = V _{GS} , I _D = -250 μAdc) Threshold Temperature Coefficient (Negative)	V _{GS(th)}	-1.0	-1.75	-3.0	Vdc
		-	3.5	-	mV/°C
Static Drain-to-Source On-Resistance (C _{pk} ≥ 2.0) (Notes 2 and 4) (V _{GS} = -10 Vdc, I _D = -5.2 Adc) (V _{GS} = -4.5 Vdc, I _D = -2.6 Adc)	R _{DS(on)}	-	76	100	mΩ
		-	107	150	
Forward Transconductance (Note 2) (V _{DS} = -15 Vdc, I _D = -2.0 Adc)	g _{fs}	2.0	3.9	-	Mhos

DYNAMIC CHARACTERISTICS

Input Capacitance	(V _{DS} = -25 Vdc, V _{GS} = 0 V, f = 1.0 MHz)	C _{iss}	-	500	950	pF
Output Capacitance		C _{oss}	-	153	440	
Transfer Capacitance		C _{rss}	-	58	140	

NTF5P03, NVF5P03

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic		Symbol	Min	Typ	Max	Unit
SWITCHING CHARACTERISTICS (Note 3)						
Turn-On Delay Time	(V _{DD} = -15 Vdc, I _D = -4.0 Adc, V _{GS} = -10 Vdc, R _G = 6.0 Ω) (Note 2)	t _{d(on)}	–	10	24	ns
Rise Time		t _r	–	33	48	
Turn-Off Delay Time		t _{d(off)}	–	38	94	
Fall Time		t _f	–	20	92	
Turn-On Delay Time	(V _{DD} = -15 Vdc, I _D = -2.0 Adc, V _{GS} = -10 Vdc, R _G = 6.0 Ω) (Note 2)	t _{d(on)}	–	16	38	ns
Rise Time		t _r	–	45	110	
Turn-Off Delay Time		t _{d(off)}	–	23	60	
Fall Time		t _f	–	24	80	
Gate Charge	(V _{DS} = -24 Vdc, I _D = -4.0 Adc, V _{GS} = -10 Vdc) (Note 2)	Q _T	–	15	38	nC
		Q ₁	–	1.6	–	
		Q ₂	–	3.5	–	
		Q ₃	–	2.6	–	

SOURCE-DRAIN DIODE CHARACTERISTICS

Forward On-Voltage	(I _S = -4.0 Adc, V _{GS} = 0 Vdc) (I _S = -4.0 Adc, V _{GS} = 0 Vdc, T _J = 125°C) (Note 2)	V _{SD}	– –	-1.1 -0.89	-1.5 –	Vdc
Reverse Recovery Time	(I _S = -4.0 Adc, V _{GS} = 0 Vdc, dI _S /dt = 100 A/μs) (Note 2)	t _{rr}	–	34	–	ns
		t _a	–	20	–	
		t _b	–	14	–	
Reverse Recovery Stored Charge		Q _{RR}	–	0.036	–	μC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

- Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2.0%.
- Switching characteristics are independent of operating junction temperatures.
- Reflects typical values.

$$C_{pk} = \left| \frac{\text{Max limit} - \text{Typ}}{3 \times \text{SIGMA}} \right|$$

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance versus Gate-to-Source Voltage




Figure 4. On-Resistance versus Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current versus Voltage

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage versus Total Charge




Figure 9. Resistive Switching Time Variation versus Gate Resistance





Figure 10. Diode Forward Voltage versus Current



Mounted on 2"sq. FR4 board (1"sq. 2 oz. Cu 0.06" thick single sided) with on die operating, 10 s max.

Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Avalanche Energy versus Starting Junction Temperature

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 13. FET Thermal Response

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales